

CATALOG LISTING  
1TP67-L4 SERIES CHART 1  
PAGE 1 OF 1

ISSUE  
3

CHECK

REVISIONS  
A C092162  
JAK  
5 MAR 98  
B C094412  
DLM  
13 OCT 99

CHECK

CHECK

CHECK

CHECK


FORMTEK  
DRAWN  
KDR 10 JUN 94

**MICRO SWITCH**  
FREEPORT ILLINOIS U.S.A.  
A DIVISION OF HONEYWELL  
FED MFG CODE 91929

**SWITCH-ROCKER  
FLUSH KEY**

CATALOG LISTING  
**1TP67-L4 SERIES**  
**CHART 1**

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



| CATALOG LISTING | CIRCUIT MADE WITH<br>BUTTON DEPRESSED ON |                 |                          | ELECTRICAL<br>DATA                                                                   |
|-----------------|------------------------------------------|-----------------|--------------------------|--------------------------------------------------------------------------------------|
|                 | LUG<br>SIDE<br>(1-2)                     | CENTER<br>(1-2) | OPPOSITE<br>LUG<br>(2-3) |                                                                                      |
| ITP67-1-L4      | ON                                       | OFF             | ON                       | L191 15A 125, 250, 277 VAC<br>1/2HP 125 VAC<br>1HP 250, 277 VAC<br>5A 125 VAC "L"    |
| ITP67-2-L4      | OFF                                      | NONE            | ON                       |                                                                                      |
| ITP67-3-L4      | ON                                       | NONE            | ON                       |                                                                                      |
| ITP67-21-L4     | NONE                                     | OFF             | ON                       |                                                                                      |
| ITP67-31-L4     | NONE                                     | ON              | ON                       |                                                                                      |
| ITP67-4-L4      | MOM OFF                                  | NONE            | ON                       | L192 10A 125, 250, 277 VAC<br>1/4HP 125 VAC,<br>1/2HP 250, 277 VAC<br>3A 125 VAC "L" |
| ITP67-5-L4      | MOM ON                                   | OFF             | ON                       |                                                                                      |
| ITP67-6-L4      | MOM ON                                   | NONE            | OFF                      |                                                                                      |
| ITP67-7-L4      | MOM ON                                   | OFF             | MOM ON                   |                                                                                      |
| ITP67-8-L4      | MOM ON                                   | NONE            | ON                       |                                                                                      |
| ITP67-51-L4     | NONE                                     | ON              | MOM ON                   |                                                                                      |
| ITP67-61-L4     | MOM ON                                   | OFF             | NONE                     |                                                                                      |



NOTES  
1 - MICRO SWITCH CAT LISTING MARKED ON SIDE OF SWITCH  
2 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F  
3 - SCREWS FURNISHED UNASSEMBLED

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES  
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR  
REFERENCE UNLESS NOTED. TOLERANCES ARE:

|              | DIM     | TOL   | DIM     | TOL   |
|--------------|---------|-------|---------|-------|
|              | mm      | mm/in | in      | mm/in |
| NO PLACES    | X       | 1/32  | X       | 0.015 |
| ONE PLACE    | X X     | 0.015 | X X     | 0.015 |
| TWO PLACES   | X X X   | 0.005 | X X X   | 0.005 |
| THREE PLACES | X X X X | 0.001 | X X X X | 0.001 |
| ANGLES       |         |       |         |       |

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

WEIGHT