



INSERTO SERRACAVI
(CLAMPING INSERT)

CORPO CORAZZA
(CABLE CLAMP BODY)

#5-20 VITI AUTOFILETTANTI IN ACCIAIO ZINCATO (Q.TA' 2)
(#5-20 SELF-TAPPING SCREWS, ZINC PLATED STEEL, Q.TY 2)



AREA SERRAGGIO CAVI
(CLAMPING AREA)



1) MATERIALE : TERMOPLASTICO, COLORE NERO
(MATERIAL : THERMOPLASTIC, BLACK COLOUR)


2) PARTICOLARI FORNITI NON ASSEMBLATI IN SACCHETTO DI PLASTICA
(PARTS PACKAGED UNASSEMBLED INTO A PLASTIC BAG)

3) L'AREA SERRAGGIO CAVI E' VARIABILE DA 6.45 A 103.9 mm²
IN FUNZIONE DEL TIPO E POSIZIONE DELL'INSERTO SERRACAVO
(CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .161 SQ. IN.
BY SELECTING AND REVERSING CLAMPING INSERTS)

4) QUESTO CONNETTORE E' RICONOSCIUTO  E CERTIFICATO 
(THIS CONNECTOR IS UL RECOGNIZED AND CSA CERTIFIED)

5) Ø MAX DEL FASCIO CAVI = 11.5 mm.
(MAXIMUM CABLE O.D. = .453 IN.)

P/N 182663-1 COME RAPPRESENTATO
(P/N 182663-1 AS SHOWN)

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN R. FABRIS	TE Connectivity	
		0 PLC ± 1 PLC ± ±0.3 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±2°		CHK -	NAME C.P.C. CABLE CLAMP KIT SIZE 13	
MATERIAL -		FINISH -		APVD C. TARTARI	SIZE A3	CAGE CODE 00779
				PRODUCT SPEC 108-10024	DRAWING NO C-182663	
				APPLICATION SPEC -	SCALE 2:1	
				WEIGHT -	SHEET 1	
				CUSTOMER DRAWING	REV C1	