

Straight Blade Devices 15 and 20 Ampere, 250 Volts

2 Pole, 3 Wire Grounding

HBL® Extra Heavy Duty, Specification Grade Receptacles



15A 250V
NEMA 6-15R
UL CSA
1.5 HP



20A 250V
NEMA 6-20R
UL CSA
2 HP

Receptacles

HBL® Extra Heavy Duty, Specification Grade, Duplex

Description	Color	Catalog Numbers	
Flush, nylon face, back and side wired, multiple drive screws.	Black	—	HBL5462BK
	Brown	HBL5662	HBL5462
	Gray	—	HBL5462GY
	Ivory	HBL5662I	HBL5462I
	Red	—	HBL5462R
Isolated ground. ⁽¹⁾	Orange	IG5662	IG5462

HBL® Extra Heavy Duty, Specification Grade, Single

Description	Color	Catalog Numbers	
Flush, nylon face, back & side wired.	Brown	HBL5661	HBL5461
	Ivory	HBL5661I	HBL5461I
Isolated ground. ⁽¹⁾	Orange	IG5661	IG5461
Panel mount 1.94 in. (49.3) centers.	Brown	HBL5684	—
Ring terminal connection.	Brown	HBL5661RT	—

HBL® Extra Heavy Duty, Specification Grade Duplex and Panel Mount, Single

Description	Color	Catalog Numbers	
Flush, nylon face, side wired only.	Brown	HBL5652	—
	Ivory	HBL5652I	—
Panel mount 1.75 in. (44.5) centers.	Brown	HBL5658	—

Notes: HP ratings are AC only.

See page A-44 for accessories.

(1) See Section J for full line of isolated ground devices.

