


DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENING VERPLICHT.

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO JS IN CASE OF NO USAGE

BS, A , 201499, 002, 00

REV.	DATE	DESCRIPTION	BY	C'K'D'
01	12-02-96	CONVERSION ME10	NIETVELT	
02	08.10.96	CHANGED DRILLING HOLE PATTERN	S.V.D.	
03	29-08-97	B-SYMBOL DELETED	NIETVELT	



MATERIAL :

BODY : POLYAMIDE 6.6 ; COLOUR : BLACK

CONTACTS : BRASS

PERFORMANCE CHARACTERISTICS :

OPERATING TEMPERATURE : -55°C TO +105°C

INSULATING RESISTANCE : 5000M Ω MIN.

TEST POTENTIAL : 2000 VAC

CURRENT RATING : 5 AMPS

NOTES :

CONNECTOR SUPPLIED FULLY LOADED WITH MACHINED MALE CONTACTS.

MATING PART : SMS10P3

*PLATING INDICATION : SEE SHEET 001.

GEN. ST.	01		02		03		04		05		06		07		08		0D		50		60		70		80		90				
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88

1DEC $\pm 0,2$ 1DEC 2DEC $\pm 0,1$ 2DEC ANGLES $\pm 1^\circ$ HOEKEN	APPR.	DATE	SIGN.	QIKMATE R.ANGLED PINHEADER 10MALE DIPSOLDER CTS.
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	DRAFT	31-08-92	Y.D.	CAT. No. SMS10PHGE6
ALL DIMENSIONS IN MM	CHECKED			 SOURIAU Connection Technology
ALLE AFMETINGEN IN MM	PROD. MGR.			SOURIAU Route Nationale 23 72470 CHAMPAGNE
	PR. ENG. MGR.			SCALE 2 / 1
	PR. MGT. MGR.			BS, A , 201499, 002, 00 DRAWING NR. CUSTOMER DRAWING
	REFERENCES / REFERENTIES			NOT EXPORT CONTROLLED