





- 1 ACCEPTS RECEPTACLE CONTACTS 1217378(#18-#22 AWG SINGLE WIRE), 1217094(#18-#14 AWG SINGLE WIRE) AND 1217095 (TWO #18'S OR TWO #16'S OR A #16 + #18 COMBINATION).
- 2 FRONT AND BACK VIEWS SHOW ONLY THE GRIPPERS. FOR KEYING AND POLARIZATION FEATURES, SEE SPECIAL FRONT VIEW.
- 3 MOLDED WITHOUT GRIPPERS.
- 4 PRELIMINARY - NOT FOR PRODUCTION.
- 5 PA6, GWEPT 750°C NO FLAME.
- 6 PRE-PRODUCTION - FASR REQUIRED



04-A	NATURAL	3C,4D	1B	521206-7 ⁵
-	BLUE	1C,2C,3C,4D	1A,1B,2A,3B,4A,4B	⁴ 521206-6
04-C	BLUE	4D	1A,4B	⁴ 521206-5
-	BLUE	NONE	NONE	⁴ 521206-4
-	NATURAL	3C,4D	1B	⁶ 521206-3
-	BLUE	NONE	NONE	⁴ 521206-2 ³
04-A	BLUE	3C,4D	1B	521206-1
RAST CONFIGURATION	FINISH/COLOR	KEYING FEATURE	POLARIZATION FEATURE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
NYLON

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.25 [.010]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

SEE TABLE

APVD
E HOWARD
10/20/98

PRODUCT SPEC
APPLICATION SPEC

WEIGHT
-

CUSTOMER DRAWING

DWN
JR RUTH
10/20/98

CHK
MS FEHER
10/20/98

APVD
E HOWARD
10/20/98

NAME
HOUSING, RECEPT, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES, 4 POSITION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=521206

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
G

TE Connectivity

521206