




PANDUIT PART NO.	DIMENSIONS			
	'A'	'B' (REF)	'C'	'D'
HBN.75	0.075 (1.905)	1.40 (35.56)	0.62 (15.75)	0.75 (19.05)
HBN1		1.65 (41.91)		1.00 (25.4)
HBN1.5	0.084 (2.134)	2.16 (54.86)		1.50 (38.1)
HBN2	0.093 (2.362)	2.66 (67.56)		2.00 (50.8)
HBN2.5	0.107 (2.718)	3.16 (80.26)		2.50 (63.5)
HBN3	0.122 (3.099)	3.67 (93.22)		3.00 (76.2)
HBN4	0.142 (3.607)	4.67 (118.62)		4.00 (101.6)

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS, PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239KB_PB_HBN_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

HBN - HARNESS BOARD NAIL

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:(.XX) $\pm$ 0.100
(2.54)(.XXX) $\pm$ 0.010 (0.25)
ANGLES $\pm$ 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN

IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

JAD

MAT'L:

NICKEL PLATED
STEEL

SCALE

NONE

DATE

4/10/03

CHK'D

DRAWING NO.

GB0239KB

DWG

A
SIZE

I	2/28/06	JAD		MODIFY TOL FOR .XX DIM'S--WAS 0.06 REVISED DIM 'B' ALL P/N'S	GB0239KB	I			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	