


Size D



as per DIN 41 612



Dimensional drawings

Male connector

Female connector



① connectors for dip soldering are available with terminations of 1x1mm or 0.6x0.6. Wire-wrap terminations 1x1mm.

Ordering details

Male connector size D

as per DIN 41 612, maximum two rows loaded, maximum 32 contacts

STV-D 32-M-ac 2,4,6...32			
	PBT	533 210*	533 410
	PC	563 024	563 025

STV-D 32-M-ac 2,4,6...32			
Termination cross section 1x1mm			
	101	201	
	PC	563 021	

* German MIL approval can be found on page 3.

Male connectors with early make/last break contacts can be loaded in any position.

Further versions on request.

Female connector size D

as per DIN 41 612, maximum three rows loaded, maximum 32 contacts

STV-D 32-F-ac 2,4,6...32			
	107	207	
	PBT	594 566*	594 567

STV-D 32-F-ac 2,4,6...32			
Termination cross section 0,6x2,0mm for solder eyelet			
	107	207	
	PBT		033 426

STV-D 32-F-ac 2,4,6...32			
Termination cross section 1x1mm			
	107	207	
	PBT	594 569*	594 570

STV-D 32-F-ac 2,4,6...32			
Termination cross section 0,6x0,6mm			
	107	207	
	PBT		033 428

STV-D 32-F-ac 2,4,6...32			
Termination cross section 1,2x0,6mm			
	107	207	
	PBT		033 579

*German MIL approval can be found on page 3.

Female connector size D

as per DIN 41 612 with gold plated transfer zone ①

STV-D 32-F-ac UE ① 2,4,6...32			
Termination cross section 1x1mm transfer zone 1x0,6mm			
	101	201	
	PBT	594 445	314 409

① Entire length of contacts nickel-plated, transfer zone (5mm) solid-gold plated.

Further versions on request.

<u>Part-No.</u>	<u>Page</u>
033426	2
033428	2
033579	2
314409	2
533210	2
533410	2
563021	2
563024	2
563025	2
594445	2
594566	2
594567	2
594569	2
594570	2