



Surface Mount Common Mode Choke (8 Chokes, 16 Data Lines)

Electrical Specifications at 25° C


Part Number	Pri. Ind. OCL, Min. (μH)	DCR Max. (Ω)	Hi-Pot Min. V _{RMS}	Common Mode Attenuation (dB)							
				100k	1M	10M	30M	50M	100M	300M	500M
F-1921HV	47	0.3	2000	3	20	33	37	35	27	9	4

Operating Temperature Range: 0 °C to +70 °C

P/N F-1921V
Schematic Diagram



40-Pin 50-mil
SMD Package



RHOMBUS P/N: F-1921HV

CUST P/N:

NAME:

DATE: 1/17/2001

SHEET: 1 OF 1