


FEATURES

Non-Polarized
24 Volt DC Operation
12V AC or DC Operation
CRI ≥ 80 (WW)
 ≥ 70 (CW)



SPECIFICATIONS

PARAMETERS	SYMBOL	VALUES			UNIT
		MIN	TYP	MAX	
Input Voltage	Vin	10	12	30	VDC
Input Current (Bright)	Iin	0.02	0.05	0.07	A
Power Consumption (MAX)	P	0.6			W
CRI	Ra	≥ 80 (Warm White) / ≥ 70 (Cool White)			
Product Life	H	50000			Hr
CCT	- -	3000 (Warm White) / 6000 (Cool White)			K
Lumunous Flux (MAX)	Φ	55-65 (Warm White) 65-75 (Cool White)			Lm
Operating Temperature	Topr	-20	25	40	°C

ACCESSORIES

SOCKET: 2910F-47

JKL PART NUMBERS: LE-3042-02-CW and LE-3042-02-WW

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/-		JKL COMPONENTS CORPORATION TITLE NON-POLARIZED 360 DEGREES LED FESTOON LAMP				
A	ADD FEATURES/ACCESS, CHNG SPEC		11/4/13	DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.	LE-3042-02 MULTI	
	RELEASED		10/8/13	L. WENGSTROM		L.R.	11/4/13	A	55335		
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET
							NONE	10/8/13	11/4/13	A	1 OF 1