

181-32006

Slotted Wall Wiring Duct, 3" X 2", Non-Adhesive, PVC, Gray, 120ft/Carton

Article Number: 181-32006

Part Number: 181-32006

Type: SL3X2



[Find a Distributor](#)

[Order Samples](#)


[Get Technical Drawings](#)

[Share](#)

Base Data

Part No.	181-32006
Type	SL3X2
Color	Gray (GY)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection

Product Dimensions



Length (L)	6.0ft / 1.83m
Width (W) (imperial)	3.03"
Width (W)	76.96mm
Width (W2)	3.0" / 76.2mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	1.62" / 41.1mm
Width (W6)	1.0" / 25.4mm
Height (H)	2.0" / 50.8mm
Mounting Hole Centers	4.00" / 101.6mm



➡ **Material and Specifications**

Material Polyvinylchloride (PVC)

CSA Certified Yes

Flammability self-extinguishing

Material Specification RoHS

Operating Temperature +122 °F (+50 °C)

Specification UL / CSA

UL Listed (US and Canada) No

UL Recognized (US and Canada) No / Yes

➡ **Logistic and Packaging**

Packaging Type carton

Pkg. Qty. 120ft / 36.6m

Carton Qty. 120

UPC 089306295211

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)

[Home](#) | [About HellermannTyton](#) | [Products](#) | [Careers](#) | [Contact](#) | [Terms](#)

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001](#) Certified
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512