

Cable - CABLE-KS50/KS50/20M/YUC/CS - 2904421

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 20.0 m

RoHS

Key Commercial Data

Packing unit	1 STK
Custom tariff number	85444290
Country of origin	China

Technical data

General

Nominal voltage U_N	30 V DC
Max. current carrying capacity per path	500 mA (up to 70°C ambient temperature)
Max. conductor resistance	0.16 Ω /m
Length of cable	20 m
Single wire, cross section	0.14 mm ²
Single wire, cross section [AWG]	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	11 mm
Shielding	yes
Outer sheath, material	PVC
External sheath, color	gray RAL 7035

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Cable - CABLE-KS50/KS50/20M/YUC/CS - 2904421

Technical data

Environmental conditions

Flame resistance	IEC 60332-3-22
Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	Against occasional splashes

Connector, module side

Connection name	Field level
Connection method	Yokogawa, KS compatible
Torque	0.5 Nm (Screw connection)
Number of connections	1
Number of positions	50

Connector, controller side

Connection name	Controller level
Connection method	Yokogawa, I/O cards compatible
Torque	0.5 Nm (Screw connection)
Number of connections	1
Number of positions	50

Supported controller

Controller	YOKOGAWA CS3000 CentumVP
- suitable I/O card	AAR145

Standards and Regulations

Resistance to oil	DIN VDE 0472 Part 803, test type B
Flame resistance	IEC 60332-3-22

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 6.0	27249205
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237

Cable - CABLE-KS50/KS50/20M/YUC/CS - 2904421

Classifications

ETIM

ETIM 4.0	EC000237
ETIM 5.0	EC000237

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620