


TINA-TAPE lenses for Golden/ Platinum & Dragon+ LEDs

OSRAM
www.osram.com



- Designed & optimized for Osram-os Golden Dragon+ series of LEDs
- Lens material optical grade PC with high UV and temperature resistance (130°C/220°F). Allows use of high current and temperature conditions
- Best available optical efficiency, over 90%, with an extremely good cutoff of light
- Fastening to heat sink with a PU foam adhesive tape of automotive grade (included)
- Compact dimensions 16.1 x 10.1 mm.

LENS TYPES


NAME	ORDERING CODE	FWHM Angle
Tina-0-Plus Real Spot	FA10886_Tina-0-Plus-RS	±5°
Tina-0-Plus Diffuser	FA10642_Tina-0-Plus-D	±6°
Tina-0-Plus Medium	FA10643_Tina-0-Plus-M	±14°
Tina-0-Plus Oval	FA11199_Tina-0-Plus-O	Coming soon

© Ledil Oy – PRELIMINARY - Subject to change without prior notice

MEASUREMENTS


TINA-0-Plus-RS

Relative Intensity of FA10886_Tina-0-Plus-RS



TINA-0-Plus-D


Relative Intensity of Tina-0+-D



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

TINA-0-Plus-M

Relative Intensity of Tina-0+-M




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001

2009-11-28

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice