


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		L	ECO-07-012860	24JUL2007	RB	MM

D


C

B

A



"AMP", PART NO. & DATE CODE INK STAMPED (WHITE OR HOT STAMP NO WHITE TAPE) IN THIS AREA. (SIDE OPTIONAL)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	15JUL75	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
		CHK	15JUL75			
		APVD	16JUL75	NAME		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
				APPLICATION SPEC		
				WEIGHT		
MATERIAL SEE CALL-OUT		FINISH SEE CALL-OUT		SIZE	CAGE CODE	DRAWING NO
				A2	00779	C=530677
				CUSTOMER DRAWING		
				SCALE	SHEET	REV
				5:1	1 of 2	L

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

- 1

.000015 MIN. GOLD OVER .000050 MIN. NICKEL IN CONTACT AREA
- 2

.000030 MIN. GOLD OVER .000050 MIN. NICKEL IN CONTACT AREA
- 3

ALL PARTS ASSEMBLED IN MEXICO MUST BE STAMPED "ASSY IN MEXICO"
THE WORD "MEXICO"CAN BE SUBSTITUTED ONLY WHERE PART SIZE
PROHIBITS STAMPING "ASSY IN MEXICO" INK STAMP COLOR WHITE OR HOT
STAMP (NO WHITE TAPE) 115—9009, APPROX. WHERE SHOWN, SIDE OPTIONAL.
- 4

MATTE TIN PLATED CONTACT TAILS

4	.437	8—530677—3	7.557	7.012	7.307	6.872	6.552	43	
4	.370	7—530677—4	3.189	2.644	2.939	2.504	2.184	15	
4	.370	7—530677—1	1.785	1.240	1.535	1.100	.780	6	
	.437	3—530677—3	7.557	7.012	7.307	6.872	6.552	43	1—530677—3
	.370	3—530677—2	5.217	4.672	4.967	4.532	4.212	28	1—530677—2
	.437	3—530677—1	7.713	7168	7.463	7.028	6.708	44	1—530677—1
	.437	3—530677—0	6.465	5.920	6.215	5.780	5.460	36	1—530677—0
	.437	2—530677—9	5.529	4.984	5.279	4.844	4.524	30	530677—9
	.370	2—530677—8	4.749	4.204	4.499	4.064	3.744	25	530677—8
	.370	2—530677—7	4.593	4.048	4.343	3.908	3.588	24	530677—7
	.370	2—530677—6	4.281	3.736	4.031	3.596	3.276	22	530677—6
	.370	2—530677—5	3.657	3.112	3.407	2.972	2.652	18	530677—5
	.370	2—530677—4	3.189	2.644	2.939	2.504	2.184	15	530677—4
	.370	2—530677—3	3.721	2.176	2.471	2.036	1.716	12	530677—3
	.370	2—530677—2	2.409	1.864	2.159	1.724	1.404	10	530677—2
	.370	2—530677—1	1.785	1.240	1.535	1.100	.780	6	530677—1
W	PART NO. 2		F	D	C	B	A	NO OF POSN.	1 PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN — 15JUL75

CHK — 15JUL75

APVD — 16JUL75

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± .005
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —

MATERIAL —

FINISH —

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT —

CUSTOMER DRAWING

15JUL75

15JUL75

16JUL75

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105—3608

NAME

HOUSING ASSY, LOW PROFILE EDGE
CONNECTOR. FLOW SOLDER POST FOR
.052 DIA. HOLE, .156 X .200 CENTERS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=530677

—

SCALE 5:1

SHEET 2 of 2

REV L