

プラスチック防水ハンドル

PLASTIC WATERPROOF HANDLES



AP-140
プラスチック製

特徴 Feature

- 防水タイプ(Oリング・シートパッキン使用)
- 亜鉛合金がインサートされております。
- 耐酸・耐絶縁性を必要とする扉に最適
- 左右兼用型
- Waterproof (using O-ring and sheet packing)
- Zinc alloy is inserted.
- Suitable for doors that require acid-resistance and insulation.
- For both left-hand and right-hand use.

仕様 • 材質: ABS樹脂

- 標準色: N7(グレー)
5Y7/1(アイボリー)

鍵番号: 2001

付属品: 大ナット・ビスセット(止め金用)・キー2本

用途 • 隧道用配分電盤

納期 • 標準在庫品

備考 • ダブルOリングの完全防水タイプも製作致します。
• 止め金は646~650ページの中からお選びください。

• マスターシステムの組込みが可能です。お問い合わせください。

• 常温でご使用ください。

• 施錠は錠前の構造上、鍵を押しながら回してください。

• 本製品の止め金取付け用ねじは、緩み防止のため「緩み防止剤」の塗布をお奨め致します。

• 緩み防止剤等、溶剤を使用する際は十分に検証を行ってください。

Specifications • Material: ABS resin

• Standard color: N7: Gray. 5Y7/1: Ivory

• Key No.: 2001

• Accessories: Two keys, large nut and screws (for stopper plate)

Specific use • Tunnel power/distribution boards

Remarks • Double-O-ring-fully-waterproof type is available.

• Select stopper plate on page 646 to 650.

• Incorporating master system is possible. Consult us.

• Use this product in normal temperatures.

• Due to the structure of the lock, the key must be pushed in as it is turned in order to release the lock.

• It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.

• Be sure to test adequately when using a solvent such as thread-locking fluid.




AP-140-1-1
N7



AP-140-2-1
5Y7/1

キーNo.2001
Key



Specific use

Remarks

• Double-O-ring-fully-waterproof type is available.

• Select stopper plate on page 646 to 650.

• Incorporating master system is possible. Consult us.


• Use this product in normal temperatures.

• Due to the structure of the lock, the key must be pushed in as it is turned in order to release the lock.

• It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.

• Be sure to test adequately when using a solvent such as thread-locking fluid.

パネル穴明け寸法 Panel drilling dimensions



商品番号 Product No.	RoHS 2D/3D	備考 Remarks	L ₁	L ₂	W ₁	W ₂	W ₃	(W ₄)	(H ₁)	H ₂	H ₃	H ₄	H ₅	P	ΦD ₁	ΦD ₂	ΦD ₃	(M)	最大適用板厚 Max. applicable panel thickness	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price	
																							数量 Quantity	単価 Price
AP-140-1-1-N7	● 2D/3D	鍵付き With lock	158	7	40	25	10	42	61	9	26	24	6	50	70	25	30	M24	9.5	520	00314	¥2,500	10個~	¥2,400
AP-140-1-1-5Y7/1	● 2D/3D	鍵なし Without lock																			01038		10個~	¥2,400
AP-140-1-2-N7	● 3D	鍵なし Without lock																			00316	¥1,700	10個~	¥1,632
AP-140-1-2-5Y7/1	● 3D	鍵なし Without lock																			01039	¥1,700	10個~	¥1,632
AP-140-2-1-N7	● 2D/3D	鍵付き With lock	122	6	32	20	8	32	55	7	31	20	4	40	60	23	27	M22	7	330	00318	¥2,250	20個~	¥2,160
AP-140-2-1-5Y7/1	● 2D/3D	鍵なし Without lock																			01040		20個~	¥2,160
AP-140-2-2-N7	● 3D	鍵なし Without lock																			00320	¥1,650	20個~	¥1,584
AP-140-2-2-5Y7/1	● 3D	鍵なし Without lock																			01041	¥1,650	20個~	¥1,584

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

ハンドル・取手
周辺機器

A

クレモン

ローラー
締り

特装密閉
ハンドル

フリーザー
密閉

平面
スイング

ギア式

平面
ハンドル

ポップ
ハンドル

リフト
ハンドル

アジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L型
ハンドル

T型
ハンドル

丸型
小型

押ボタン

取手

つまみ

止め金
ロッド棒

ジョイント
リンク

ワイヤ

18.01

TAKIGEN

総合 24

497