


# Ferrules UNINSULATED (INDUSTRIAL STANDARD)

Uninsulated ferrules <Tin-plated electrolytic copper>



DIN 46228, part 1, except #

| Model No.  | Applicable wire |     | Style | Dimensions (mm) |      |      |     |
|------------|-----------------|-----|-------|-----------------|------|------|-----|
|            | mm2             | AWG |       | L1              | D1   | S    | D2  |
| WE0.25-6 # | 0.25            | 24  | I     | 5               | 0.8  | 0.15 | 1.7 |
| WE0.5-10   | 0.50            | 20  | I     | 10              | 1.0  | 0.15 | 2.1 |
| WE0.75-10  | 0.75            | 18  | I     | 10              | 1.2  | 0.15 | 2.3 |
| WE1-10     | 1.00            | 18  | I     | 10              | 1.4  | 0.15 | 2.5 |
| WE1.5-10   | 1.50            | 16  | I     | 10              | 1.7  | 0.15 | 2.8 |
| WE2.5-10   | 2.50            | 14  | I     | 10              | 2.2  | 0.15 | 3.4 |
| WE4-12     | 4.00            | 12  | I     | 12              | 2.8  | 0.20 | 4.0 |
| WE6-15     | 6.00            | 10  | I     | 15              | 3.5  | 0.20 | 4.7 |
| WE10-15    | 10.0            | 8   | I     | 15              | 4.5  | 0.20 | 5.8 |
| WE16-15    | 16.0            | 6   | I     | 15              | 5.8  | 0.20 | 7.5 |
| WE25-15    | 25.0            | 4   | I     | 15              | 7.3  | 0.20 | 9.5 |
| WE35-18    | 35.0            | 2   | I     | 18              | 8.3  | 0.20 | 11  |
| WE50-22 #  | 50.0            | 1   | I     | 22              | 10.3 | 0.30 | 13  |

Note: 1) Style I - Suitable for Tri-rated cable, Style II - Standard  
2) Maximum operating temperature: + 105°C  
3) Delivery lead times may vary depending on the product. These products are **ONLY** available from the following JST affiliates;  
J.S.T. (U.K.) Ltd, J.S.T. Belgium N.V., J.S.T. India Liaison Office, and JST-SouthAfrica.com.