




DESCRIPTION: HIGH DENSITY VERTICAL HIGH PROFILE MACHINED



DIMENSIONS (IN.)				
No. OF PINS	A	B	C	D
15	1.214 [30.84]	0.984 [24.99]	0.405 [10.29]	0.090 [2.29]
26	1.545 [39.24]	1.312 [33.32]	0.765 [19.43]	0.090 [2.29]
44	2.087 [53.00]	1.852 [47.04]	1.305 [33.15]	0.090 [2.29]
62	2.728 [69.30]	2.500 [63.50]	1.948 [49.47]	0.095 [2.41]
78	2.638 [67.00]	2.406 [61.10]	1.805 [45.85]	0.095 [2.41]

4 ROWS

MATERIAL:

INSULATOR: PBT, UL94V-0, 230°C PROCESS TEMP.,
CHEMICAL RESISTANCE, COLOR - BLACK
SHELL: STEEL, NICKEL PLATED
CONTACT: PHOSPHOR BRONZE, GOLD PLATED

ELECTRICAL:

CURRENT RATING: 2 AMPS
DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC rms
INSULATION RESISTANCE: 5,000 MegOhms Min.
CONTACT RESISTANCE: 10 MilliOhms Max.
WORKING TEMPERATURE: -55°C TO +125°C






196-YYY-213LYY1

SERIES _____
POSITIONS _____
015
026
044
062
078
GENDER _____
2 = FEMALE
TERMINATION _____
1 = PC MOUNT
SHELL PLATING _____
3 = NICKEL PLATED
RoHS COMPLIANT (LOW TEMP. PROCESS) _____
HARDWARE OPTIONS _____
00 = 0.120" MOUNTING HOLE
03 = 4-40 HEX STANDOFFS
55 = 4-40 INSERTS
PLATING _____
1 = GOLD FLASH (ENTIRE CONTACT)
2 = 30u" GOLD PLATING

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 09-15-05		
		CHECKED:		DATE:		
NorComp			SCALE: 1 : 1	SHEET 1 OF 3		REV 7
			DWG NO. 196-YYY-213LYY1			

RoHS COMPLIANT



180 SERIES
HIGH DENSITY
VERTICAL

HOLE PATTERN SHOWN
ARE FOR FEMALE

* TYP. ON ALL SIZES


DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 10-29-01			
		CHECKED:		DATE:			
NorComp		SCALE: 2 : 1		SHEET 2 OF 3		REV 7	
		DWG NO. 196-YYY-213LYY1					


RoHS COMPLIANT

TOLERANCE:
ALL DIMENSIONS ARE ±0.010

55X 0.158" (BOARD SIDE)



03X 0.158" (BOARD SIDE) - 0.230" MATING SIDE



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

11-19-10

CHECKED:

DATE:

SCALE:

SHEET

OF

3

3

REV

7

DWG NO.

196-YYY-213LYY1

RoHS COMPLIANT

NorComp