


Dimensions: mm (In.)



Electrical Specifications:

- Rating: 50mA/12VDC
- Contact Resistance: 100m Ω max. initial
- Insulation Resistance: 100M Ω min. @ 100VDC
- Dielectric Strength: 250 VAC for 1 minute.
- LED: Voltage - 4.2 typ, 6V max.;
- Current - 15mA, Max.20mA

Mechanical Specifications:

- Bounce: 10m sec. max
- Operating Temperature: +10°C~+60°C
- Storage Temperature: -20°C~+70°C
- Operating Force: 250gf max.
- Travel: 0.3 $\pm$ 0.1mm
- Life: 300,000 cycles min.

Mouser Stock No.	Illuminated Button Color
107-LP12-3-EV	Yellow
107-LP12-5-EV	Red
107-LP12-7-EV	Green

Note:

- RoHS compliant and process compatible with 260° solder

Illuminated Pushbutton Switches
 107-LP12-3-EV, 107-LP12-5-EV, 107-LP12-7-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[107-LP12-7-EV](#) [107-LP12-5-EV](#) [107-LP12-3-EV](#)