

Coaxial Cable Connector 11_BNC-50-2-13/133_N

Description

Straight cable plug

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	crimped
Outer 2contact	crimped
Weight	0.0098 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

Related Documents

Outline drawing	DOU-00006215
Catalogue drawing	DOU-00006199
Assembly instruction	DOC-0000179123

Ordering Information

Bulk 100 pcs package	11_BNC-50-2-13/133_NH
Single package	11_BNC-50-2-13/133_NE

Additional Information

Suitable cables	RG_316/_U, ENVIROFLEX_316, RG_188_A/U, RG 174 /U
-----------------	--