







NOTES:

1. MATERIALS:
HOOD: PBT GF UL94 V-0 BLACK
FRONTSEALING: SILICONE VMQ BLUE
SCREW: STAINLESS STEEL
O-RING: NBR BLACK
2. TEMPERATURE RANGE: -30°C TO +90°C
3. RECOMMENDED TORQUE FOR SCREW:
35Ncm (3.1 in.LB)
MAX. TORQUE: 68Ncm (6 in.LB)
4. SINGLE PACKED

* COMPLETELY TIGHTENED

(1 : 1)



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance ± 0,3 unless otherw. specified			scale: 1,5:1 (1:1)			
				dim. in mm			material: SEE TABLE			
				date			name			
				drawn		07.02.2014	Heinrich		title: WATER RESISTANT D-SUB HOOD (b) 9 pos. with short screw 4-40UNC thread/ stainless steel	
				appd.		07.02.2014	Huether			
norm										
d-old				dwg no: 15K1A1153		DIN-A3 sh: 1				
b	A5061	07.02.2014	Heinrich							
a	Origin									
rev.		description	date	name			part no: (b) 15-004710			