

SUPER E-LINE

TABLE 3: HIGH CURRENT SUPER E-LINE TRANSISTORS (P_D=1.2 Watts)

This range of devices is rated at 1.2 Watts and offers extremely low saturation voltages coupled with high continuous and pulsed current capability. Typical application areas to benefit from these products are emergency lighting, lap top computer power supplies, automotive circuits and flash gun converters.

PART NO.	V _{CBO}	V _{CEO}	I _C	I _{CM}	V _{CE(sat)} max @			h _{FE} min @			h _{FE} min @			f _T typ @			PIN OUT 123
	V	V	A	A	V	I _C A	I _B mA		I _C A	V _{CE} V		I _C A	V _{CE} V		I _C mA		
NPN																	
ZTX858*	400	400	2	6	0.20	0.3	100	50	0.01	10	30	0.5	10	80	100	CBE	
ZTX857	330	300	3	10	0.25	3	600	100	0.5	10	15	2	10	80	100	CBE	
ZTX855	250	150	4	10	0.26	4	400	100	1.0	5	35	4	5	90	100	CBE	
ZTX853	200	100	4	10	0.20	4	400	100	2.0	2	20	10	2	130	100	CBE	
ZTX851	150	60	5	20	0.25	5	200	100	2.0	1	25	10	1	130	100	CBE	
ZTX849	80	30	5	20	0.22	5	200	100	1.0	1	30	20	1	100	100	CBE	
ZTX869	60	25	5	20	0.22	5	100	250	5.0	1	40	20	1	100	100	CBE	
PNP																	
ZTX958	-400	-400	-0.5	-1.5	-0.40	-0.5	-100	100	-0.5	-10	10	-1	-10	85	-100	CBE	
ZTX957	-330	-300	-1	-2	-0.20	-1	-300	100	-0.5	-10	90	-1	-10	85	-100	CBE	
ZTX956	-220	-200	-2	-5	-0.25	-2	-400	100	-1.0	-5	50	-2	-5	110	-100	CBE	
ZTX955	-180	-140	-3	-10	-0.33	-3	-300	100	-1.0	-5	75	-3	-5	110	-100	CBE	
ZTX953	-140	-100	-3.5	-10	-0.33	-4	-400	100	-1.0	-1	30	-4	-1	125	-100	CBE	
ZTX951	-100	-60	-4	-15	-0.30	-4	-400	100	-1.0	-1	10	-10	-1	120	-100	CBE	
ZTX949	-50	-30	-4.5	-20	-0.32	-5	-300	100	-1.0	-1	75	-5	-1	100	-100	CBE	
ZTX948	-40	-20	-4.5	-20	-0.31	-5	-300	100	-1.0	-1	15	-20	-1	80	-100	CBE	
ZTX968	-15	-12	-4.5	-20	-0.30	-5	-200	300	-0.5	-1	150	-10	-1	85	-100	CBE	

* Development Sample Data

TABLE 4: HIGH PERFORMANCE DARLINGTON TRANSISTORS (P_D= upto 1 Watt)

The devices shown in this table are designed for applications requiring very high current gain at current levels up to 1A and power dissipation upto 1 Watt. They are ideal for lamp, relay and solenoid drivers in wide ranging applications from dot matrix printers to harsh environments such as automotive circuits.

PART NO.	V _{CBO}	V _{CEO}	I _C	I _{CM}	V _{CE(sat)} max @			h _{FE} @			h _{FE} min @			f _T min @			PIN OUT 123
	V	V	A	A	V	I _C mA	I _B mA		I _C mA	V _{CE} V		I _C A	V _{CE} V		I _C mA		
NPN																	
ZTX601	180	160	1	4	1.2	1000	10	2K-100K	500	10	1K	1	10	150	100		CBE
ZTX601A	180	160	1	4	1.2	1000	10	2K-20K	500	10	1K	1	10	150	100		CBE
ZTX601B	180	160	1	4	1.2	1000	10	10K-100K	500	10	5K	1	10	150	100		CBE
FXT601B	180	160	1	4	1.2	1000	10	10K-100K	500	10	5K	1	10	150	100		BCE
ZTX600	160	140	1	4	1.2	1000	10	2K-100K	500	10	1K	1	10	150	100		CBE
ZTX600A	160	140	1	4	1.2	1000	10	2K-20K	500	10	1K	1	10	150	100		CBE
ZTX600B	160	140	1	4	1.2	1000	10	10K-100K	500	10	5K	1	10	150	100		CBE
ZTX605	140	120	1	4	1.5	1000	1	5K	500	5	0.5K	2	5	150	100		CBE
FXT605	140	120	1	4	1.5	1000	1	5K	500	5	0.5K	2	5	150	100		BCE
ZTX604	120	100	1	4	1.5	1000	1	5K	500	5	0.5K	2	5	150	100		CBE
ZTX614	120	100	0.8	2	1.25	800	8	5K	100	5	10K	0.5	5	-	-		CBE
FXT614	120	100	0.8	2	1.25	800	8	5K	100	5	10K	0.5	5	-	-		BCE
BC372P	100	100	1	2	1	250	0.25	8K	100	5	10K	0.25	5	100	100		CBE
ZTX603	100	80	1	4	1	1000	1	5K	500	5	0.5K	2	5	150	100		CBE
FXT603	100	80	1	4	1	1000	1	5K	500	5	0.5K	2	5	150	100		BCE
ZTX602	80	60	1	4	1	1000	1	5K	500	5	0.5K	2	5	150	100		CBE
BCX38A	80	60	0.8	2	1.25	800	8	0.5K	100	5	1K	0.5	5	-	-		CBE
BCX38B	80	60	0.8	2	1.25	800	8	2K	100	5	4K	0.5	5	-	-		CBE
BCX38C	80	60	0.8	2	1.25	800	8	5K	100	5	10K	0.5	5	-	-		CBE
FXT38C	80	60	0.8	2	1.25	800	8	5K	100	5	10K	0.5	5	-	-		BCE
2N6725	60	50	1	2	1	200	2	15K	500	5	4K	1	5	-	-		CBE
2N6724	50	40	1	2	1	200	2	15K	500	5	4K	1	5	-	-		CBE
PNP																	
ZTX705	-140	-120	-1	-4	-1.3	-1000	-1	3K	-100	-5	2K	-2	-5	160 [#]	-100		CBE
FXT705	-140	-120	-1	-4	-1.3	-1000	-1	3K	-100	-5	2K	-2	-5	160 [#]	-100		BCE
ZTX704	-120	-100	-1	-4	-1.3	-1000	-1	3K	-100	-5	2K	-2	-5	160 [#]	-100		CBE
FXT704	-120	-100	-1	-4	-1.3	-1000	-1	3K	-100	-5	2K	-2	-5	160 [#]	-100		BCE
ZTX712	-80	-60	-0.8	-2	-1.25	-800	-8	5K	-100	-5	10K	-0.5	-5	-	-		CBE
MPSA77P	-80	-60	-0.5	-2	-1.5	-100	-0.1	10K	-10	-5	10K	-0.1	-5	-	-		CBE

#Typical Values