

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0851000048](#)
Status: **Obsolete**
Description: 2.50mm (.098") Pitch Omnigrid Receptacle, Right Angle, 1 SU, 12 Circuits

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Backplane Connectors
Series	85100
Application	Daughtercard
Comments	Performance Level 1
Component Type	PCB Receptacle
Product Name	Omnigrid
Style	N/A

Physical

Circuits (Loaded)	12
Circuits (maximum)	35
Color - Resin	Gray
Durability (mating cycles max)	500
Flammability	94V-0
Keying to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Material - Resin	Polycarbonate
Number of Columns	N/A
Number of Pairs	N/A
Number of Rows	5
Orientation	Right Angle
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Pitch - Mating Interface	2.50mm (.098")
Plating min - Mating	2.032µm (80µ")
Plating min - Termination	0.203µm (8µ")
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	1A
Data Rate	N/A
Voltage - Maximum	750V

Material Info

Reference - Drawing Numbers

Product Specification	PS-851**-0005
Sales Drawing	SDA-85100-0***




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[85100Series](#)

This document was generated on 05/18/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION