



KERN HFB The professional alternative up to 600 kg with rear-facing second display



Available from July 2010

Superior display size
digit height 25 mm.
Bright backlight for easy reading of weight, even from a distance

High mobility
thanks to battery operation, compact construction and low weight, it is suitable for use in several locations (production, warehouse, dispatch department,...)

Radio remote control
standard. Range approx. 20 m. All functions (excl. ON/OFF) can be selected. WxDxH 48x10x95 mm, Batteries size AAA (2 x 1.5 V) included



Second display
on the rear, standard. For easy reading of the weight from both sides

Hook
with safety catch, revolving




STANDARD



Charge display
for integrated rechargeable battery pack, using LED

Rechargeable battery pack
internal, standard. Operating time approx. 40 h, charging time approx. 12 h with mains adapter

Data Hold function
the weight display can be "frozen" using the HOLD key, until the HOLD key is pressed again



Technical data:

Precision 0.2% from Max.

Permissible ambient temperature 0 ...+40 °C

Model	Weighing range Max kg	Read-out d g	Net weight kg	Housing size WxDxH mm	Dimensions				OPTION Certifi- cate KERN DKD
					A	B	C	D	
KERN					mm	mm	mm	mm	
HFB 150K50	150	50	2	163x126x159	26	25	358	390	963-129
HFB 300K100	300	100	2	163x126x159	26	25	358	390	963-129
HFB 600K200	600	200	2	163x126x159	26	25	358	390	963-130

100

Order Hotline: Go to back page of catalogue

KERN - Your DKD-Calibration Partner

issues DKD calibration certificates for balances and test weights in its own accredited laboratories. It is internationally valid.

KERN is a manufacturer of test weights in the international classes of accuracy E1, E2, F1, F2, M1, M2, M3, from 1 mg up to 2000 kg
DKD = German Calibration Service



Your KERN specialist dealer