

HG 4000 E**Getting heat to where it's needed**

The HG 4000 E has a smaller nozzle than the HG 5000 E and delivers up to 600 l of hot air straight to where it's needed. Fitted with the appropriate attachments (accessories), the HG 4000 E is ideal for welding plastics.

Features

- Fully electronic temperature and airflow control
- Intelligent motor and temperature control
- Temperature display showing selected and actual temperature
- Easy-to-read LED segment display
- Sturdy single-piece enclosure
- High-performance, long-life brushless motor
- Barrel shape for optimum stationary use

Settings

- Continuously adjustable airflow and temperature

Maintenance

- Easy-to-change heating element
- Power cord can be changed without taking enclosure apart

HG 4000 E

Prod. No.
Length / dia. (at knock guard)
Voltage

Output
Temperature
Display mode
Airflow regulation
Airflow rate
Delivery nozzle
Motor life
Heater life
Mains power cord
Weight (without power cord)
Accessories

350215
370 mm / 122 mm
230 V / 50 Hz
(other voltages also available)
1750 W
25 - 600° C
LED segment display
continuous
600 l / min. max.
30 mm dia.
20 000 hrs.
approx. 500 – 800 hrs.
H07 RN-F 2 x 1
1115 g
Metal case

Prod. No.

350154
Subject to technical modifications



[print](#)—[close](#)—