

[Home](#)> [5710103F](#)

Search For

Part Number

Part Number: **5710103F**

General Description	
Series	571
Configuration	2 mm Lens
Description	2 mm Bi-Level CBI X-Y
Package Options	Bulk Packaging
Sizes	2mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Pin 1 & 3
Lens Style	Tinted, Diffused
Viewing Angle	70
LED Centerline	2.54mm
Solder Temperature	260 for 5 secs

Absolute Maximum Ratings (Ta = 25)	
Operating Temperature	-40 to +85
Storage Temperature	-40 to +85

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Blank	Yellow
LED Type	Standard Efficiency	Standard Efficiency
Peak Wave Length		590
Luminous Intensity Min		5
Luminous Intensity Typical		8
Forward Voltage Typical		2.1
Forward Voltage Max		2.5
Power Dissipation Max		105mW



5710103F

[check stock](#)



[This is a RoHS Compliant Product](#)
[To learn more click here](#)