

# Wera Kraftform® Plus Series 300

With a multi-component Kraftform® handle for demanding applications.

## 335 Slotted Screwdriver



**Application:** For slotted screws  
**Blade:** Round, mat nickel  
**Tip:** DIN 5264-A, ISO 2380, Lasertip®  
**Handle:** Kraftform® with anti-roll protection, multi-component

| Code                      | mm  | mm  | mm  | mm  | mm  | mm    | mm     | mm | mm |
|---------------------------|-----|-----|-----|-----|-----|-------|--------|----|----|
| 05008006001 <sup>1)</sup> | 0,4 | 2,0 | 60  | 70  | 2,5 | 5/64" | 2 3/8" | 10 |    |
| 05110000001 <sup>1)</sup> | 0,4 | 2,5 | 60  | 70  | 2,5 | 3/32" | 2 3/8" | 10 |    |
| 05008007001 <sup>1)</sup> | 0,4 | 2,5 | 75  | 70  | 2,5 | 3/32" | 3"     | 10 |    |
| 05008008001 <sup>1)</sup> | 0,5 | 3,0 | 150 | 81  | 4,0 | 1/8"  | 6"     | 10 |    |
| 05008009001 <sup>1)</sup> | 0,5 | 3,0 | 200 | 81  | 4,0 | 1/8"  | 8"     | 10 |    |
| 05110001001 <sup>1)</sup> | 0,5 | 3,0 | 80  | 81  | 3,0 | 1/8"  | 3 1/8" | 10 |    |
| 05008015001               | 0,6 | 3,5 | 100 | 81  | 3,5 | 9/64" | 4"     | 10 |    |
| 05110002001               | 0,6 | 3,5 | 125 | 81  | 3,5 | 9/64" | 5"     | 10 |    |
| 05110003001               | 0,6 | 3,5 | 200 | 81  | 3,5 | 9/64" | 8"     | 5  |    |
| 05110004001               | 0,8 | 4,0 | 100 | 98  | 4,0 | 5/32" | 4"     | 10 |    |
| 05110005001               | 0,8 | 4,0 | 150 | 98  | 4,0 | 5/32" | 6"     | 10 |    |
| 05110006001               | 0,8 | 4,0 | 200 | 98  | 4,0 | 5/32" | 8"     | 5  |    |
| 05008027001 <sup>1)</sup> | 0,8 | 4,0 | 300 | 98  | 4,0 | 5/32" | 12"    | 2  |    |
| 05110007001               | 1,0 | 5,5 | 125 | 98  | 5,5 | 7/32" | 5"     | 10 |    |
| 05008055001               | 1,0 | 5,5 | 150 | 98  | 5,5 | 7/32" | 6"     | 10 |    |
| 05110008001               | 1,0 | 5,5 | 200 | 98  | 5,5 | 7/32" | 8"     | 5  |    |
| 05008060001 <sup>1)</sup> | 1,0 | 5,5 | 300 | 98  | 5,5 | 7/32" | 12"    | 2  |    |
| 05008061001               | 1,2 | 6,0 | 100 | 105 | 6,0 | 5/16" | 4"     | 10 |    |

<sup>1)</sup> without Lasertip®

## 334 Slotted Screwdriver



**Application:** For slotted screws  
**Blade:** Round, mat nickel  
**Tip:** DIN 5264-A, ISO 2380, Lasertip®  
**Handle:** Kraftform®, with anti-roll protection, multi component  
**Sizes:** 2.0 x 12.0; 2.5 x 14.0: material = Weralit® II, one component

| Code                        | mm  | mm   | mm  | mm  | mm   | mm     | mm  | mm | mm |
|-----------------------------|-----|------|-----|-----|------|--------|-----|----|----|
| 05007610001 <sup>1)</sup>   | 0,8 | 5,0  | 100 | 98  | 5,0  | 3/16"  | 4"  | 10 |    |
| 05007620001 <sup>1)</sup>   | 1,0 | 6,0  | 125 | 105 | 6,0  | 15/64" | 5"  | 10 |    |
| 05340330001                 | 1,0 | 6,0  | 150 | 105 | 6,0  | 1/4"   | 6"  | 10 |    |
| 05110010001                 | 1,2 | 6,5  | 150 | 105 | 6,0  | 1/4"   | 6"  | 10 |    |
| 05007621001                 | 1,2 | 7,0  | 150 | 105 | 7,0  | 9/32"  | 6"  | 5  |    |
| 05007635001 <sup>1)</sup>   | 1,2 | 7,0  | 150 | 105 | 7,0  | 9/32"  | 6"  | 10 |    |
| 05110011001                 | 1,2 | 8,0  | 175 | 112 | 7,0  | 5/16"  | 7"  | 5  |    |
| 05007640001                 | 1,2 | 8,0  | 175 | 112 | 7,0  | 5/16"  | 7"  | 5  |    |
| 05110104001                 | 1,6 | 10,0 | 200 | 112 | 9,0  | 3/8"   | 8"  | 5  |    |
| 05110105001 <sup>2)</sup>   | 2,0 | 12,0 | 250 | 117 | 10,0 | 1/2"   | 10" | 2  |    |
| 05018274001 <sup>2,3)</sup> | 2,5 | 14,0 | 250 | 117 | -    | 1/4"   | 8"  | 2  |    |

<sup>1)</sup> These sizes are not included in standard specifications.

<sup>2)</sup> without Lasertip®

<sup>3)</sup> Identical with item 932 A, pound-thru hexagon blade, impact cap, hexagon bolster.

## 334 SK Slotted Screwdriver



**Application:** For slotted screws  
**Blade:** Hexagonal, with bolster from 0,8 x 4,5, mat nickel  
**Tip:** DIN 5264-A, ISO 2380, Lasertip®  
**Handle:** Kraftform®, multi-component

| Code        | mm  | mm   | mm | mm | mm  | mm  | mm     | mm     | mm |
|-------------|-----|------|----|----|-----|-----|--------|--------|----|
| 05007670001 | 0,6 | 3,5  | 4  | 0  | 75  | 81  | 9/64"  | 3"     | 10 |
| 05007671001 | 0,8 | 4,0  | 4  | 0  | 90  | 81  | 5/32"  | 3 1/2" | 10 |
| 05007672001 | 0,8 | 4,5  | 5  | 8  | 90  | 98  | 0,178" | 3 1/2" | 10 |
| 05007673001 | 1,0 | 5,5  | 6  | 10 | 100 | 98  | 7/32"  | 4"     | 10 |
| 05007674001 | 1,2 | 6,5  | 6  | 10 | 125 | 105 | 1/4"   | 5"     | 10 |
| 05007675001 | 1,2 | 7,0  | 6  | 10 | 125 | 105 | 9/32"  | 5"     | 10 |
| 05007676001 | 1,6 | 9,0  | 8  | 13 | 150 | 112 | 11/32" | 6"     | 10 |
| 05007677001 | 1,6 | 10,0 | 8  | 13 | 175 | 112 | 3/8"   | 7"     | 5  |

## 378 B Slotted Screwdriver



**Application:** For slotted screws  
**Blade:** Square, mat nickel  
**Tip:** DIN 5264-A, ISO 2380, Black Point  
**Handle:** Kraftform®, with anti-roll protection, multi component; size: 2,5 x 14,0 x 225: material = Weralit® II, one-component

| Code        | mm  | mm   | mm | mm  | mm  | mm    | mm     | mm | mm |
|-------------|-----|------|----|-----|-----|-------|--------|----|----|
| 05110050001 | 0,8 | 4,0  | 4  | 75  | 98  | 5/32" | 3"     | 10 |    |
| 05110051001 | 1,0 | 5,5  | 5  | 100 | 98  | 7/32" | 4"     | 10 |    |
| 05110052001 | 1,2 | 6,5  | 6  | 125 | 105 | 1/4"  | 5"     | 10 |    |
| 05110053001 | 1,6 | 8,0  | 8  | 150 | 112 | 5/16" | 6"     | 10 |    |
| 05007355001 | 1,6 | 10,0 | 8  | 60  | 112 | 3/8"  | 2 3/8" | 5  |    |
| 05110054001 | 1,6 | 10,0 | 8  | 175 | 112 | 3/8"  | 7"     | 5  |    |
| 05110150001 | 1,6 | 10,0 | 8  | 200 | 112 | 3/8"  | 8"     | 5  |    |
| 05007360001 | 1,6 | 10,0 | 8  | 600 | 112 | 3/8"  | 24"    | 5  |    |
| 05110055001 | 2,0 | 12,0 | 10 | 200 | 112 | 1/2"  | 8"     | 5  |    |
| 05110151001 | 2,0 | 12,0 | 10 | 250 | 112 | 1/2"  | 10"    | 5  |    |
| 05110056001 | 2,5 | 14,0 | 12 | 225 | 117 | 9/16" | 9"     | 2  |    |