

Patch cable - FL CAT5 PATCH 2,0 - 2832289

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Patch cable, CAT5, assembled, 2 m



RoHS

Ethernet

Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 044011
GTIN	4046356044011

Technical data

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

External sheath

Outer sheath, material	LSFROH
External diameter	5.5 mm
External diameter max.	6.2 mm

Single wire

Individual wires per module	8
Single wire, material	Cu litz wire
Single wire, cross section	0.14 mm ²

Mechanical properties

Smallest bending radius, fixed installation	30 mm
---	-------

General

Conductor length	2 m
Nominal voltage U _N	150 V _{rms}
Transmission characteristics (category)	CAT5

Patch cable - FL CAT5 PATCH 2,0 - 2832289

Technical data

Behavior in fire

Flame resistance	according to IEC 60332-3C
Concentration of fumes	in accordance with IEC 61034
Halogen-free	According to IEC 60754-1

Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Halogen-free	According to IEC 60754-1
Flame resistance	according to IEC 60332-3C

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>