


Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: 1A/250VAC, 3A/120VAC or 28VDC
- Contact Resistance: 20mΩmax. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩmin.
- Dielectric Strength: 1,000 V RMS@ sea level

Mechanical Specifications:

- Mechanical Life: 60,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Materials:

- Case: Dialyl phthalate (DAP)
- Plunger: Thermoplastic Polyester-black
- Bushing: Brass, nickel plated
- Housing: Stainless steel
- Terminal Support: Brass, tin plated
- Contact: Brass, with Silver or gold plated
- Terminal: Brass, silver plated

Note:

- RoHS compliant by exemption

Sub-Miniature Pushbutton Switch

107-3022-EVX

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[107-3022-EVX](#)