

| REV. | DESCRIPTION | DATE       |
|------|-------------|------------|
| A    | RELEASE     | 2012.11.12 |

RoHS

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: TIN, 80-100 $\mu$ "

Contact Material: Brass




Current Rating : 1A AC,DC

Contact Resistance: 20M $\Omega$  Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000M $\Omega$  Min.

Operating Temp.: -40°C~+105°C



| NUMBER<br>OF POSITIONS | DIMENSION |       |       |
|------------------------|-----------|-------|-------|
|                        | A         | B     | C     |
| 06                     | 26.92     | 5.08  | 22.86 |
| 08                     | 29.46     | 7.62  | 25.40 |
| 10                     | 32.00     | 10.16 | 27.94 |
| 12                     | 34.54     | 12.70 | 30.48 |
| 14                     | 37.08     | 15.24 | 33.02 |
| 16                     | 39.62     | 17.78 | 35.56 |
| 20                     | 44.70     | 22.86 | 40.64 |
| 24                     | 49.78     | 27.94 | 45.72 |
| 26                     | 52.32     | 30.48 | 48.26 |
| 30                     | 57.40     | 35.56 | 53.34 |
| 34                     | 62.48     | 40.64 | 58.42 |
| 40                     | 70.10     | 48.26 | 66.04 |
| 50                     | 82.80     | 60.96 | 78.74 |
| 60                     | 95.50     | 73.66 | 91.44 |
| 64                     | 100.58    | 78.74 | 96.52 |

UNLESS TOLERANCE

| GENERAL     | ANGLE        |
|-------------|--------------|
| X. ± 0.30   | X.° ± 3.0°   |
| .X ± 0.20   | .X° ± 2.0°   |
| .XX ± 0.15  | .XX° ± 1.0°  |
| .XXX ± 0.08 | .XXX° ± 0.5° |

|            |  |
|------------|--|
| DRAW BY    |  |
| DESIGN BY  |  |
| CHECK BY   |  |
| APPROVE BY |  |

CnC Tech,LLC

Part NO.

3010-XX-002-12-99



|       |       |      |
|-------|-------|------|
| SCALE | SHEET | UNIT |
| 1:1   | 1/1   | MM   |

DRW NO:

REV: A