




REV. 0
DCO 17157


COIL: @ 25°C
 RESISTANCE 700 OHMS ±10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 13.5 VDC
 MUST RELEASE 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX.
 CONTACT BOUNCE 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 2A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. BSH 07/18/01

CK.TLG 7-18-01

CII Technologies
 advanced control electronic solutions

CUST. C.I.I.
 CUST. NO. STANDARD REV.

"HFW" RELAY

HFW1230K00