


# New 'PLUG-IN' **UNI-LITE**



## Money Saving Rechargeable Lantern Battery



**Simply Plug In  
And Re-charge**


**Can be charged up to 1500 times  
Costs only 0.5 pence per charge**

### Specification and instructions

- Rechargeable lantern battery plugs directly into any standard mains domestic socket.
- No separate mains charger required.
- Plug rechargeable lantern battery into any standard mains domestic socket to begin charging.
- Charging time approx 10 hours - when battery is fully charged unplug and fit into any lantern / torch that uses a PJ996 (4R25) 'disposable' lantern battery.
- Red LED is charging indicator- which remains on when charging.
- This lantern battery is short circuit protected.
- Charging current control to prevent over charging.
- Ensure battery is completely dry before charging.
- Do not attempt to recharge this battery if it has been subjected to damage or shock.
- No attempt should be made to repair or open this sealed battery, there are no serviceable user parts inside.
- This battery may become warm when charging, this is quite normal.
- The UK300 is designed for indoor use and should not be exposed to extreme conditions and damp.
- Do not under any circumstances incinerate this battery.
- This battery can be stored in any state of recharge.
- For best performance it is recommended that you charge this battery before use.
- This is a Nickel Cadmium battery 4.8v 2000 (mAh) Input 230volts -50Hz output 6.3 volts-180 mA

**Plug-in  
and  
recharge**

**Inside  
lantern  
body**



**Battery  
position  
inside  
lantern**

**PAT PENDING and  
DESIGN COPYRIGHT**

**UNI-LITE INTERNATIONAL Ltd**  
7 Colemeadow Road North Moons Moat Redditch  
Worcestershire B98 9PB England  
Tel 01527 584344 Fax 01527 584345

**Conforms to: BS EN 60335-1:1995 & BS EN 60335-2-29:1997 BS1363 part 3:1995**



Double insulated



Do not dispose of in refuse bin  
Do not incinerate this battery is re-cyclable

Please retain these instructions  
for future reference

**UK300**