

A-42228-0213/0246						A-42228-0248/0281					
HEADER NUMBER:		41411				HEADER NUMBER:		41411			
PLATING:		154				PLATING:		208			
PIN LENGTH: L		.705/17.91				PIN LENGTH: L		.705/17.91			
MATING LENGTH: M		.295/7.49				MATING LENGTH: M		.295/7.49			
GOLD POINT: G		N/A				GOLD POINT: G		.140/3.56			
PC TAIL LENGTH: P		.120/3.05				PC TAIL LENGTH: P		.120/3.05			
TIN: T		OVERALL				TIN: T		.135/3.43			
DIMENSION Y		.022/0.56				DIMENSION Y		.022/0.56			
CKTS:		3-36				CKTS:		3-36			
KINKS:		NO				KINKS:		NO			
REMOVED BACKWALLS:		YES				REMOVED BACKWALLS:		YES			
VOIDED CKTS:		NONE				VOIDED CKTS:		NONE			
PACKAGING:		BULK, PER PK-40873-0056				PACKAGING:		BULK, PER PK-40873-0056			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20	22-28-1206	A-42228-0230	02			20	22-28-1207	A-42228-0265
03	22-28-1036	A-42228-0213	21	22-28-1216	A-42228-0231	03	22-28-1037	A-42228-0248	21	22-28-1217	A-42228-0266
04	22-28-1046	A-42228-0214	22	22-28-1226	A-42228-0232	04	22-28-1047	A-42228-0249	22	22-28-1227	A-42228-0267
05	22-28-1056	A-42228-0215	23	22-28-1236	A-42228-0233	05	22-28-1057	A-42228-0250	23	22-28-1237	A-42228-0268
06	22-28-1066	A-42228-0216	24	22-28-1246	A-42228-0234	06	22-28-1067	A-42228-0251	24	22-28-1247	A-42228-0269
07	22-28-1076	A-42228-0217	25	22-28-1256	A-42228-0235	07	22-28-1077	A-42228-0252	25	22-28-1257	A-42228-0270
08	22-28-1086	A-42228-0218	26	22-28-1266	A-42228-0236	08	22-28-1087	A-42228-0253	26	22-28-1267	A-42228-0271
09	22-28-1096	A-42228-0219	27	22-28-1276	A-42228-0237	09	22-28-1097	A-42228-0254	27	22-28-1277	A-42228-0272
10	22-28-1106	A-42228-0220	28	22-28-1286	A-42228-0238	10	22-28-1107	A-42228-0255	28	22-28-1287	A-42228-0273
11	22-28-1116	A-42228-0221	29	22-28-1296	A-42228-0239	11	22-28-1117	A-42228-0256	29	22-28-1297	A-42228-0274
12	22-28-1126	A-42228-0222	30	22-28-1306	A-42228-0240	12	22-28-1127	A-42228-0257	30	22-28-1307	A-42228-0275
13	22-28-1136	A-42228-0223	31	22-28-1316	A-42228-0241	13	22-28-1137	A-42228-0258	31	22-28-1317	A-42228-0276
14	22-28-1146	A-42228-0224	32	22-28-1326	A-42228-0242	14	22-28-1147	A-42228-0259	32	22-28-1327	A-42228-0277
15	22-28-1156	A-42228-0225	33	22-28-1336	A-42228-0243	15	22-28-1157	A-42228-0260	33	22-28-1337	A-42228-0278
16	22-28-1166	A-42228-0226	34	22-28-1346	A-42228-0244	16	22-28-1167	A-42228-0261	34	22-28-1347	A-42228-0279
17	22-28-1176	A-42228-0227	35	22-28-1356	A-42228-0245	17	22-28-1177	A-42228-0262	35	22-28-1357	A-42228-0280
18	22-28-1186	A-42228-0228	36	22-28-1366	A-42228-0246	18	22-28-1187	A-42228-0263	36	22-28-1367	A-42228-0281
19	22-28-1196	A-42228-0229				19	22-28-1197	A-42228-0264			

REV:	<u>ECR/ECN INFORMATION</u>		<u>TITLE:</u>	<u>SHEET No.</u>
L5	EC No.	UCP2012-3374	.100 FRICTION LOCK BREAKAWAY HEADER ASSY.	- 2 -
	DATE	10/12/2012		
<u>DOCUMENT NUMBER:</u>		<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>	<u>APPROVED BY:</u>
SD- 42228 -002		MKIPPER	JBELL	FSMITH-ROEMER

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC

A-42228-0283/0316						A-42228-0318/0351					
HEADER NUMBER:		41411				HEADER NUMBER:		41411			
PLATING:		228				PLATING:		154			
PIN LENGTH: L		.705/17.91				PIN LENGTH: L		.720/18.29			
MATING LENGTH: M		.295/7.49				MATING LENGTH: M		.295/7.49			
GOLD POINT: G		.140/3.56				GOLD POINT: G		N/A			
PC TAIL LENGTH: P		.120/3.05				PC TAIL LENGTH: P		.135/3.43			
TIN: T		.135/3.43				TIN: T		OVERALL			
DIMENSION Y		.022/0.56				DIMENSION Y		.022/0.56			
CKTS:		3-36				CKTS:		3-36			
KINKS:		NO				KINKS:		YES SMES-42003			
REMOVED BACKWALLS:		YES				REMOVED BACKWALLS:		YES			
VOIDED CKTS:		NONE				VOIDED CKTS:		NONE			
PACKAGING:		BULK, PER PK-40873-0056				PACKAGING:		BULK, PER PK-40873-0056			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20	22-28-1208	A-42228-0300	02			20	22-28-1209	A-42228-0335
03	22-28-1038	A-42228-0283	21	22-28-1218	A-42228-0301	03	22-28-1039	A-42228-0318	21	22-28-1219	A-42228-0336
04	22-28-1048	A-42228-0284	22	22-28-1228	A-42228-0302	04	22-28-1049	A-42228-0319	22	22-28-1229	A-42228-0337
05	22-28-1058	A-42228-0285	23	22-28-1238	A-42228-0303	05	22-28-1059	A-42228-0320	23	22-28-1239	A-42228-0338
06	22-28-1068	A-42228-0286	24	22-28-1248	A-42228-0304	06	22-28-1069	A-42228-0321	24	22-28-1249	A-42228-0339
07	22-28-1078	A-42228-0287	25	22-28-1258	A-42228-0305	07	22-28-1079	A-42228-0322	25	22-28-1259	A-42228-0340
08	22-28-1088	A-42228-0288	26	22-28-1268	A-42228-0306	08	22-28-1089	A-42228-0323	26	22-28-1269	A-42228-0341
09	22-28-1098	A-42228-0289	27	22-28-1278	A-42228-0307	09	22-28-1099	A-42228-0324	27	22-28-1279	A-42228-0342
10	22-28-1108	A-42228-0290	28	22-28-1288	A-42228-0308	10	22-28-1109	A-42228-0325	28	22-28-1289	A-42228-0343
11	22-28-1118	A-42228-0291	29	22-28-1298	A-42228-0309	11	22-28-1119	A-42228-0326	29	22-28-1299	A-42228-0344
12	22-28-1128	A-42228-0292	30	22-28-1308	A-42228-0310	12	22-28-1129	A-42228-0327	30	22-28-1309	A-42228-0345
13	22-28-1138	A-42228-0293	31	22-28-1318	A-42228-0311	13	22-28-1139	A-42228-0328	31	22-28-1319	A-42228-0346
14	22-28-1148	A-42228-0294	32	22-28-1328	A-42228-0312	14	22-28-1149	A-42228-0329	32	22-28-1329	A-42228-0347
15	22-28-1158	A-42228-0295	33	22-28-1338	A-42228-0313	15	22-28-1159	A-42228-0330	33	22-28-1339	A-42228-0348
16	22-28-1168	A-42228-0296	34	22-28-1348	A-42228-0314	16	22-28-1169	A-42228-0331	34	22-28-1349	A-42228-0349
17	22-28-1178	A-42228-0297	35	22-28-1358	A-42228-0315	17	22-28-1179	A-42228-0332	35	22-28-1359	A-42228-0350
18	22-28-1188	A-42228-0298	36	22-28-1368	A-42228-0316	18	22-28-1189	A-42228-0333	36	22-28-1369	A-42228-0351
19	22-28-1198	A-42228-0299				19	22-28-1199	A-42228-0334			

REV:	<u>ECR/ECN INFORMATION</u>		<u>TITLE:</u>	<u>SHEET No.</u>
L5	EC No.	UCP2012-3374	.100 FRICTION LOCK BREAKAWAY HEADER ASSY.	- 3 -
	DATE	10/12/2012		
<u>DOCUMENT NUMBER:</u>		<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>	<u>APPROVED BY:</u>
SD- 42228 -002		MKIPPER	JBELL	FSMITH-ROEMER

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC

--

A-42228-0422/0454					
HEADER NUMBER:		41411			
PLATING:		228			
PIN LENGTH: L		.705/17.91			
MATING LENGTH: M		.295/7.49			
GOLD POINT: G		.140/3.56			
PC TAIL LENGTH: P		.120/3.05			
TIN: T		.135/3.43			
DIMENSION Y		.022/0.56			
CKTS:		3-36			
KINKS:		NO			
REMOVED BACKWALLS:		YES			
VOIDED CKTS:		3			
PACKAGING:		BULK, PER PK-40873-0056			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20		A-42228-0439
03		A-42228-0422	21		A-42228-0440
04	22-29-1041	A-42228-0423	22		A-42228-0441
05		A-42228-0424	23		A-42228-0442
06		A-42228-0425	24		A-42228-0443
07		A-42228-0426	25		A-42228-0444
08		A-42228-0427	26		A-42228-0445
09		A-42228-0428	27		A-42228-0446
10		A-42228-0429	28		A-42228-0447
11		A-42228-0430	29		A-42228-0448
12		A-42228-0431	30		A-42228-0449
13		A-42228-0432	31		A-42228-0450
14		A-42228-0433	32		A-42228-0451
15		A-42228-0434	33		A-42228-0452
16		A-42228-0435	34		A-42228-0453
17		A-42228-0436	35		A-42228-0454
18		A-42228-0437	36		A-42228-0455
19		A-42228-0438			

A-42228-0456/0490					
HEADER NUMBER:		41411			
PLATING:		208			
PIN LENGTH: L		.720/18.29			
MATING LENGTH: M		.295/7.49			
GOLD POINT: G		.140/3.56			
PC TAIL LENGTH: P		.135/3.43			
TIN: T		.135/3.43			
DIMENSION Y		.022/0.56			
CKTS:		2-36			
KINKS:		YES SMES-42003			
REMOVED BACKWALLS:		NO			
VOIDED CKTS:		2			
PACKAGING:		BULK, PER PK-40873-0056			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02		A-42228-0456	20	22-29-1204	A-42228-0474
03	22-29-1034	A-42228-0457	21	22-29-1214	A-42228-0475
04	22-29-1044	A-42228-0458	22	22-29-1224	A-42228-0476
05	22-29-1054	A-42228-0459	23	22-29-2234	A-42228-0477
06	22-29-1064	A-42228-0460	24	22-29-1244	A-42228-0478
07	22-29-1074	A-42228-0461	25	22-29-1254	A-42228-0479
08	22-29-1084	A-42228-0462	26	22-29-1264	A-42228-0480
09	22-29-1094	A-42228-0463	27	22-29-1274	A-42228-0481
10	22-29-1104	A-42228-0464	28	22-29-1284	A-42228-0482
11	22-29-1114	A-42228-0465	29	22-29-1294	A-42228-0483
12	22-29-1124	A-42228-0466	30	22-29-1304	A-42228-0484
13	22-29-1134	A-42228-0467	31	22-29-1314	A-42228-0485
14	22-29-1144	A-42228-0468	32	22-29-1324	A-42228-0486
15	22-29-1154	A-42228-0469	33	22-29-1334	A-42228-0487
16	22-29-1164	A-42228-0470	34	22-29-1344	A-42228-0488
17	22-29-1174	A-42228-0471	35	22-29-1354	A-42228-0489
18	22-29-1184	A-42228-0472	36	22-29-1364	A-42228-0490
19	22-29-1194	A-42228-0473			

L5	<u>REV:</u>	<u>ECR/ECN INFORMATION</u>	<u>TITLE:</u>	<u>SHEET No.</u>
		<u>EC No.</u> UCP2012-3374	.100 FRICTION LOCK BREAKAWAY HEADER ASSY.	- 4 -
		<u>DATE</u> 10/12/2012		
<u>DOCUMENT NUMBER:</u>		<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>	<u>APPROVED BY:</u>
SD- 42228 -002		MKIPPER	JBELL	FSMITH-ROEMER

--

A-42228-0491/0524					
HEADER NUMBER:		41411			
PLATING:		154			
PIN LENGTH: L		.720/18.29			
MATING LENGTH: M		.295/7.49			
GOLD POINT: G		N/A			
PC TAIL LENGTH: P		.135/3.43			
TIN: T		OVERALL			
DIMENSION Y		.022/0.56			
CKTS:		3-36			
KINKS:		YES SMES-43703-0000			
REMOVED BACKWALLS:		YES			
VOIDED CKTS:		NONE			
PACKAGING:		BULK, PER PK-40873-0056			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20		A-42228-0508
03		A-42228-0491	21		A-42228-0509
04		A-42228-0492	22		A-42228-0510
05	42228-0493	A-42228-0493	23		A-42228-0511
06	42228-0494	A-42228-0494	24		A-42228-0512
07	42228-0495	A-42228-0495	25		A-42228-0513
08		A-42228-0496	26		A-42228-0514
09		A-42228-0497	27		A-42228-0515
10		A-42228-0498	28		A-42228-0516
11	42228-0499	A-42228-0499	29		A-42228-0517
12		A-42228-0500	30		A-42228-0518
13		A-42228-0501	31		A-42228-0519
14		A-42228-0502	32		A-42228-0520
15		A-42228-0503	33		A-42228-0521
16		A-42228-0504	34		A-42228-0522
17		A-42228-0505	35		A-42228-0523
18		A-42228-0506	36		A-42228-0524
19		A-42228-0507			

A-42228-0525/0537					
HEADER NUMBER:		41411			
PLATING:		154			
PIN LENGTH: L		.720/18.29			
MATING LENGTH: M		.295/7.49			
GOLD POINT: G		N/A			
PC TAIL LENGTH: P		.135/3.43			
TIN: T		OVERALL			
DIMENSION Y		.022/0.56			
CKTS:		24-36			
KINKS:		YES SMES-42003			
REMOVED BACKWALLS:		NO			
VOIDED CKTS:		5, 7, 11,13,16, 20, 24			
PACKAGING:		BULK, PER PK-40873-0056			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20		
03			21		
04			22		
05			23		
06			24	42228-0525	A-42228-0525
07			25	42228-0526	A-42228-0526
08			26	42228-0527	A-42228-0527
09			27	42228-0528	A-42228-0528
10			28	42228-0529	A-42228-0529
11			29	42228-0530	A-42228-0530
12			30	42228-0531	A-42228-0531
13			31	42228-0532	A-42228-0532
14			32	42228-0533	A-42228-0533
15			33	42228-0534	A-42228-0534
16			34	42228-0535	A-42228-0535
17			35	42228-0536	A-42228-0536
18			36	42228-0537	A-42228-0537
19					

REV: L5	<u>ECR/ECN INFORMATION</u>		<u>TITLE:</u>		<u>SHEET No.</u>
	<u>EC No.</u> UCP2012-3374		.100 FRICTION LOCK BREAKAWAY HEADER ASSY.		- 5 -
	<u>DATE</u> 10/12/2012				
<u>DOCUMENT NUMBER:</u> SD- 42228 -002			<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL	<u>APPROVED BY:</u> FSMITH-ROEMER

--

A-42228-0538/0566					
HEADER NUMBER:		41411			
PLATING:		154			
PIN LENGTH: L		.720/18.29			
MATING LENGTH: M		.295/7.49			
GOLD POINT: G		N/A			
PC TAIL LENGTH: P		.135/3.43			
TIN: T		OVERALL			
DIMENSION Y		.022/0.56			
CKTS:		8-36			
KINKS:		YES SMES-42003			
REMOVED BACKWALLS:		NO			
VOIDED CKTS:		8			
PACKAGING:		BULK, PER PK-40873-0056			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20	42228-0550	A-42228-0550
03			21	42228-0551	A-42228-0551
04			22	42228-0552	A-42228-0552
05			23	42228-0553	A-42228-0553
06			24	42228-0554	A-42228-0554
07			25	42228-0555	A-42228-0555
08	42228-0538	A-42228-0538	26	42228-0556	A-42228-0556
09	42228-0539	A-42228-0539	27	42228-0557	A-42228-0557
10	42228-0540	A-42228-0540	28	42228-0558	A-42228-0558
11	42228-0541	A-42228-0541	29	42228-0559	A-42228-0559
12	42228-0542	A-42228-0542	30	42228-0560	A-42228-0560
13	42228-0543	A-42228-0543	31	42228-0561	A-42228-0561
14	42228-0544	A-42228-0544	32	42228-0562	A-42228-0562
15	42228-0545	A-42228-0545	33	42228-0563	A-42228-0563
16	42228-0546	A-42228-0546	34	42228-0564	A-42228-0564
17	42228-0547	A-42228-0547	35	42228-0565	A-42228-0565
18	42228-0548	A-42228-0548	36	42228-0566	A-42228-0566
19	42228-0549	A-42228-0549			

REV: L5	<u>ECR/ECN INFORMATION</u>		<u>TITLE:</u> .100 FRICTION LOCK BREAKAWAY HEADER ASSY.	<u>SHEET No.</u> - 6 -
	<u>EC No.</u>	UCP2012-3374		
	<u>DATE</u>	10/12/2012		
<u>DOCUMENT NUMBER:</u> SD- 42228 -002			<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL
			<u>APPROVED BY:</u> FSMITH-ROEMER	

A-42376-0002 / 0036											
HEADER NUMBER:		42312-0002/0036									
PIN NUMBER:		42663-BKA154									
PIN LENGTH: L		.600/15.24									
MATING LENGTH: M		.361/9.17									
GOLD POINT: G		N/A									
PIN HEIGHT: Y		.142/3.61									
PC TAIL LENGTH: P		.120/3.05									
TIN: T		OVERALL									
CKTS:		2-36									
KINKS:		NONE									
VOIDED CKTS:		NONE									
PACKAGING:		BULK PK-40873-0041									
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02	22-28-6020	42376-0002	20	22-28-6200	42376-0020						
03	22-28-6030	42376-0003	21	22-28-6210	42376-0021						
04	22-28-6040	42376-0004	22	22-28-6220	42376-0022						
05	22-28-6050	42376-0005	23	22-28-6230	42376-0023						
06	22-28-6060	42376-0006	24	22-28-6240	42376-0024						
07	22-28-6070	42376-0007	25	22-28-6250	42376-0025						
08	22-28-6080	42376-0008	26	22-28-6260	42376-0026						
09	22-28-6090	42376-0009	27	22-28-6270	42376-0027						
10	22-28-6100	42376-0010	28	22-28-6280	42376-0028						
11	22-28-6110	42376-0011	29	22-28-6290	42376-0029						
12	22-28-6120	42376-0012	30	22-28-6300	42376-0030						
13	22-28-6130	42376-0013	31	22-28-6310	42376-0031						
14	22-28-6140	42376-0014	32	22-28-6320	42376-0032						
15	22-28-6150	42376-0015	33	22-28-6330	42376-0033						
16	22-28-6160	42376-0016	34	22-28-6340	42376-0034						
17	22-28-6170	42376-0017	35	22-28-6350	42376-0035						
18	22-28-6180	42376-0018	36	22-28-6360	42376-0036						
19	22-28-6190	42376-0019									
A-42376-0037 / 0071											
HEADER NUMBER:		42312-0002/0036									
PIN NUMBER:		42663-BKB208									
PIN LENGTH: L		.600/15.24									
MATING LENGTH: M		.361/9.17									
GOLD POINT: G		.180/4.57									
PIN HEIGHT: Y		.142/3.61									
PC TAIL LENGTH: P		.120/3.05									
TIN: T		.135/3.43									
CKTS:		2-36									
KINKS:		NONE									
VOIDED CKTS:		NONE									
PACKAGING:		BULK PK-40873-0041									
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02	22-28-6022	42376-0037	20	22-28-6202	42376-0055						
03	22-28-6032	42376-0038	21	22-28-6212	42376-0056						
04	22-28-6042	42376-0039	22	22-28-6222	42376-0057						
05	22-28-6052	42376-0040	23	22-28-6232	42376-0058						
06	22-28-6062	42376-0041	24	22-28-6242	42376-0059						
07	22-28-6072	42376-0042	25	22-28-6252	42376-0060						
08	22-28-6082	42376-0043	26	22-28-6262	42376-0061						
09	22-28-6092	42376-0044	27	22-28-6272	42376-0062						
10	22-28-6102	42376-0045	28	22-28-6282	42376-0063						
11	22-28-6112	42376-0046	29	22-28-6292	42376-0064						
12	22-28-6122	42376-0047	30	22-28-6302	42376-0065						
13	22-28-6132	42376-0048	31	22-28-6312	42376-0066						
14	22-28-6142	42376-0049	32	22-28-6322	42376-0067						
15	22-28-6152	42376-0050	33	22-28-6332	42376-0068						
16	22-28-6162	42376-0051	34	22-28-6342	42376-0069						
17	22-28-6172	42376-0052	35	22-28-6352	42376-0070						
18	22-28-6182	42376-0053	36	22-28-6362	42376-0071						
19	22-28-6192	42376-0054									
REV:		ECR / ECN INFORMATION:			KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY					SHEET No.	
K16		EC No.: UCP2013-3732								- 2 -	
		DATE: 10/9/2013									
DOCUMENT NUMBER:					CREATED / REVISED BY:		CHECKED BY:		APPROVED BY:		
SD- 42376-001					MKIPPER		BANDERSON		FSMITH		
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

A-42376-0072 / 0106						A-42376-0107 / 0141					
HEADER NUMBER:		42312-0002/0036				HEADER NUMBER:		42312-0002/0036			
PIN NUMBER:		42663-BKB228				PIN NUMBER:		42663-CXA154			
PIN LENGTH: L		.600/15.24				PIN LENGTH: L		.750/19.05			
MATING LENGTH: M		.361/9.17				MATING LENGTH: M		.405/10.29			
GOLD POINT: G		.180/4.57				GOLD POINT: G		N/A			
PIN HEIGHT: Y		.142/3.61				PIN HEIGHT: Y		.248/6.30			
PC TAIL LENGTH: P		.120/3.05				PC TAIL LENGTH: P		.120/3.05			
TIN: T		.135/3.43				TIN: T		OVERALL			
CKTS:		2-36				CKTS:		2-36			
KINKS:		NONE				KINKS:		NONE			
VOIDED CKTS:		NONE				VOIDED CKTS:		NONE			
PACKAGING:		BULK PK-40873-0041				PACKAGING:		BULK PK-40873-0043			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02	22-28-6024	42376-0072	20	22-28-6204	42376-0090	02	22-28-6021	42376-0107	20	22-28-6201	42376-0125
03	22-28-6034	42376-0073	21	22-28-6214	42376-0091	03	22-28-6031	42376-0108	21	22-28-6211	42376-0126
04	22-28-6044	42376-0074	22	22-28-6224	42376-0092	04	22-28-6041	42376-0109	22	22-28-6221	42376-0127
05	22-28-6054	42376-0075	23	22-28-6234	42376-0093	05	22-28-6051	42376-0110	23	22-28-6231	42376-0128
06	22-28-6064	42376-0076	24	22-28-6244	42376-0094	06	22-28-6061	42376-0111	24	22-28-6241	42376-0129
07	22-28-6074	42376-0077	25	22-28-6254	42376-0095	07	22-28-6071	42376-0112	25	22-28-6251	42376-0130
08	22-28-6084	42376-0078	26	22-28-6264	42376-0096	08	22-28-6081	42376-0113	26	22-28-6261	42376-0131
09	22-28-6094	42376-0079	27	22-28-6274	42376-0097	09	22-28-6091	42376-0114	27	22-28-6271	42376-0132
10	22-28-6104	42376-0080	28	22-28-6284	42376-0098	10	22-28-6101	42376-0015	28	22-28-6281	42376-0133
11	22-28-6114	42376-0081	29	22-28-6294	42376-0099	11	22-28-6111	42376-0116	29	22-28-6291	42376-0134
12	22-28-6124	42376-0082	30	22-28-6304	42376-0100	12	22-28-6121	42376-0117	30	22-28-6301	42376-0135
13	22-28-6134	42376-0083	31	22-28-6314	42376-0101	13	22-28-6131	42376-0118	31	22-28-6311	42376-0136
14	22-28-6144	42376-0084	32	22-28-6324	42376-0102	14	22-28-6141	42376-0119	32	22-28-6321	42376-0137
15	22-28-6154	42376-0085	33	22-28-6334	42376-0103	15	22-28-6151	42376-0120	33	22-28-6331	42376-0138
16	22-28-6164	42376-0086	34	22-28-6344	42376-0104	16	22-28-6161	42376-0121	34	22-28-6341	42376-0139
17	22-28-6174	42376-0087	35	22-28-6354	42376-0105	17	22-28-6171	42376-0122	35	22-28-6351	42376-0140
18	22-28-6184	42376-0088	36	22-28-6364	42376-0106	18	22-28-6181	42376-0123	36	22-28-6361	42376-0141
19	22-28-6194	42376-0089				19	22-28-6191	42376-0124			
REV:		ECR / ECN INFORMATION:		TITLE:				SHEET No.			
K16		EC No.: UCP2013-3732		KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY				- 3 -			
		DATE: 10/9/2013									
DOCUMENT NUMBER:				CREATED / REVISED BY:		CHECKED BY:		APPROVED BY:			
SD- 42376-001				MKIPPER		BANDERSON		FSMITH			
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

A-42376-0142 / 0176						A-42376-0177 / 0211					
HEADER NUMBER:			42312-0002/0036			HEADER NUMBER:			42312-0002/0036		
PIN NUMBER:			42663-CXB208			PIN NUMBER:			42663-CXB228		
PIN LENGTH: L			.750/19.05			PIN LENGTH: L			.750/19.05		
MATING LENGTH: M			.405/10.29			MATING LENGTH: M			.405/10.29		
GOLD POINT: G			.180/4.57			GOLD POINT: G			.180/4.57		
PIN HEIGHT: Y			.248/6.30			PIN HEIGHT: Y			.248/6.30		
PC TAIL LENGTH: P			.120/3.05			PC TAIL LENGTH: P			.120/3.05		
TIN: T			.135/3.43			TIN: T			.135/3.43		
CKTS:			2-36			CKTS:			2-36		
KINKS:			NONE			KINKS:			NONE		
VOIDED CKTS:			NONE			VOIDED CKTS:			NONE		
PACKAGING:			BULK PK-40873-0043			PACKAGING:			BULK PK-40873-0043		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02	22-28-6023	42376-0142	20	22-28-6203	42376-0160	02	22-28-6025	42376-0177	20	22-28-6205	42376-0195
03	22-28-6033	42376-0143	21	22-28-6213	42376-0161	03	22-28-6035	42376-0178	21	22-28-6215	42376-0196
04	22-28-6043	42376-0144	22	22-28-6223	42376-0162	04	22-28-6045	42376-0179	22	22-28-6225	42376-0197
05	22-28-6053	42376-0145	23	22-28-6233	42376-0163	05	22-28-6055	42376-0180	23	22-28-6235	42376-0198
06	22-28-6063	42376-0146	24	22-28-6243	42376-0164	06	22-28-6065	42376-0181	24	22-28-6245	42376-0199
07	22-28-6073	42376-0147	25	22-28-6253	42376-0165	07	22-28-6075	42376-0182	25	22-28-6255	42376-0200
08	22-28-6083	42376-0148	26	22-28-6263	42376-0166	08	22-28-6085	42376-0183	26	22-28-6265	42376-0201
09	22-28-6093	42376-0149	27	22-28-6273	42376-0167	09	22-28-6095	42376-0184	27	22-28-6275	42376-0202
10	22-28-6103	42376-0150	28	22-28-6283	42376-0168	10	22-28-6105	42376-0185	28	22-28-6285	42376-0203
11	22-28-6113	42376-0151	29	22-28-6293	42376-0169	11	22-28-6115	42376-0186	29	22-28-6295	42376-0204
12	22-28-6123	42376-0152	30	22-28-6303	42376-0170	12	22-28-6125	42376-0187	30	22-28-6305	42376-0205
13	22-28-6133	42376-0153	31	22-28-6313	42376-0171	13	22-28-6135	42376-0188	31	22-28-6315	42376-0206
14	22-28-6143	42376-0154	32	22-28-6323	42376-0172	14	22-28-6145	42376-0189	32	22-28-6325	42376-0207
15	22-28-6153	42376-0155	33	22-28-6333	42376-0173	15	22-28-6155	42376-0190	33	22-28-6335	42376-0208
16	22-28-6163	42376-0156	34	22-28-6343	42376-0174	16	22-28-6165	42376-0191	34	22-28-6345	42376-0209
17	22-28-6173	42376-0157	35	22-28-6353	42376-0175	17	22-28-6175	42376-0192	35	22-28-6355	42376-0210
18	22-28-6183	42376-0158	36	22-28-6363	42376-0176	18	22-28-6185	42376-0193	36	22-28-6365	42376-0211
19	22-28-6193	42376-0159				19	22-28-6195	42376-0194			
REV:		ECR / ECN INFORMATION:		KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY						SHEET No.	
K16		EC No.: UCP2013-3732								- 4 -	
		DATE: 10/9/2013									
DOCUMENT NUMBER:				CREATED / REVISED BY:		CHECKED BY:		APPROVED BY:			
SD- 42376-001				MKIPPER		BANDERSON		FSMITH			
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

A-42376-0212 / 0246											
HEADER NUMBER:		42312-0002/0036									
PIN NUMBER:		42663-BNA154									
PIN LENGTH: L		.615/15.62									
MATING LENGTH: M		.361/9.17									
GOLD POINT: G		N/A									
PIN HEIGHT: Y		.142/3.61									
PC TAIL LENGTH: P		.135/3.43									
TIN: T		OVERALL									
CKTS:		2-36									
KINKS:		PER SMES-42003									
VOIDED CKTS:		NONE									
PACKAGING:		BULK PK-40873-0041									
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02	22-28-7020	42376-0212	20	22-28-7200	42376-0230						
03	22-28-7030	42376-0213	21	22-28-7210	42376-0231						
04	22-28-7040	42376-0214	22	22-28-7220	42376-0232						
05	22-28-7050	42376-0215	23	22-28-7230	42376-0233						
06	22-28-7060	42376-0216	24	22-28-7240	42376-0234						
07	22-28-7070	42376-0217	25	22-28-7250	42376-0235						
08	22-28-7080	42376-0218	26	22-28-7260	42376-0236						
09	22-28-7090	42376-0219	27	22-28-7270	42376-0237						
10	22-28-7100	42376-0220	28	22-28-7280	42376-0238						
11	22-28-7110	42376-0221	29	22-28-7290	42376-0239						
12	22-28-7120	42376-0222	30	22-28-7300	42376-0240						
13	22-28-7130	42376-0223	31	22-28-7310	42376-0241						
14	22-28-7140	42376-0224	32	22-28-7320	42376-0242						
15	22-28-7150	42376-0225	33	22-28-7330	42376-0243						
16	22-28-7160	42376-0226	34	22-28-7340	42376-0244						
17	22-28-7170	42376-0227	35	22-28-7350	42376-0245						
18	22-28-7180	42376-0228	36	22-28-7360	42376-0246						
19	22-28-7190	42376-0229									
REV:		ECR / ECN INFORMATION:		KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY						SHEET No.	
K16		EC No.: UCP2013-3732								- 5 -	
		DATE: 10/9/2013									
DOCUMENT NUMBER:				CREATED / REVISED BY:		CHECKED BY:		APPROVED BY:			
SD- 42376-001				MKIPPER		BANDERSON		FSMITH			
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

A-42376-0247 / 0281					
HEADER NUMBER:			42312-0002/0036		
PIN NUMBER:			42663-BNB208		
PIN LENGTH: L			.615/15.62		
MATING LENGTH: M			.361/9.17		
GOLD POINT: G			.180/4.57		
PIN HEIGHT: Y			.142/3.61		
PC TAIL LENGTH: P			.135/3.43		
TIN: T			.135/3.43		
CKTS:			2-36		
KINKS:			PER SMES-42003		
VOIDED CKTS:			NONE		
PACKAGING:			BULK PK-40873-0041		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02	22-28-7022	42376-0247	20	22-28-7202	42376-0265
03	22-28-7032	42376-0248	21	22-28-7212	42376-0266
04	22-28-7042	42376-0249	22	22-28-7222	42376-0267
05	22-28-7052	42376-0250	23	22-28-7232	42376-0268
06	22-28-7062	42376-0251	24	22-28-7242	42376-0269
07	22-28-7072	42376-0252	25	22-28-7252	42376-0270
08	22-28-7082	42376-0253	26	22-28-7262	42376-0271
09	22-28-7092	42376-0254	27	22-28-7272	42376-0272
10	22-28-7102	42376-0255	28	22-28-7282	42376-0273
11	22-28-7112	42376-0256	29	22-28-7292	42376-0274
12	22-28-7122	42376-0257	30	22-28-7302	42376-0275
13	22-28-7132	42376-0258	31	22-28-7312	42376-0276
14	22-28-7142	42376-0259	32	22-28-7322	42376-0277
15	22-28-7152	42376-0260	33	22-28-7332	42376-0278
16	22-28-7162	42376-0261	34	22-28-7342	42376-0279
17	22-28-7172	42376-0262	35	22-28-7352	42376-0280
18	22-28-7182	42376-0263	36	22-28-7362	42376-0281
19	22-28-7192	42376-0264			

A-42376-0282/ 0316						A-42376-0317 / 0351					
HEADER NUMBER:			42312-0002/0036			HEADER NUMBER:			42312-0002/0036		
PIN NUMBER:			42663-BNB228			PIN NUMBER:			42663-DAA154		
PIN LENGTH: L			.615/15.62			PIN LENGTH: L			.765/19.43		
MATING LENGTH: M			.361/9.17			MATING LENGTH: M			.405/10.29		
GOLD POINT: G			.180/4.57			GOLD POINT: G			N/A		
PIN HEIGHT: Y			.142/3.61			PIN HEIGHT: Y			.248/6.30		
PC TAIL LENGTH: P			.135/3.43			PC TAIL LENGTH: P			.135/3.43		
TIN: T			.135/3.43			TIN: T			OVERALL		
CKTS:			2-36			CKTS:			2-36		
KINKS:			PER SMES-42003			KINKS:			PER SMES-42003		
VOIDED CKTS:			NONE			VOIDED CKTS:			NONE		
PACKAGING:			BULK PK-40873-0041			PACKAGING:			BULK PK-40873-0043		
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02	22-28-7024	42376-0282	20	22-28-7204	42376-0300	02	22-28-7021	42376-0317	20	22-28-7201	42376-0335
03	22-28-7034	42376-0283	21	22-28-7214	42376-0301	03	22-28-7031	42376-0318	21	22-28-7211	42376-0336
04	22-28-7044	42376-0284	22	22-28-7224	42376-0302	04	22-28-7041	42376-0319	22	22-28-7221	42376-0337
05	22-28-7054	42376-0285	23	22-28-7234	42376-0303	05	22-28-7051	42376-0320	23	22-28-7231	42376-0338
06	22-28-7064	42376-0286	24	22-28-7244	42376-0304	06	22-28-7061	42376-0321	24	22-28-7241	42376-0339
07	22-28-7074	42376-0287	25	22-28-7254	42376-0305	07	22-28-7071	42376-0322	25	22-28-7251	42376-0340
08	22-28-7084	42376-0288	26	22-28-7264	42376-0306	08	22-28-7081	42376-0323	26	22-28-7261	42376-0341
09	22-28-7094	42376-0289	27	22-28-7274	42376-0307	09	22-28-7091	42376-0324	27	22-28-7271	42376-0342
10	22-28-7104	42376-0290	28	22-28-7284	42376-0308	10	22-28-7101	42376-0325	28	22-28-7281	42376-0343
11	22-28-7114	42376-0291	29	22-28-7294	42376-0309	11	22-28-7111	42376-0326	29	22-28-7291	42376-0344
12	22-28-7124	42376-0292	30	22-28-7304	42376-0310	12	22-28-7121	42376-0327	30	22-28-7301	42376-0345
13	22-28-7134	42376-0293	31	22-28-7314	42376-0311	13	22-28-7131	42376-0328	31	22-28-7311	42376-0346
14	22-28-7144	42376-0294	32	22-28-7324	42376-0312	14	22-28-7141	42376-0329	32	22-28-7321	42376-0347
15	22-28-7154	42376-0295	33	22-28-7334	42376-0313	15	22-28-7151	42376-0330	33	22-28-7331	42376-0348
16	22-28-7164	42376-0296	34	22-28-7344	42376-0314	16	22-28-7161	42376-0331	34	22-28-7341	42376-0349
17	22-28-7174	42376-0297	35	22-28-7354	42376-0315	17	22-28-7171	42376-0332	35	22-28-7351	42376-0350
18	22-28-7184	42376-0298	36	22-28-7364	42376-0316	18	22-28-7181	42376-0333	36	22-28-7361	42376-0351
19	22-28-7194	42376-0299				19	22-28-7191	42376-0334			
REV:		ECR / ECN INFORMATION:		KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY						<u>SHEET No.</u> - 6 -	
K16		EC No.: UCP2013-3732									
		DATE: 10/9/2013									
DOCUMENT NUMBER:				CREATED / REVISED BY:		CHECKED BY:		APPROVED BY:			
SD- 42376-001				MKIPPER		BANDERSON		FSMITH			
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

A-42376-0352 / 0386											
HEADER NUMBER:		42312-0002/0036									
PIN NUMBER:		42663-DAB208									
PIN LENGTH: L		.765/19.43									
MATING LENGTH: M		.405/10.29									
GOLD POINT: G		.180/4.57									
PIN HEIGHT: Y		.248/6.30									
PC TAIL LENGTH: P		.135/3.43									
TIN: T		.135/3.43									
CKTS:		2-36									
KINKS:		PER SMES-42003									
VOIDED CKTS:		NONE									
PACKAGING:		BULK PK-40873-0043									
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02	22-28-7023	42376-0352	20	22-28-7203	42376-0370						
03	22-28-7033	42376-0353	21	22-28-7213	42376-0371						
04	22-28-7043	42376-0354	22	22-28-7223	42376-0372						
05	22-28-7053	42376-0355	23	22-28-7233	42376-0373						
06	22-28-7063	42376-0356	24	22-28-7243	42376-0374						
07	22-28-7073	42376-0357	25	22-28-7253	42376-0375						
08	22-28-7083	42376-0358	26	22-28-7263	42376-0376						
09	22-28-7093	42376-0359	27	22-28-7273	42376-0377						
10	22-28-7103	42376-0360	28	22-28-7283	42376-0378						
11	22-28-7113	42376-0361	29	22-28-7293	42376-0379						
12	22-28-7123	42376-0362	30	22-28-7303	42376-0380						
13	22-28-7133	42376-0363	31	22-28-7313	42376-0381						
14	22-28-7143	42376-0364	32	22-28-7323	42376-0382						
15	22-28-7153	42376-0365	33	22-28-7333	42376-0383						
16	22-28-7163	42376-0366	34	22-28-7343	42376-0384						
17	22-28-7173	42376-0367	35	22-28-7353	42376-0385						
18	22-28-7183	42376-0368	36	22-28-7363	42376-0386						
19	22-28-7193	42376-0369									
REV:		ECR / ECN INFORMATION:			KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY					SHEET No.	
K16		EC No.: UCP2013-3732								- 7 -	
		DATE: 10/9/2013									
DOCUMENT NUMBER:					CREATED / REVISED BY:		CHECKED BY:		APPROVED BY:		
SD- 42376-001					MKIPPER		BANDERSON		FSMITH		
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

A-42376-0387 / 0421					
HEADER NUMBER:		42312-0002/0036			
PIN NUMBER:		42663-DAB228			
PIN LENGTH: L		.765/19.43			
MATING LENGTH: M		.405/10.29			
GOLD POINT: G		.180/4.57			
PIN HEIGHT: Y		.248/6.30			
PC TAIL LENGTH: P		.135/3.43			
TIN: T		.135/3.43			
CKTS:		2-36			
KINKS:		PER SMES-42003			
VOIDED CKTS:		NONE			
PACKAGING:		BULK PK-40873-0043			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02	22-28-7025	42376-0387	20	22-28-7205	42376-0405
03	22-28-7035	42376-0388	21	22-28-7215	42376-0406
04	22-28-7045	42376-0389	22	22-28-7225	42376-0407
05	22-28-7055	42376-0390	23	22-28-7235	42376-0408
06	22-28-7065	42376-0391	24	22-28-7245	42376-0409
07	22-28-7075	42376-0392	25	22-28-7255	42376-0410
08	22-28-7085	42376-0393	26	22-28-7265	42376-0411
09	22-28-7095	42376-0394	27	22-28-7275	42376-0412
10	22-28-7105	42376-0395	28	22-28-7285	42376-0413
11	22-28-7115	42376-0396	29	22-28-7295	42376-0414
12	22-28-7125	42376-0397	30	22-28-7305	42376-0415
13	22-28-7135	42376-0398	31	22-28-7315	42376-0416
14	22-28-7145	42376-0399	32	22-28-7325	42376-0417
15	22-28-7155	42376-0400	33	22-28-7335	42376-0418
16	22-28-7165	42376-0401	34	22-28-7345	42376-0419
17	22-28-7175	42376-0402	35	22-28-7355	42376-0420
18	22-28-7185	42376-0403	36	22-28-7365	42376-0421
19	22-28-7195	42376-0404			

A-42376-0422/0456				A-42376-0549/0581				A-42376-0582/0616			
HEADER NUMBER:		42312-0002/0036		HEADER NUMBER:		42312-0004/0036		HEADER NUMBER:		42312-0002/0036	
PIN NUMBER:		42663-ATA154		PIN NUMBER:		42663-DAA154		PIN NUMBER:		42663-DCA154	
PIN LENGTH: L		.530/13.46		PIN LENGTH: L		.765/19.43		PIN LENGTH: L		.775/19.69	
MATING LENGTH: M		.276/7.01		MATING LENGTH: M		.405/10.29		MATING LENGTH: M		.524/13.31	
GOLD POINT: G		N/A		GOLD POINT: G		N/A		GOLD POINT: G		N/A	
PIN HEIGHT: Y		.142/3.61		PIN HEIGHT: Y		.248/6.30		PIN HEIGHT: Y		.142/3.61	
PC TAIL LENGTH: P		.135/3.43		PC TAIL LENGTH: P		.135/3.43		PC TAIL LENGTH: P		.131/3.33	
TIN: T		OVERALL		TIN: T		OVERALL		TIN: T		OVERALL	
CKTS:		2-36		CKTS:		4-36		CKTS:		2-36	
KINKS:		PER SMES-42003		KINKS:		PER SMES-42003		KINKS:		NONE	
VOIDED CKTS:		NONE		VOIDED CKTS:		3		VOIDED CKTS:		NONE	
PACKAGING		PK-40873-0041		PACKAGING		BULK PK-40873-0043		PACKAGING		PK-40873-0043	
CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER	CKTS	MATERIAL NUMBER
02	42376-0422	20	42376-0440	02		20	42376-0565	02	42376-0582	20	42376-0600
03	42376-0423	21	42376-0441	03		21	42376-0566	03	42376-0583	21	42376-0601
04	42376-0424	22	42376-0442	04	42376-0549	22	42376-0567	04	42376-0584	22	42376-0602
05	42376-0425	23	42376-0443	05	42376-0550	23	42376-0568	05	42376-0585	23	42376-0603
06	42376-0426	24	42376-0444	06	42376-0551	24	42376-0569	06	42376-0586	24	42376-0604
07	42376-0427	25	42376-0445	07	42376-0552	25	42376-0570	07	42376-0587	25	42376-0605
08	42376-0428	26	42376-0446	08	42376-0553	26	42376-0571	08	42376-0588	26	42376-0606
09	42376-0429	27	42376-0447	09	42376-0554	27	42376-0572	09	42376-0589	27	42376-0607
10	42376-0430	28	42376-0448	10	42376-0555	28	42376-0573	10	42376-0590	28	42376-0608
11	42376-0431	29	42376-0449	11	42376-0556	29	42376-0574	11	42376-0591	29	42376-0609
12	42376-0432	30	42376-0450	12	42376-0557	30	42376-0575	12	42376-0592	30	42376-0610
13	42376-0433	31	42376-0451	13	42376-0558	31	42376-0576	13	42376-0593	31	42376-0611
14	42376-0434	32	42376-0452	14	42376-0559	32	42376-0577	14	42376-0594	32	42376-0612
15	42376-0435	33	42376-0453	15	42376-0560	33	42376-0578	15	42376-0595	33	42376-0613
16	42376-0436	34	42376-0454	16	42376-0561	34	42376-0579	16	42376-0596	34	42376-0614
17	42376-0437	35	42376-0455	17	42376-0562	35	42376-0580	17	42376-0597	35	42376-0615
18	42376-0438	36	42376-0456	18	42376-0563	36	42376-0581	18	42376-0598	36	42376-0616
19	42376-0439			19	42376-0564			19	42376-0599		

REV:	ECR / ECN INFORMATION:	TITLE:	SHEET No.
K16	EC No.: UCP2013-3732	KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY	- 8 -
	DATE: 10/9/2013		
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
SD- 42376-001	MKIPPER	BANDERSON	FSMITH

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC

42376-0683 / ----											
HEADER NUMBER:			42312-0002/0036								
PIN NUMBER:			42663-CTB208								
PIN LENGTH: L			.740/18.80								
MATING LENGTH: M			.405/10.29								
GOLD POINT: G			.180/4.57								
PIN HEIGHT: Y			.235/5.97								
PC TAIL LENGTH: P			.123/3.12								
TIN: T			.135/3.43								
CKTS:			2-36								
KINKS:			NONE								
VOIDED CKTS:			NONE								
PACKAGING:			BULK PK-40873-0041								
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02			20								
03			21								
04			22								
05			23								
06	423760687	42376-0687	24								
07			25								
08			26								
09			27								
10			28								
11			29								
12			30								
13			31								
14			32								
15			33								
16			34								
17			35								
18			36								
19											
42376-0718 / ----											
HEADER NUMBER:			42312-0002/0036								
PIN NUMBER:			42663-ANA154								
PIN LENGTH: L			.510/12.95								
MATING LENGTH: M			.175/4.45								
GOLD POINT: G			N/A								
PIN HEIGHT: Y			.248/6.30								
PC TAIL LENGTH: P			.100/2.54								
TIN: T			OVERALL								
CKTS:			2-36								
KINKS:			NONE								
VOIDED CKTS:			NONE								
PACKAGING:			BULK PK-40873-0041								
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02	423760718	42376-0718	20								
03			21								
04			22								
05			23								
06			24								
07			25								
08			26								
09			27								
10			28								
11			29								
12			30								
13			31								
14			32								
15			33								
16			34								
17			35								
18			36								
19											
REV:		ECR / ECN INFORMATION:			KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY					SHEET No.	
K16		EC No.: UCP2013-3732								- 9 -	
		DATE: 10/9/2013									
DOCUMENT NUMBER:					CREATED / REVISED BY:		CHECKED BY:		APPROVED BY:		
SD- 42376-001					MKIPPER		BANDERSON		FSMITH		
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

42376-0753 / 0787											
HEADER NUMBER:			42312-0002/0036								
PIN NUMBER:			42663-BBA154								
PIN LENGTH: L			.560/14.22								
MATING LENGTH: M			.208/5.28								
GOLD POINT: G			N/A								
PIN HEIGHT: Y			.248/6.30								
PC TAIL LENGTH: P			.120/3.05								
TIN: T			OVERALL								
CKTS:			2-36								
KINKS:			NONE								
VOIDED CKTS:			NONE								
PACKAGING:			BULK PK-40873-0041								
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02			20								
03			21								
04			22								
05	423760756	42376-0756	23								
06			24								
07			25								
08			26								
09			27	423760778	42376-0778						
10			28								
11			29	423760780	42376-0780						
12			30								
13			31								
14			32								
15			33								
16			34								
17			35								
18			36								
19											
42376-0788 / 0822											
HEADER NUMBER:			42312-0002/0036								
PIN NUMBER:			42663-DHA154								
PIN LENGTH: L			.800 / 20.32								
MATING LENGTH: M			.350 / 8.90								
GOLD POINT: G			N/A								
PIN HEIGHT: Y			.354 / 9.00								
PC TAIL LENGTH: P			.118 / 3.00								
TIN: T			OVERALL								
CKTS:			2-36								
KINKS:			NONE								
VOIDED CKTS:			NONE								
PACKAGING:			BULK PK-40873-0041								
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER						
02			20								
03			21								
04	423760790	42376-0790	22								
05			23								
06	423760792	42376-0792	24								
07			25								
08			26								
09			27								
10			28								
11			29								
12			30								
13			31								
14			32								
15			33								
16			34								
17			35								
18			36								
19											
REV:		ECR / ECN INFORMATION:			<u>TITLE:</u>					<u>SHEET No.</u>	
K16		<u>EC No.:</u> UCP2013-3732			KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY					- 10 -	
		<u>DATE:</u> 10/9/2013									
<u>DOCUMENT NUMBER:</u>					<u>CREATED / REVISED BY:</u>		<u>CHECKED BY:</u>		<u>APPROVED BY:</u>		
SD- 42376-001					MKIPPER		BANDERSON		FSMITH		
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC											

42376-0822 / 0856					
HEADER NUMBER:		42312-0002/0036			
PIN NUMBER:		42663-ATA154			
PIN LENGTH: L		.530/13.46			
MATING LENGTH: M		.198/5.03			
GOLD POINT: G		N/A			
PIN HEIGHT: Y		.235/5.97			
PC TAIL LENGTH: P		.120/3.05			
TIN: T		OVERALL			
CKTS:		2-36			
KINKS:		NONE			
VOIDED CKTS:		NONE			
PACKAGING:		BULK PK-40873-0041			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20		
03			21		
04			22		
05	423760825	42376-0825	23		
06			24		
07			25		
08			26		
09			27		
10			28		
11			29		
12			30		
13			31		
14			32		
15			33		
16			34		
17			35		
18			36		
19					

42376-0892 / 0926					
HEADER NUMBER:		42312-0002/0036			
PIN NUMBER:		42663-DYA154			
PIN LENGTH: L		.860/21.84			
MATING LENGTH: M		.649/16.48			
GOLD POINT: G		N/A			
PIN HEIGHT: Y		.142/3.61			
PC TAIL LENGTH: P		.093/2.35			
TIN: T		OVERALL			
CKTS:		2-36			
KINKS:		NONE			
VOIDED CKTS:		NONE			
PACKAGING:		BULK PK-40873-0041			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20		
03			21		
04			22		
05			23		
06			24		
07			25		
08	423760898	42376-0898	26		
09			27		
10			28		
11			29		
12			30		
13			31		
14			32		
15			33		
16			34		
17			35		
18			36		
19					

REV:	ECR / ECN INFORMATION:	<u>TITLE:</u>	SHEET No.
K16	EC No.: UCP2013-3732	KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY	- 11 -
	DATE: 10/9/2013		
<u>DOCUMENT NUMBER:</u>		<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>
SD- 42376-001		MKIPPER	BANDERSON
		<u>APPROVED BY:</u>	
		FSMITH	

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC

42376-0928						42376-0962					
HEADER NUMBER:		42312-0002/0036				HEADER NUMBER:		42312-0002/0036			
PIN NUMBER:		42663-0642				PIN NUMBER:		42663-0203			
PLATING:		197				PLATING:		208			
PIN LENGTH: L		.730/18.54				PIN LENGTH: L		.510/12.95			
MATING LENGTH: M		.501/12.72				MATING LENGTH: M		.164/4.17			
GOLD POINT: G		N/A				GOLD POINT: G		.140/3.56			
PIN HEIGHT: Y		.142/3.61				PIN HEIGHT: Y		.142/3.61			
PC TAIL LENGTH: P		.110/.280				PC TAIL LENGTH: P		.227/5.77			
TIN: T		OVERALL				TIN: T		.135/3.43			
CKTS:		2-36				CKTS:		2-36			
KINKS:		NONE				KINKS:		NONE			
VOIDED CKTS:		NONE				VOIDED CKTS:		NONE			
PACKAGING:		BULK PK-40873-0041				PACKAGING:		BULK PK-40873-0041			
CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER	CKTS	MATERIAL NUMBER	ENG NUMBER
02			20			02	42376-0962	42376-0962	20		
03	42376-0928	42376-0928	21			03			21		
04			22			04			22		
05			23			05			23		
06			24			06			24		
07			25			07			25		
08			26			08			26		
09			27			09			27		
10			28			10			28		
11			29			11			29		
12			30			12			30		
13			31			13			31		
14			32			14			32		
15			33			15			33		
16			34			16			34		
17			35			17			35		
18			36			18			36		
19						19					

REV:	ECR / ECN INFORMATION:	<u>TITLE:</u>	<u>SHEET No.</u>
K16	<u>EC No.:</u> UCP2013-3732 <u>DATE:</u> 10/9/2013	KK 100 HEADER ASSEMBLY FLAT RIGHT ANGLE BREAKAWAY	- 12 -
<u>DOCUMENT NUMBER:</u>		<u>CREATED / REVISED BY:</u>	<u>CHECKED BY:</u>
SD- 42376-001		MKIPPER	BANDERSON
		<u>APPROVED BY:</u>	
		FSMITH	

TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC