



General ordering data

Order No.	0282900000
Part designation	H10,0/12
Version	Wire-end ferrule, 10 mm²
EAN	4008190075972
Qty.	500 pc(s).

Technical data

Length	12 mm
Width	5.8 mm
Height	5.8 mm

Product data

Conductor rated cross-section	10 mm²
AWG	7
Total length (L1)	12 mm
Contact surface diameter (D1)	4.5 mm
Metal sleeve thickness (S1)	0.2 mm

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000005
ETIM 3.0	EC000005
eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01
eClass 5.1	27-40-02-01

Similar products

Order No.	Part designation	Version
0124800000	H10,0/15	Wire-end ferrule, 10 mm²
0379300000	H10,0/18	Wire-end ferrule, 10 mm²
0492500000	H16,0/12	Wire-end ferrule, 16 mm²
0124300000	H16,0/15	Wire-end ferrule, 16 mm²
0375200000	H16,0/18	Wire-end ferrule, 16 mm²
9004150000	H16,0/25	Wire-end ferrule, 16 mm²
9004160000	H16,0/32	Wire-end ferrule, 16 mm²
0124400000	H25,0/15	Wire-end ferrule, 25 mm²
0375300000	H25,0/18	Wire-end ferrule, 25 mm²

9004170000	H25,0/25	Wire-end ferrule, 25 mm ²
9004180000	H25,0/32	Wire-end ferrule, 25 mm ²
0368900000	H35,0/18	Wire-end ferrule, 35 mm ²
9004190000	H35,0/25	Wire-end ferrule, 35 mm ²
9451000000	H35,0/30S	Wire-end ferrule, 35 mm ²
9004200000	H35,0/32	Wire-end ferrule, 35 mm ²
9004210000	H50,0/18	Wire-end ferrule, 50 mm ²
9025880000	H50,0/25	Wire-end ferrule, 50 mm ²
9004220000	H50,0/32	Wire-end ferrule, 50 mm ²
9004230000	H70,0/25	Wire-end ferrule, 70 mm ²
9004240000	H70,0/32	Wire-end ferrule, 70 mm ²
9004250000	H95,0/25	Wire-end ferrule, 95 mm ²
9004260000	H95,0/32	Wire-end ferrule, 95 mm ²
9036240000	H120,0/32	Wire end ferrule, 120 mm ²
9036250000	H150,0/32	Wire end ferrule, 150 mm ²
9036260000	H185,0/32	Wire end ferrule, 185 mm ²