

Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-PV22-2R-CY P
- Part Drawings
- PDF-Ring Termina ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 Text Search: 'PV22-10R-CY'

Your search criteria matched only one product, shown below

PV22-10R-CY



- Insulation support helps to prevent wire damage in bending applications
 - Ring tongue design assures a secure connection in high vibration applications
 - Brazed seam protects terminal barrel from splitting during the crimp process
 - Internal barrel serrations assure good wire contact and maximum tensile strength
 - UL Flammability UL 94V-0, maximum insulation temperature 221 °F (105°C)
 - UL and CSA rated up 600 V per UL 486A/B, where applicable
- ‡UL and CSA approved tooling/product combinations.
Note: Wire sizes #26 – #22 AWG, are not UL Listed or

CSA Certified.

• Part Number	PV22-10R-CY
• RoHS Compliancy Status	Compliant
• Note	PV22-10R-CY replaces PV22-10R-C
• Part Description	Ring Terminal, 26 – 22 AWG, #10 stud size, vinyl insulated, funnel entry.
• Product Type	Terminals
• CSA Certified	No
• UL Listed	No
• Length (In.)	0.78
• Length (mm)	19.8
• Width (In.)	0.32
• Width (mm)	8.1
• CE Compliant	No
• Clearance	0.24
• Clearance (mm)	6.1
• Insulation	Vinyl
• Max. Ins.	0.110
• Max. Ins. (mm)	2.8
• Panduit Color Code	Yellow
• Plating Type	Tinned
• Pricing Description	Ring Terminal, vinyl insulated, 26 - 22 AWG, #10 stud size, funnel entry
• Stock	0.02
• Stock (mm)	0.5
• Stud Size	#10
• Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
• Tool	CT-600-A, CT-1525, CT-2500
• Wire Range	26 – 22 AWG
• Wire Range (mm²)	0.14 – 0.50
• Min. Order UOM	PC
• Min. Order Qty.	100
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.