






|   |          |   |               |       |                         |       |       |    |                  |                            |
|---|----------|---|---------------|-------|-------------------------|-------|-------|----|------------------|----------------------------|
| 7 | OBSOLETE | 6 | NONE          | NONE  | 50                      | 2.484 | 2.400 | 24 | 50               | 5-104232-3                 |
|   |          | 6 | NONE          | NONE  | 80                      | 3.984 | 3.900 | 39 | 80               | 5-104232-2                 |
| 7 | OBSOLETE | 5 | NONE          | NONE  | 50                      | 2.484 | 2.400 | 24 | 50               | 104232-3                   |
|   |          | 5 | NONE          | NONE  | 80                      | 3.984 | 3.900 | 39 | 80               | 104232-2                   |
|   | OBSOLETE | 5 | 10            | NONE  | 25                      | 1.284 | 1.200 | 12 | 26               | 104232-1                   |
|   |          |   | ROW X         | ROW Y | ACTIVE<br>NO OF<br>POSN | C     | B     | A  | NO<br>OF<br>POSN | ASSEMBLY<br>PART<br>NUMBER |
|   |          |   | POSTS OMITTED |       |                         |       |       |    |                  |                            |

|                                                                                                                                       |  |                                                                                                                            |  |                                                                                                        |  |
|---------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                                                |  | DWN 24-2-87<br>H MOLL<br>CHK 27-2-87<br>T. CLARK<br>APVD 27-2-87<br>T. CLARK<br>PRODUCT SPEC<br>—<br>APPLICATION SPEC<br>— |  |  TE Connectivity  |  |
| DIMENSIONS:<br>INCHES<br>                        |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± —<br>1 PLC ± —<br>2 PLC ± —<br>3 PLC ± .005<br>4 PLC ± —<br>ANGLES ± ± — |  | NAME<br>HEADER ASSY, MOD II, BREAKAWAY,<br>RIGHT ANGLE, DOUBLE ROW,<br>.100X.100 C/L, W/ .025 SQ POSTS |  |
| MATERIAL<br>HOUSING : GLASS FILLED THERMOPLASTIC<br>(THAT WILL WITHSTAND VAPOR PHASE REFLOW)<br>COLOR : BLACK<br>POSTS : COPPER ALLOY |  | FINISH<br>SEE TABLE                                                                                                        |  |                                                                                                        |  |
|                                                                                                                                       |  | WEIGHT<br>—                                                                                                                |  | SIZE<br>A2                                                                                             |  |
|                                                                                                                                       |  | CUSTOMER DRAWING                                                                                                           |  | CAGE CODE<br>00779                                                                                     |  |
|                                                                                                                                       |  |                                                                                                                            |  | DRAWING NO<br>C-104232                                                                                 |  |
|                                                                                                                                       |  |                                                                                                                            |  | RESTRICTED TO<br>—                                                                                     |  |
|                                                                                                                                       |  |                                                                                                                            |  | SCALE 4:1<br>SHEET 1 of 1<br>REV K                                                                     |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-104232-2](#)