

Bolt & Strand Cutters

TOUGH TOOLS FOR TOUGH CUTS

**KLEIN
TOOLS**



For Professionals... Since 1857™



Heavy-Duty Ratcheting Bolt Cutter

Easily slices through guy strand in just one cut. A smooth ratchet mechanism makes this bolt cutter the easiest to use on the market.

- Cuts 1/2" and 5/8" copper-clad ground rod, up to 1/2" rebar, 7/16" grade 8 bolts, 1/2" grade 5 bolts
- Cuts 1/2" utility-grade guy strand, 3/8" EHS
- Spring-loaded cable retention hook snaps onto the cable in one hands-free motion and keeps strands between cutting blades
- Long handles provide leverage when cutting
- Lockplate reinforcement keeps jaws in correct alignment



Steel and Fiberglass Handled Bolt Cutters

- All-purpose, center-cut jaws
- Forged, alloy tool steel jaws are precision ground for sure, efficient cutting and long life
- Lock plate reinforcement prevents jaw bolts from loosening or turning, keeping jaws in correct alignment
- **NOT** for cutting cable
- Replacement blades available



Cutting Maximum Capacities

Cat. No.	UPC 0-92644+	Overall Length	Soft & Medium*	Hard Material†	Replacement Head
Steel Handled					
63314	63314-0	14" (356 mm)	5/16" (8 mm)	3/16" (5 mm)	63814
63318	63318-8	18" (457 mm)	3/8" (10 mm)	1/4" (6 mm)	63818
63324	63324-9	24" (610 mm)	7/16" (11 mm)	5/16" (8 mm)	63824
63330	63330-0	30" (762 mm)	1/2" (13 mm)	3/8" (10 mm)	63831
63336	63336-2	36" (914 mm)	9/16" (14 mm)	7/16" (11 mm)	63836
63342	63342-3	42" (1067 mm)	11/16" (18 mm)	1/2" (13 mm)	63842
Fiberglass Handled					
63118	63118-4	18.25" (464 mm)	3/8" (10 mm)	1/4" (6 mm)	63918
63124	63124-5	24.5" (622 mm)	7/16" (11 mm)	5/16" (8 mm)	63924
63130	63130-6	30.5" (775 mm)	1/2" (13 mm)	3/8" (10 mm)	63930
63136	63136-8	36.5" (927 mm)	9/16" (14 mm)	7/16" (11 mm)	63936

*Up to Brinell 300, Rockwell C31. †Up to Brinell 400, Rockwell C42.

Cat. No.	UPC 0-92644+	Overall Length	Cutting Maximum Capacities
Heavy-Duty Ratcheting Bolt Cutter			
63RBCHD	63067-5	31" (787 mm)	1/2" and 5/8" copper-clad ground rod, up to 1/2" rebar, 7/16" grade 8 bolts, 1/2" grade 5 bolts, 1/2" utility-grade guy strand (up to HRC 31), 3/8" EHS (up to HRC 42)‡

‡As defined by ASTM A475-98, 1/2" utility grade 7-strand guy strand has minimum breaking strength of 25,000 lbs (11,339.81 kg). 3/8" EHS 7-strand has minimum breaking strength of 15,400 lbs (6,985 kg).

KLEIN TOOLS
For Professionals... Since 1857™

See our complete line of Bolt Cutters

www.kleintools.com



© 2017 Klein Tools, Inc.
Lincolnshire, IL 60069
96485 Rev. 04/17 B