



REVISIONS				DATE	APPROVED
1	DESCRIPTION	0720-0230-93		2/28/94	



AMP WIRE RANGE		UL E13288 Listed	
12-10 AWG STRANDED		12-10 AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	

△ STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX

VOLTAGE RATING: NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² (5,180-13,100) CIR MILS STRANDED

FINISH: TIN PLATE

0.0025(1.000100) MIN THK PER MIL-T-10727

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS
FOR APPLICATION TOOLING ASSISTANCE CENTER
FOR ORDER ENTRY

AMP
AMP Incorporated
Harrisburg, PA 17125-3508

TERMINAL, RING TONGUE, BUDGET

SIZE CASE CODE 00779
DRAWING NO 34891

PART NO 34891

34891