




FIGURE 1
FOR .050 TO .082 WIRE INSULATION DIA




FIGURE 2
INSULATION RESTRICTING
FOR X/Y WIRE INSULATION DIA

- 1 TONGUE MATERIAL THK IS .018±.002
2 MEETS MS25036-144, CLASS 2

8-323914-1	FIGURE 1	#26-#22	NONE	-	
2-323914-2	FIGURE 2	#24	BLUE	.031/.055	
323914 2	FIGURE 1	#26-#22	NONE	-	2-323914-1 2
PART NO.	STYLE	WIRE SIZE	STRIPE COLOR	"X/Y"	PART NO. ON TAPE

1	WIRE TERMINAL INSULATION RESTRICTING	BODY: COPPER (ASTM-B152) TIN PL (ASTM-B545) SLEEVE: COPPER (ASTM-B152) NICKEL PL. (QQ-N-290) INSULATION: NYLON COLOR: YELLOW (ASTM-D4066) TYPE 1	2-323914-2
100	LOOSE PC, BOX	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NYLON COLOR: YELLOW (ASTM-D4066) TYPE 1	8-323914-1
4000	323914 ON TAPE		2 2-323914-1
1	WIRE TERMINAL		2 323914
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 02OCT09	TE Connectivity			
DIMENSIONS: INCHES		CHK TOM MICHELUTTI 02OCT09				
		APVD MIKE PERCHERKE 02OCT09	NAME			
		PRODUCT SPEC	TERMINAL, NYLON - PIDG - RING TONGUE			
MATERIAL SEE TABLE		FINISH SEE TABLE	WIRE SIZE: 26-22			
		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-323914	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 of 1	REV R