


**Part Number: 90331-4003**

3.96mm Pitch Industry Standard Power Supply Housing for Crimp Terminals, 6 Circuits, Keying to the Mating Part Required at Circuit 4



Series image - Reference only

Status: **OBsolete**
Replacement: [903310003](#)
Series: 90331
Category: Crimp Housings

Mates With Part(s): [8619](#)**Use With:** [8993](#)**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:** **REACH SVHC:** Not Reviewed**Low-Halogen Status:** Not Reviewed**Part Detail****General**

Status	Obsolete
Category	Crimp Housings
Series	90331
Application	Signal
Obsolete Date	2004/11/01
Product Name	N/A

Physical

Breakaway	No
Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Temperature Range - Operating	-40°C to +85°C

Agency Certification

CSA	LR19980
UL	E29179

Material Info

UPC	800753962996
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-90331-001
---------------	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)

