

MATERIAL SPECIFICATION:

COVER: PVC

BODY: NYLON #66

CONTACTS: BRASS, NICKEL PLATED

RATING: 50mΩ Max

INSULATION RATING: 500VDC, 100mΩ MIN.

DIELECTRIC STRENGTH: 1500VAC 1 MIN.


NUT: NYLON #66

BASE: NYLON #66

DECORATIVE PLATE: NYLON #66

RATING: 12V, 20AMP


ø29.25 [1.15]



PANEL CUT OUT


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
07/29/11	A	ADDED ROHS COMPLIANT	T.B.	B.S.	

ROHS COMPLIANT




DECORATIVE PLATE

ø28.45 [ø1.12]



"12V"



Tolerance
(Except as noted)



Memory Protection Devices, Inc

200 Broad Hollow Road, Farmingdale, New York 11735

decimal
±.5 (.020)

Scale

Drawn By B.S.

Fractional
± .8 (.030)

Title 12V CIGARETTE SOCKET, 20AMP

Approved By T.B.

Angular
± 3°

Date
07/29/11

Drawing Number
AS212-L