

Indicator Lights *Sealed to IP67*

Colours and voltages:

-  **Neon** Available with Red, Amber, Green or Clear lenses
100/130V (marked 110V), 200/250V (marked 230V)
-  **LED - DC** Red, Yellow, Green, Blue, White
2.0/2.2V Resistors for other voltages available.
-  **LED - AC** Red, Yellow, Green, Blue, White
110-230V ac operation.
-  **Filament lamp** Available with Red, Amber, Green, Clear or Blue lenses
6V, 12/14V, 24/28V.











- ▶ IP67 Panel Sealing
- ▶ Supplied complete with gaskets/'o' rings
- ▶ Neon, LED, mains LED or filament lamp
- ▶ Bezel sizes from 7.6 to 22.9mm dia
- ▶ Red, amber, green and clear lenses
- ▶ Red, yellow, green, blue and white LEDs
- ▶ Wide choice of styles

RoHS

RoHS compliant

To create a catalogue number:

Refer to the 2 columns below (terminal and type), then state: Lens colour, voltage and whether neon, LED or filament lamp

TERM	TYPE	PANEL	ILLUMINATION OPTIONS	DIMENSIONS (mm)	
L 	(L) 1041 OS Chrome bezel 	 6.3  5.3 max	   		
L 	(L) 0245 OS Chrome bezel 	 7.1  4.6 max	   		
L  C 6.3 	(C) 0275 OS Chrome bezel 	 10.0  11.5 max	   		
L  C 6.3 	(C) 0277 OS Chrome bezel 	 10.0  11.5 max	   		
L  C 6.3 	(C) 0177 OS Chrome bezel 	 12.7  11.5 max	   		
C 6.3 	(C) 1092 FFS 	 19.0  4.0 max		