




DIN 7985 A

~ISO 7045

Standard withdrawn



BN 81882

Pozi pan head machine screws

form Z

Stainless steel A2

- ~UNI 7687
- ~ČSN 021147

[3D Cadenas](#)

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
3646007	M1,6	3,2	1,42	0	1,8	0,92	1,17	3
3646009								4
3646010								5
3646011								6
3646012								8
3646013								10
3646014								12
3646015								16
5400411	M2	4	1,72	1	2,4	1,1	1,35	3
3060695								4
3060696								5
3060698								6
3060699								8
3060700								10
3060701								12
3060702								16
3060703								20
5400420	M2,5	5	2,12	1	2,6	1,27	1,52	3
3060704								4
3060705								5
3060706								6
3060707								8
3060708								10
3060709								12
8227837								(14)
3060710								16
5400428								(18)
3060712								20

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
3060714	M3	6	2,52	1	3	1,68	1,93	4
3060715								5
3060716								6
3060717								8
3060718								10
3060719								12
3060720								16
5400436								(18)
3060721								20
3060722								25
3060723								30
3060724								35
3060726								40
5400442								45
5400443	M4	8	3,25	2	4,3	1,9	2,36	5
3060727								6
3060729								8
3060731								10
3060732								12
3060733								16
5400449								(18)
3060734								20
3060735								25
3060736								30
3060737								35
3060738								40
3060739								45
3060740								50
3060741								60
3060742	M5	10	3,95	2	5	2,64	3,1	6
3060743								8
3060744								10
3060745								12
8250758								(14)
3060746								16
3060748								20
3060750								25
3060751								30
3060753								35
3060754								40
3060755								45

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
3060757	M5	10	3,95	2	5	2,64	3,1	50
3060758								60
3060759	M6	12	4,75	3	6,7	3,02	3,48	8
3060760								10
3060761								12
3060762								16
3060763								20
3060764								25
3060765								30
3060766								35
3060767								40
3060768								45
3060769								50
3060770								60