





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	03/28/02	MCCORMICK
B	ECN# 1605 ADDED COMPONENT SPECIFICATION TABLE	12/22/02	MCCORMICK
C	ECN# 2296; DRAWING UPDATES; ADDED NOTES	02/22/06	MCCORMICK
D	ECN3150: UPDATE DWG FORMAT	1/10/08	D.GRIFFIN



BNC PLUG



NOTES:


MATERIAL:
BODY: BRASS
SHELL: BRASS
WASHER: BRASS
HEX NUT: BRASS
CENTER PIN: BRASS
INSULATOR: ACETAL

FINISH:
BODY: NICKEL PLATE
SHELL: NICKEL PLATE
WASHER: NICKEL PLATE
HEX NUT: NICKEL PLATE
CENTER PIN: GOLD PLATE

ELECTRICAL:
IMPEDANCE: 50 OHM

PACKAGING:
INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG

APPLICATION:
PANEL MOUNT ASSEMBLIES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm)		APPROVALS		DATE		 NORTH ANDOVER, MA 01845	
TOLERANCES TO BE:		DRAWN BY CMCCORMICK		03/28/2002		CATEGORY	
$.X \pm 1$ [2.5] ANGLES $\pm 2^\circ$ $.XX \pm 0.1$ [25] $.XXX \pm 0.05$ [1.3]		CHECKED BY D.PARHAM		03/28/2002		COAXIAL	
OVERALL CABLE LENGTH TOL:		APPROVED BY R.CARRICK		03/28/2002		PRODUCT DESCRIPTION	
≤ 60 [1524] +3 [76.2] / - 0 > 60 [1524] +5% / -0%		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		RECEPTACLE BNC M BHD			
PROJ		COLOR VARIATIONS MAY OCCUR		SIZE B	FSCM NO. 43321	DWG. NO. BAC1501	REV. D
				SCALE: 1:1		CAD FILE: BAC1501.SLDDRW	SHEET 1 OF 1