


Test Leads

13TC081

KOBI CONN

Test Leads



Dimensions: In.

SPECIFICATIONS	
Type:	IC clip to IC clip
Withstand voltage:	2KVAC for 1 minute
Insulation resistance:	100MΩ min. @ 500VDC
Lead wire:	24AWG
Cap, body:	nylon 6
Terminal:	phosphor bronze
Spring:	steel
Colors:	red, black

Date Last Revised: 10-20-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300817

13TC081

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[13TC081](#)