




CATALOG NUMBER:	See table below
CUSTOMER:	Stock
DESCRIPTION:	Polar/ Solar Plus SJEOW extension cord with power indicator light in the cord connector
APPROVALS:	UL Listed and CSA Certified (16-12 ga) Outdoor Use Cord Set

CONSTRUCTION PARAMETERS:

Conductor:	See table below
Jacket material:	TPE, yellow
Overall cable O.D. (nom):	See table below
Cord rating:	Hard Usage per the National Electric Code
Attachment plug configuration:	NEMA 5-15P
Cord connector configuration:	NEMA 5-15R
Plug and connector material:	Clear PVC, with neon power indicator lamp in the cord connector



ELECTRICAL PROPERTIES:

Cable temperature rating:	-55 to +90 °C
Maximum operating voltage:	125 VAC
Maximum operating current:	See table below

MARKINGS:

Cable legend type:	Indent print
Logo/legend on fittings:	"E53440"

Catalog number	Length	Conductor	Cable O.D. (nom)	Current rating
01287	25 ft	16/3 26/30 BC	0.315 in	13A
01288	50 ft			10A
01289	100 ft			
01487	25 ft	14/3 41/30 BC	0.352 in	15A
01488	50 ft			13A
01489	100 ft			
01687	25 ft	12/3 65/30 BC	0.420 in	15A
01688	50 ft			
01689	100 ft			
01787	25 ft	10/3 104/30 BC	0.567 in	
01788	50 ft			
01789	100 ft			

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.