

LED Cool Light

24 Vac/dc 6W and 12W



- Low Voltage Power 24Vdc or 24Vac
- LED Driver can be externally mounted for increasing LED bulbs
- Reinforced Lense for high resistance
- Furnished with 1.8 meters cord without plug
- Long service life up to 40,000 hours
- Suitable for Semiconductors manufacturing equipment and clean room
- Temperature range -30°C to +60°C
- IP67 Rated

Built in Ballast Series

Stock No.	LED BULB QUANTITY	LIGHT OUTPUT	A	C	D	Ø
777-7934	1W x 6	780 lm	380mm	396mm	414mm	70mm
777-7943	1W x 12	1560 lm	658mm	674mm	692mm	70mm

