

# CAD32M7

## RELAY 600V 10AMP TESYS + OPTIONS

List Price \$62.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

|                        |   |
|------------------------|---|
| Approvals              | UL Listed File Number: E164353 CCN NKCR - CSA Certified File Number: LR43364<br>Class 3211 03 - CE Marked - IEC Rated |
| Ampere Rating          | 10A   |
| Contact Material       | Silver-Nickel   |
| Contact Rating         | A600 - Q600   |
| Coil Voltage           | 220/230VAC  |
| Maximum Voltage Rating | 600VAC  |
| Mounting Type          | Din Rail(35mm)/Panel  |
| Terminal Type          | Screw Clamp   |
| Type                   | TeSys D   |
| Depth                  | 3.66 Inches   |
| Height                 | 3.03 Inches   |
| Marketing Trade Name   | TeSys   |
| Width                  | 1.77 Inches   |
| Contact Configuration  | 3 N.O./2 N.C.   |
| Weight                 | 1.28 Pounds   |

### Shipping and Ordering

|                   |   |
|-------------------|---|
| Category          | 22371 - Relays, Control, IEC  |
| Discount Schedule | I12   |
| GTIN              | 00785901611905  |
| Package Quantity  | 1   |
| Weight            | 0.77 lbs.   |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility. |
| Returnability     | Y   |
| Country of Origin | MX  |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.