

PVC Strain Relief



Description

- Component:
Press-Fit Version
- bend protection

References

Weblinks

[General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Store](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Variants

Suitable for	Color	Für Leitung mit Mantelaus- sendurchmesser	Tüllenlänge [mm]	Order Number
0101,0102,0104,0106,0112	black or grey	8 - 10 mm	40.3	HN 14.109
1611,1612,1651,1652,4013,4020,4021,4022,8101,8111,9009,9013	-	8,7 - 10 mm	40.3	HN 14.110
4012	-	8 - 10 mm	36.7	HN 14.111
1251,3017	-	6,5 mm	30	HN 14.40
0101,0102,0104,0106,0112	-	8 mm	38	HN 14.41
0101,0102,0104,0106,0112	-	10.0 mm	39	HN 14.43
1611,1612,1651,1652,4013,4020,4021,4022,8101,8111,9009,9013	-	8.7 mm	39.4	HN 14.45
1611,1612,1651,1652,4013,4020,4021,4022,8101,8111,9009,9013	-	10.0 mm	39	HN 14.46
4012	-	8 mm	37.5	HN 14.48
4012	-	10.0 mm	37	HN 14.49

Packaging unit 100 Pcs