


**General ordering data**

Order No.	9510310000
Part designation	Klippon POK 10 Ex
Version	EXI enclosure, 120 mm, 405 mm, 400 mm, glass fibre-reinforced polyester
EAN	4008190498801
Qty.	1 pc(s).

Dimensions

Fixing dimension, height	355 mm
Fixing dimension, width	380 mm
Height	120 mm
Length	405 mm
Width	400 mm

General details

Cover fixing	4 stainless steel M6 screws
Enclosure fixing	Holes 6 mm
Sealing material	Polyurethane and chloroprene
Colour	grey
Class of protection to EN 60529	IP 66
Weight	5,580 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	90 °C

Screwed cable glands top/bottom

M 12	62
M 16	54
M 20	33
M 25	18
M 32	14
M 40	6
M 50	4
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	60
M16	39
M20	30
M25	18
M32	7
M40	5
M50	4
On housing side	left / right

Approvals

Approvals institutes

GOSTEX ATEX ATEX

**Classifications**

ETIM 2.0	EC000520
ETIM 3.0	EC000049
eClass 4.1	27-14-12-06
eClass 5.0	27-18-05-02
eClass 5.1	27-18-05-02

Similar products

Order No.	Part designation	Version
1565440000	Klippon POK 10	Housings, 120 mm, 405 mm, 400 mm, glass fibre-reinforced polyester