

SOLUTIONS & ACCESSORIES FOR:

**STRUCTURED CABLING
TELECOMMUNICATIONS
DATA CENTERS
BROADCAST/HEADEND
AUDIO/VISUAL**

Co-Location (CL)
Cabinet Series
Page 16

**RACK & CABINET
QUICK REFERENCE
PRODUCT GUIDE**



Company Overview

Hammond Manufacturing Co. Ltd., first began as a manufacturer of tube-driven radios and amplifiers in 1917. Today Hammond is today a leading designer, manufacturer and marketer of communication infrastructure, electrical and electronic products.

Hammond products are widely used in many different applications and have been recognized as a brand that designs and manufactures their products to be durable and long-lasting.

Hammond offers a diverse product line that includes electrical and electronic enclosures, power outlet strips, electronic transformers as well as rack and cabinet solutions and accessories for the computer rooms small to large.

Hammond Manufacturing has over 13,000 skus of Electrical products available to you.

Download our E6 Catalog PDF at www.hammondmfg.com



Open Rack Systems	4-6
Wall Mount Solutions	7-10
Rack Cabinet Solutions	11-17
Rack Accessories	18-19
Outlet Strips	20-21
Hammond Modification Services	22-23
Contact Information	24

Introduction and Table of Contents

Thank you for your interest in the Hammond Data Communication Infrastructure product line. In this edition we have added an additional eight (8) pages of content, including our new low-profile wall mount cabinet, our Co-location Series and our new Rack Basics economy line.

The icons below will help you identify various features such as if the product requires assembly or if it can be modified. These icons are simple ways we are working hard to make it easier to find the best solution for your project. If you have any questions or are in need of assistance, flip to the back of the guide for the phone numbers.

As a reminder, if you are not already a subscriber, please sign-up to receive our monthly newsletter called the Hammond Communicator. Details are on the back cover.




This product guide is intended to be used for quick reference only. It includes our most popular skus and products for your consideration.

For our full product offering, please visit our website at: www.hammondmfg.com

www.hammondmfg.com



New! - This product or service was recently added or updated



Knockdown - This product is shipped un-assembled (flat-pack)




Modification - This product can be modified (see pages 22-23)



Heavy Duty - Engineered for maximum strength and durability

Open Frame Rack Systems

DNRR**HDW - Heavy Duty Welded 2-Post Open Frame Rack




Features:

- Constructed of heavy duty 10-gauge steel (Suggested load capacity of 1,530 lb.)
- EIA-310-D compliant 10-32 tapped rails with either 19" or 23" mounting. (Visit web for 23" sizes).
- Side rails include:
 - 1.25" cable pass-thru
 - Tapped 10-32 accessory hole
 - Ganging and accessory mounting holes
- Finished in smooth black powder paint.
- Rails and Base packaged in heavy duty cardboard to prevent freight damage.

Single Tapped Part No.	Double Tapped Part No.	Description
DNRR42HDW	•	24U, 19" Rack Mounting, 48.13" Overall Height
DNRR77HDW	DNRR77HDWB	44U, 19" Rack Mounting, 83.13" Overall Height
DNRR84HDW	DNRR84HDWB	48U, 19" Rack Mounting, 90.13" Overall Height



DNRR**LDW - Light Duty Welded 2-Post Open Frame Rack




Features:

- Constructed of 12-gauge steel (Suggested load capacity of 1,200 lb.)
- EIA-310-D compliant 10-32 tapped rails with 19" mounting.
- Finished in smooth black powder paint.
- Rails and Base packaged in heavy duty cardboard to prevent freight damage.

Single Tapped Part No.	Description
DNRR77LDW	44U, 19" Rack Mounting, 83.13" Overall Height
DNRR84LDW	48U, 19" Rack Mounting, 90.13" Overall Height



RACK BASICS - Economy Welded 2-Post Open Frame Rack



RACK BASICS®

When you need quality on a budget, you can trust RACK BASICS, the contractor-friendly brand of economy rack and cabinet solutions. Introducing the RB-2P77, your best economy option when a standard welded rack is required.

Features:

- Constructed in 12-gauge steel (Maximum load capacity of 800 lb.)
- EIA-310-D compliant 10-32 tapped rails with 19" mounting.
- Side ganging and accessory mounting holes (compatible with all Hammond rack accessories). Bonding Studs located bottom and top to accommodate grounding options.
- Finished in smooth black powder paint.
- Rails and Base packaged in cardboard to prevent freight damage.


Single Tapped Part No.	Description
RB-2P77	44U, 19" Rack Mounting, 83.13" Overall Height

NEW!

New Product!

Open Frame Rack Systems

DNRR**HDKB - Heavy Duty Knockdown 2-Post Open Frame Rack




Features:

- Constructed of heavy duty 10-gauge steel (Suggested load capacity of 1,200 lb.)
- Easy to assembly knockdown design.
- EIA-310-D compliant 10-32 double tapped rails with 19" mounting.
- Side rails include:
 - 1.25" cable pass-thru
 - Tapped 10-32 accessory hole and ganging/accessory holes
- Finished in smooth black powder paint.
- Ships in heavy duty packaging to prevent freight damage.

Double Tapped	
Part No.	Description
DNRR70HDKB	40U, 19" Rack Mounting, 48.13" Overall Height
DNRR77HDKB	44U, 19" Rack Mounting, 83.13" Overall Height
DNRR84HDKB	48U, 19" Rack Mounting, 90.13" Overall Height



DC2R - Light Duty Knockdown 2-Post Open Frame Rack




Features:

- Constructed of heavy duty 12-gauge (Suggested load capacity of 800 lb.)
- EIA-310-D compliant square hole rails with 19" mounting.
- Side rails include:
 - 1.12" cable pass-thru
 - Ganging and accessory mounting holes
- Finished in smooth black powder paint.
- Ships in heavy duty packaging to prevent freight damage.

Part No.	Description
DC2R44	44U, 19" Rack Mounting, 83.13" Overall Height



RRAL - Aluminum Knockdown 2-Post Open Frame Rack



Features:


- Constructed of 6063-T6 Aluminum (Suggested load capacity of 840 lb.)
- EIA-310-D compliant 12-24 tapped rails with either 19" or 23" mounting. (Visit web for 23" sizes)
- Side rails include:
 - 1.25" cable pass-thru
 - Ganging and accessory mounting holes
- Natural finish or in smooth black powder paint (BK)
- Ships in heavy duty packaging to prevent freight damage.

Single Tapped	
Part No.	Description
RRAL1984	45U, 19" Rack Mounting, 84" Natural Finish
RRAL1984BK	45U, 19" Rack Mounting, 84" Painted Black



Open Frame Rack Systems

DC4R Series - 4-Post Steel Open Frame Rack



The Hammond DC4R Open Rack series is one of the most economical solutions to house servers and other devices in wiring closets or data centers. In situations where the wiring closet itself is under lock and key and accessed by a limited number of people, full cabinets having locking doors and side panels may not be required resulting in a significant cost savings.

Features:

- Available in 24U and 44U and up to 48" in overall depth (See table below).
 - 24U (42") - 48.125" over-all height, 20.5" over-all width
 - 44U (77") - 83.13" over-all height, 20.5" over-all width
- Two (2) pair of 19" mounting EIA-310-D compliant square-hole rails integrated into DC4R Frame. Features rack unit space marking hole.
- Includes one (1) set of two (2) horizontal cable manager bars (DC4RSHCM). Additional cable manager bars available (see below).
- Constructed of 12-gauge steel
- Suggested load capacity of 2,000 lb.
- Finished in smooth black powder paint.



Part No.	Description
DC4R24	24U 4-Post Rack Kit (24" to 36" overall depth)
DC4R44	44U 4-Post Rack Kit (24" to 36" overall depth)
DC4R4448	44U 4-Post Rack Kit (32" to 48" overall depth)



DC4RSHCM
Horizontal Cable Manager Bars with Adjustable Depth


Accessories

Part No.	Description
RRALJK	Standard Baying Hardware Kit
DC4RSHCM	Additional Horizontal Cable Bars (2)
DC4RPR24	Additional pair of rails for DC4R 24U
DC4RPR44	Additional pair of rails for DC4R 44U



RRALJK
Baying Kit

2 & 4-Post Open Frame Accessories



Vertical Cable Managers

Part No.	Description	H	W	D
RRCM44UD	44U Manager w/Door	77"	6"	5"
RRCM84UD	44U Manager w/Door	77"	8"	6"
RRCM124UD	44U Manager w/Door	77"	12"	6"

These are our most popular sizes! Hammond offers more Vertical Cable Managers varying in size, material and design! Please visit our web site for additional models.

- Available in three widths (6", 8", 12")
- Hinged doors secured with magnets
- Can mount on left or right of rack
- Managers can also bay racks
- 16 gauge steel
- Mounting hardware included



Cable Chimneys (Attaches directly to VCM)

Part No.	Description	H	W	D
RRCMCH65	Cable chimney	36"	6"	5"
RRCMCH86	Cable chimney	36"	8"	6"
RRCMCH126	Cable chimney	36"	12"	6"

Note: The above cable chimneys are designed to connect directly to our vertical cable managers, and are not compatible with our Top Cable Manager (TCM) System below.

Cable Chimneys are assembled from two halves, making it easy to attach around existing cables.

- Attaches directly to Vertical Managers
- 18 gauge steel
- Easy installation
- Mounting hardware included

Compatible Casters and Dollies

Part No.	Description
RRLDCASTER	Light Duty Casters (4) Rated for 800 lb (Adds 3.75" to overall height)
RRLPDOL	Low Profile Dolly Rated for 1080 lb (Adds 1.25" to overall height)
RRHDHOL	Heavy Duty Dolly Rated for 1500 lb (Adds 3.50" to overall height)




RRLDCASTER RRLPDOL RRHDHOL



Don't forget to order your mounting hardware!

See page 18 for options.

HPB Series - Heavy Duty Fixed Wall Bracket



Part No.	Description
HPB19003BK1	2U Wall Bracket
HPB19005BK1	3U Wall Bracket
HPB19007BK1	4U Wall Bracket
PBCOVER	6" Depth Dust cover/shelf

Includes 10 or 25-pack of 10-32 black rack screws with washers and mounting template for easy installation. Wall mounting hardware not included.

Features:

- Knock-down design.
- Assembly required (flat-pack shipment).
- 14 gauge formed steel.
- Hinged for easy rear access to devices.
- Fixed-depth of 6".
- Multiple tie points for cable management.
- EIA compliant 10-32 tapped holes.
- Suggested load capacity of 90 lb.
- Black powder paint finish.

NEW! Now Easier to Assemble!



APB Series - Heavy Duty Adjustable Wall Bracket



Part No.	Description
APB19007BK1	4U Wall Bracket
APB19010BK1	6U Wall Bracket
APB19014BK1	8U Wall Bracket
APB19021BK1	12U Wall Bracket
PBCOVER	Dust cover/shelf

Now available by special order, new deeper models available up to 24" in depth. Contact us today to inquire.

Includes 25-pack of 10-32 black rack screws with washers and mounting template for easy installation. Wall mounting hardware not included.


Features:

- Knock-down design.
- Ships un-assembled (flat-pack).
- 14 gauge formed steel.
- Double-hinged for easy rear access.
- Adjustable depth from 12" to 18" using slots for easy set-up and adjusting.
- Multiple tie points for cable management.
- EIA compliant 10-32 tapped holes.
- Suggested load capacity of 80 lb.
- Generous cable access.
- Black powder paint finish.

NEW! Now Easier to Assemble!



VPB Series - Heavy Duty Vertical Wall Bracket




Part No.	Description
VPB192UBK	2U Vertical Wall Bracket
VPB194UBK	4U Vertical Wall Bracket
VPB196UBK	6U Vertical Wall Bracket

Includes four (4) 10-32 black rack screws with washers and clip nuts per rack unit. Wall mounting hardware not included.

Features:

- Horizontal or vertical equipment mounting.
- EIA compliant rails with clip-nuts.
- 14 gauge formed steel rails.
- Suggested load capacity of 135 lb.
- Rear cable access.
- Black powder paint finish.

1459 Series - Open Frame Wall Mount Rack



Part #	Rack Space Mounting		Overall Dimensions (Inches)		
	Inches	Units	Height	Width	Depth
1459FBK1	22.75	13	24.70	21.12	16.14
1459JBK1	33.25	19	35.20	21.12	16.14
1459MBK1	47.25	27	27.50	21.12	16.14

Includes starter pack of 10-32 black rack screws and washers. Wall mounting hardware not included.

Optional Solid Side Panels:

Part #	Description
1459FQBK1	13U Side Panel (Pair)
1459JBK1	19U Side Panel (Pair)
1459MQBK1	27U Side Panel (Pair)

Features:

- Rugged welded design.
- 16 gauge formed steel.
- For use as desktop or wall mount rack.
- Included removable top/bottom panels.
- Optional solid side panels.
- EIA compliant 10-32 tapped holes.
- Suggested load capacity of 800 lb.
- Generous cable access.
- Black powder paint finish.



Wall Mount Solutions

HLP Series - Low-Profile Network/Security Wall Mount Cabinet




NEW! New Product!

Features:


- Available in three (3) depths with the ability to install an additional 4U rail.
- Rack mounting units available in 4U, 6U and 8U.
- Rails pivot 180 degrees for easy equipment mounting.
- 22" usable equipment mounting depth (vertical).
- Front door features:
 - Louvered front door for equipment airflow.
 - Can be installed to swing open either from left or right.
 - Locking hinged top and separately locking hinged body.
- Rear wall mounting section features:
 - 2.0", 1.5", 1.0", 11/16" and 9/16" conduit laser knock-outs on all sides.
 - Three (3) located top and bottom, two (2) located each side.
 - Two (2) laser knockouts for optional fans located top and bottom.
 - Generous cable management lances located on the rear section.
 - Heavy duty keyhole for wall mounting.
 - Large opening in rear for cable access.
- Body and backpan of rack shall be constructed of 16-gauge steel, rackrail shall be 12-gauge steel with punched holes for use with 10-32 clip nuts in universal EIA spacing and accommodate mounting brackets. Hinged top shall be 16-gauge steel, hinged top and door section shall be locking and is keyed the same. (Optional separately keyed lock available)
- Grounding/bonding lugs are located on top and bottom of the door and rear sections. (Grounding kit sold separately).
- Rugged sand-textured black powder paint (reduced fingerprints and marks).
- HLP Series shall be RoHS EU Directive 2002/95/EC compliant.
- Suggested load capacity of 150 lb.



Top/Bottom fan laser knockouts for thermal management.



Large cable management hooks located on both sides.




Four (4) locations for easy mounting of 1.875" x 2.375" metal utility box.

Part #	Rack Space Mounting		Overall Dimensions (Inches)		
	Inches	Units	Height	Width	Depth
HLP4UBK	7.0	4	31.00	27.50	10.80
HLP6UBK	10.5	6	31.00	27.50	15.05
HLP8UBK	14	8	31.00	27.50	19.30

Includes starter pack of 10-32 black rack screws and clip nuts. Wall mounting hardware not included.

Optional Accessories:

Part #	Description
HLP4UR	4U Mounting Rail Kit
H1032BK500	500 Pack of 10-32 Screws
1421N100	100 Pack of 10-32 Clip Nuts
HWMSLOCK	Door lock (Keyed differently)
GRDKIT04	10 Gauge Ground Wire Kit
DNFK1AC120	Single (1) Fan kit with grills & cord
DNFK2AC120	Dual (2) Fan kit with grills & cord



12 Gauge Rails pivot 180° with locking thumb screw.

RCHLB Series - Heavy Duty Ventilated Wall Mount Security Lock box



Part No.	Panel Height	Overall Dim's (mm)		
		H	W	D
RCHLB193UBK1	3U	133 (5.25")	533 (21.00")	361 (14.23")

Note: Usable depth = 340mm (13.41")



Features:

- 16-gauge steel construction.
- Vented sides with cable entry hole
- Lock and key included.
- Fixed 19" mounting rails recessed (1").
- Includes single pair of fixed EIA 19" punched holes for use with 10-32 screws and clip nuts.
- Suggested load capacity of 130 lb.
- Finished in textured black powder paint.

HWM Series - Swing Out Wall Mount Cabinet



HWM Body

The HWM body was engineered for superior weight capacity. Constructed of heavy duty steel (14 gauge rear section and 16 gauge Center section and door) the HWM Series has a suggested load capacity of 275 lb. The HWM can handle UPS batteries, servers and more without compromising structural security. The HWM body is finished in sand-textured black powder paint and includes grounding studs provided on rear/center section and door.

Mounting Rails

Includes one (1) pair of 19" mounting EIA-310-D compliant 10-32 tapped rails with U-markings. Rails are infinitely adjustable in depth. Rails are fabricated of heavy duty twelve (12) gauge steel finished in black powder paint.

Cable Entry & Management



The HWM includes multiple points of cable entry. The largest is the generous rear opening that is designed for mounting over a power receptacle. Cable conduit knockouts are located on the top, bottom and side of the cabinet. Included knockouts are designed for conduit fittings that range in diameter from 1.125" to 3.00" (top/bottom) and 2.00" to 2.50" (sides). For cable management, multiple lancing points are formed on the rear panel and on all panel rails.

Doors

A factory installed vented and locking door is included with each unit. Both tinted acrylic and solid doors are available for installation on-site. Doors can be reversed hinged (by rotating mid section). Optional lock is available (keyed differently than lock for rear section) for enhanced security.

Thermal Performance

The top and bottom of the HWM includes two (2) 3.5" diameter laser knockouts (centered) for fan installation. The included front perforated door offers 65% airflow. The ventilated center section includes two (2) fan cutouts (per side), designed for side airflow high capacity servers and switches.



Part No.	Center Depth		Panel Height		Overall Dim.	
	(In)	Inches	Units	Height	(In)	Depth
HWM2412U11BK	11	21	12	27.75	16.7	
HWM2420U11BK	11	35	20	41.75	16.7	
HWM2424U11BK	11	42	24	48.75	16.7	
HWM2432U11BK	11	56	32	62.75	16.7	
HWM2412U20BK	20	21	12	27.75	25.7	
HWM2420U20BK	20	35	20	41.75	25.7	
HWM2424U20BK	20	42	24	48.75	25.7	
HWM2432U20BK	20	56	32	62.75	25.7	
HWM2412U26BK	26	21	12	27.75	31.7	
HWM2420U26BK	26	35	20	41.75	31.7	
HWM2424U26BK	26	42	24	48.75	31.7	
HWM2432U26BK	26	56	32	62.75	31.7	

Optional Accessories:

Part No.	Description
HWMPCLIP	Power Outlet Strip Clip
HWMSLOCK	Front lock (keyed differently)
GRDKIT04	Cabinet Ground Cable Kit
MPC616	Magnetic Vent Cover
DNFK1AC120	Single (1) Fan kit with grills and cord
DNFK2AC120	Dual (2) Fan kit with grills and cord
Outlet Strip	See page 17 for part numbers



Designed for side venting high capacity servers, switches and other equipment.

Additional Rail Options:

Part No.	Description
HWMTR12U	12U Tapped 10-32 Rail (Pair)
HWMTR20U	20U Tapped 10-32 Rail (Pair)
HWMTR24U	24U Tapped 10-32 Rail (Pair)
HWMTR32U	32U Tapped 10-32 Rail (Pair)
HWMSR12U	12U Square Hole Rail (Pair)
HWMSR20U	20U Square Hole Rail (Pair)
HWMSR24U	24U Square Hole Rail (Pair)
HWMSR32U	32U Square Hole Rail (Pair)

Door Options:


Part No.	Description
HWMSD2412UBK	12U Solid Door
HWMSD2420UBK	20U Solid Door
HWMSD2424UBK	24U Solid Door
HWMSD2432UBK	32U Solid Door
HWMPD2412UBK	12U Tinted Acrylic Door
HWMPD2420UBK	20U Tinted Acrylic Door
HWMPD2424UBK	24U Tinted Acrylic Door
HWMPD2432UBK	32U Tinted Acrylic Door

For detailed drawings please visit
www.hammondmg.com

HAMMOND MODIFICATION SERVICES

If the above HWM just doesn't meet your needs, the product designers at Hammond Mfg can work with you to design the perfect cabinet!

Recently we built a HWM cabinet that was extra-wide to support cable managers (see right). Please keep in mind that Hammond offers a full range of modification services. Take a look at page 22 for more information.



Wall Mount Solutions

RACK BASICS®

Introducing Rack Basics® by Hammond Manufacturing. Rack Basics® is a brand name for our entry-level product that is both built locally and sourced abroad. The Rack Basics® product line is perfect for light duty applications and is economically priced. In addition, Rack Basics® products are compatible with most Hammond Manufacturing accessories and outlet strips. Contact your local Hammond rep for details.

RACK BASICS® - Economy Fixed Wall Bracket



RACK BASICS®

Part No.	Description
FWB191UBK	1U Wall Bracket
FWB192UBK	2U Wall Bracket
FWB194UBK	4U Wall Bracket

Features:

- Hinged for easy rear access to devices.
- Fixed-depth of 6".
- 16 gauge formed steel.
- Rear cable access.
- Black powder paint finish.
- Suggested load capacity of 70 lb.
- Includes four (4) 10-32 black rack screws with washers and clip nuts per rack unit.

RACK BASICS® - Economy Wall Mount Cabinet



RACK BASICS®

Part No.	Panel Height	Overall Dim's (mm)		
		H	W	D
WMC1901023BK2	6U	14.1	23.6	23.6
WMC1901523BK2	9U	19.4	23.6	23.6
WMC1902123BK2	12U	24.6	23.6	23.6
WMC1902623BK2	15U	29.9	23.6	23.6

Note: Usable depth = 21.25"

Includes starter pack of M5 screws and cage nuts.

Features:

- Knock-down design.
- Ships un-assembled.
- 16 gauge formed steel.
- Includes two (2) pairs of EIA compliant square hole rails.
- Rails adjustable depth in 25mm increments.
- Tempered glass front door.
- Front and sides vented for air flow.
- Rear cable access.
- Provision for optional fans on top panel.
- Maximum load capacity of 90 lb.
- Black powder paint finish.

NEW!

Now Easier to Assemble!



RACK BASICS® - Economy Swing Out Wall Mount Cabinet



RACK BASICS®

Part No.	Panel Height	Overall Dim's (mm)		
		H	W	D
SWCC1901021BK2	6U	15.1	23.6	21.7
SWCC1901521BK2	9U	20.4	23.6	21.7
SWCC1902121BK2	12U	25.6	23.6	21.7
SWCC1902621BK2	15U	30.9	23.6	21.7
SWCC1903121BK2	18U	36.1	23.6	21.7
SWCCLOC	Use for side panel lock mechanism			

Note: Usable depth = 16.20"

Includes starter pack of M5 screws and cage nuts.

Features:

- Double-hinged for easy rear access (body swings open to 120°).
- 16 gauge formed steel.
- Includes two (2) pairs of EIA compliant square hole rails.
- Rails adjustable depth in 25mm increments.
- Tempered glass front door.
- Front and sides vented for air flow.
- Rear cable access.
- Provision for optional fans on top panel.
- Maximum load capacity of 90 lb.
- Black powder paint finish.

RACK BASICS® - Economy Server Cabinet



RACK BASICS®

The DC200 series cabinets are offered in two capacities, 24U spaces and 42U spaces. A standard overall width of 23.6" (24") allow cabinets to side or bay together matching standard 2ft floor tile placement, optimizing sub-floor cable and cold-air access without conflict.

The DC200 features a fully-welded 16-gauge steel frame with heavy-duty struts contributing to a maximum load capacity of 950 lb.

Frame	Four (4) leveling feet are included with support for included recessed casters. Grounding studs provided on frame. Pair of solid side panels are removable and include stiffeners to support the full depth.
Mounting Rails	Includes two (2) pairs of 19" mounting EIA compliant square-hole design feature rack unit markings. Rails can adjust in depth in 25mm increments.
Cable Entry & Management	Includes two (2) 4" diameter cable entry holes (top) and one (1) 8" x 12" opening (bottom). Open frame bottom allows raised tile floor cable and air access.
Doors	Perforated front/rear doors provide excellent ventilation featuring swing handles complete with locks and keys. Front door has attractive 4 point latch, curved and ribbed surface for added stability, and can be easily removed and hinged in either direction. Rear features split doors making access easier in tight spaces.

Part No.	Panel Height		Overall Dim's (mm)		
	Inches	Units	H	W	D
DC2004242	73.5"	42	1997 (78.6")	600 (23.6")	1100 (43.3")
DC2004224	42"	24	1197 (47.1")	600 (23.6")	1100 (43.3")

Optional Accessories:

Part No.	Description
DC2PBCLP	Mounting bracket for Hammond vertical outlet strips



Save time configuring a cabinet!

1. Choose you desired product series.
2. Select the components and accessories required.
3. Provide us with the required contact information.
4. The configured quotation will be sent to you.*

It's That Easy!

Q-Assembly allows you to build and order the custom assembly that YOU want, without compromise. The bill of materials is automatically generated, eliminating ordering errors. When you place your order, your configured cabinet ships assembled at no additional charge** Component stock levels are maintained for quick turnaround and delivery.

Available for the Hammond C4 and CL Cabinet Series - See pages 14-17

Build your own assembly at: www.q-assembly.com

*Quotation will be sent through your Hammond Distributor of choice. **Accessories are shipped loose inside cabinet. Accessories may be installed for an additional fee.

Rack Cabinet Solutions

RCHS Series - Heavy Duty Knockdown Cabinet



Part No.	Rack Units	Overall Dim's (in)		
		H	W	D
RCHS1901017BK1	6U	10.75	21.00	17.50
RCHS1901417BK1	8U	16.00	21.00	17.50
RCHS1901717BK1	10U	19.50	21.00	17.50
RCHS1902817BK1	16U	30.00	21.00	17.50
RCHS1901024BK1	6U	10.75	21.00	24.50
RCHS1901424BK1	8U	16.00	21.00	24.50
RCHS1901724BK1	10U	19.50	21.00	24.50
RCHS1902824BK1	16U	30.00	21.00	24.50
RCHS1901031BK1	6U	10.75	21.00	31.50
RCHS1901431BK1	8U	16.00	21.00	31.50
RCHS1901731BK1	10U	19.50	21.00	31.50
RCHS1902831BK1	16U	30.00	21.00	31.50


Includes rubber feet, black ABS plastic handles, a starter pack of 10-32 clip nuts & matching 1421ABK screws.

Features:

- Knock-down design.
- Assembly required (flat-pack shipment).
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included).
- EIA compliant rails with punched round holes for clip-nuts.
- 16 gauge formed steel.
- Suggested load capacity of 800 lb.
- Black powder paint finish.



RCHV Series - Heavy Duty Knockdown Cabinet



Part No.	Rack Units	Overall Dim's (in)		
		H	W	D
RCHV1901017BK1	6U	10.75	21.00	17.50
RCHV1901417BK1	8U	16.00	21.00	17.50
RCHV1901717BK1	10U	19.50	21.00	17.50
RCHV1902817BK1	16U	30.00	21.00	17.50
RCHV1901024BK1	6U	10.75	21.00	24.50
RCHV1901424BK1	8U	16.00	21.00	24.50
RCHV1901724BK1	10U	19.50	21.00	24.50
RCHV1902824BK1	16U	30.00	21.00	24.50
RCHV1901031BK1	6U	10.75	21.00	31.50
RCHV1901431BK1	8U	16.00	21.00	31.50
RCHV1901731BK1	10U	19.50	21.00	31.50
RCHV1902831BK1	16U	30.00	21.00	31.50


Includes rubber feet, black ABS plastic handles, a starter pack of 10-32 clip nuts & matching 1421ABK screws.

Features:

- Knock-down design.
- Side ventilated for passive air flow.
- Assembly required (flat-pack shipment).
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included).
- EIA compliant rails with punched round holes for clip-nuts.
- 16 gauge formed steel.
- Suggested load capacity of 800 lb.
- Black powder paint finish.



RCHD Series - Locking Door for RCHS/HCHV Cabinet Series



Part No.	Rack Units	Overall Dim's (in)		
		H	W	D
RCHD1910BK1	6U	8.75	18.88	0.50
RCHD1914BK1	8U	14.00	18.88	0.50
RCHD1917BK1	10U	17.50	18.88	0.50
RCHD1928BK1	16U	28.00	18.88	0.50

Features:


- 16-gauge formed steel.
- Both front & back of "RCHS" rack cabinets are punched to accept these doors
- Mounts either right or left hand hinge (door & cabinet are symmetrical)
- Includes installed lock and two keys
- Finished in rugged textured powder paint to match RCHS/RCHV enclosures
- Includes mounting hardware
- Black powder paint finish.



HAMMOND MODIFICATION SERVICES

If the above RCHS/RCHV just doesn't meet your needs, the product designers at Hammond Mfg can work with you to design the perfect cabinet!

Recently we built a RCHS cabinet that was reduced to 3U in height. (right) It included casters, a bonding kit and special cutouts on both front and rear panels. Hammond offers a full range of modification services. See page 22 for details.




RCSC Series - Stacking SMB Server Cabinet




Optional Vented Window door shown.



**EASY
ASSEMBLY!**



**OPTIONAL
DOORS**



The RCSC Rack Cabinet features a stacking design that allows for up to three (3) cabinets* to be stacked atop each other. This Rack Cabinet is fully loaded and includes two (2) pairs of infinitely adjustable sliding EIA square-hole rails, punch-outs for cable entry and/or fan cooling and comes in a variety of sizes and depths.

The unique stacking feature enables your cabinet space to grow as your needs do. *Stack up-to three (3) 12U, two (2) 24U or one (1) of each cabinet atop each other using the required baying kit (RCSCBAY). The 12U cabinet is a great starter cabinet for any small to medium sized business.

RCSC Frame

Knockdown 16-gauge steel frame with heavy-duty struts contributing to a weight-load rating of 1500 lb. Ships un-assembled in (flat-pack). Four (4) embosses are included with support for optional levelling feet or casters. Grounding studs provided on body.

Mounting Rails

Includes two (2) pair of 19" mounting EIA-310-D compliant square-hole design feature U space markings. Rails are infinitely adjustable in depth. Rails are fabricated of heavy duty fourteen (14) gauge steel, painted smooth black.

Cable Entry & Management

The top and bottom of the RCSC includes two (2) laser knockouts (per side) for cable-entry or fans (includes gasket strip material). For 36" depth cabinet side panels include cable entry knockouts. Also includes a laser knockout rear gland plate for floor-level cable entry.

Doors

Optional doors are available in solid, tinted acrylic with venting (see above-left) and high airflow vented. Snap-in hinges can be mounted without having to bolt-on from inside the cabinet. In addition, the hinges can be mounted on the left or right.

Thermal Performance

High airflow perforated doors for both front and rear of the cabinet are suggested for most server applications. Perforated doors meet server manufacturer Free-Air-Ratio (FAR) requirements at 65%.

Finish

Finished in rugged black powder paint.

Part No.	Units	Overall Height	Overall Depth	Max Mounting Depth
RCSC1902124BK1	12U	25"	24"	23.5"
RCSC1904224BK1	24U	46"	24"	23.5"
RCSC1902131BK1	12U	25"	31"	29.0"
RCSC1904231BK1	24U	46"	31"	29.0"
RCSC1902136BK1	12U	25"	36"	29.0"
RCSC1904236BK1	24U	46"	36"	29.0"

Includes 50-Pack 10-32 cage nuts and screws.
42" Depth option available upon request.

Optional Locking Doors


Part No.	Description
RCSC19021SDBK1	12U Solid Door w/lock
RCSC19021VDBK1	12U Vented Door w/lock
RCSC19021WDBK1	12U Vented Window Door w/lock
RCSC19042SDBK1	24U Solid Door w/lock
RCSC19042VDBK1	24U Vented Door w/lock
RCSC19042WDBK1	24U Vented Window Door w/lock

Optional Accessories:

Part No.	Description
RCSCATIP	Anti-tip brackets
RCSCBAY	Baying kit - bays (2) RCSC's together (vertically or horizontally)
GRDKIT04	Cabinet ground cable kit
DNFK1AC120	Single (1) Fan kit with grills and cord
DNFK2AC120	Dual (2) Fan kit with grills and cord

Optional Casters

Part No.	Description	Rated
1425P	Light-duty casters(4)	400 lb
1425BH	Heavy duty casters(4)	1000 lb



Dual laser knockouts at rear of cabinet for optional fans or cable entry when stacked.

**For detailed drawings please
visit www.hammondmf.com**

*NOTE: Baying kit (RCSCBAY) is required to lock cabinets together securely when stacking.

Rack Cabinet Solutions

C4 Series - Modular Data Center Cabinet System



For detailed drawings please visit www.hammondmgf.com

The C4 Rack Cabinet Series provides users with maximum flexibility:

- Standard C4 assemblies provide easy-ordering for common applications
- Mix and match standard C4 components
- Contact Hammond for special colours, sizes or other modifications

The C4 features a fully-welded 14-gauge steel frame with heavy-duty struts contributing to a weight-load rating of 2000 lb. With an available depth of up to 42", the C4 series can support deep server dimensions while providing ample space for cable management.

C4 Frame

Four (4) leveling feet are included with support for optional casters. Grounding studs provided on frame as well as side panels and doors.

Mounting Rails

EIA-compliant square-hole design feature rack unit markings. Infinite-depth setting using C-channel struts. Zinc-plated for superior grounding. The 30" wide C4 rails have cable-tie support and pass-through holes.

Cable Entry & Management

The 30" wide C4 has generous cabling space, four (3.5" wide) cable entry holes on the top, support for up to four optional 4"-deep vertical cable managers, and an open base for easy cable access from raised-tile sub-floors. Vertical cable trays are available for both 24" and 30"-Wide cabinets. The 30" wide compatible versions feature magnetic-latching doors, and 3.5" wide x 4" deep cable space.

Door Flexibility

Available options include solid, Acrylic and perforated versions. Perforated doors are offered in both single and split door designs. Split doors can save valuable working space when accessing the back of the cabinet.

Thermal Performance


Perforated doors for both front and back of the cabinet are suggested for most server applications. The C4 cabinet frame features an open-top design supporting optional solid and vented top panels, as well as a selection of fan tops capable of up to 550 CFM. Cabinets come standard with an open base design to allow for cable entry and cold-air supply in raised-tile-floor installations. See page 15 for a selection of C4 fan tops and page 19 for fan trays and blowers.

Seismic Ready

The structural integrity of the standard C4 frame design meets Seismic UBC Zone-4 certification.

Finish

All C4 cabinet components (and many accessories) are finished in textured black powder paint.



Your **QUICK & EASY** configuration tool is just a click away!



Build your own assembly at: www.q-assembly.com





HAMMOND MODIFICATION SERVICES

Hammond gives you complete flexibility when it comes to product modification. Designed for the test/measurement industry, this modified RCHS (right) was reduced to 3U, includes casters and special modified panels.

If the above RCHS/RCHV just doesn't meet your needs, the product designers at Hammond Mfg can work with you to design the perfect cabinet! Take a look at page 22 for more information.



C4 Series - Modular Data Center Cabinet System

SAVE TIME AND BUILD YOUR CABINET ONLINE USING Q-ASSEMBLY! www.q-assembly.com		24" Overall Width		30" Overall Width		
		42U	44U	44U		
		79.3" Overall Ht.	83.5" Overall Ht.	83.5" Overall Ht.		
Step 1 Frame Dimension		31.5" Deep Frame (Usable depth = 29.5")	☐ C4F247331BK1	☐ C4F247731BK1	☐ C4F307731BK1	
		36" Deep Frame (Usable depth = 34")	☐ C4F247336BK1	☐ C4F247736BK1	☐ C4F307736BK1	
		42" Deep Frame (Usable depth = 40")	☐ C4F247342BK1	☐ C4F247742BK1	☐ C4F307742BK1	
		48" Deep Frame (Usable depth = 46")	☐ Special Order	☐ Special Order	☐ Special Order	
		Looking for a specific size not listed above? Please keep in mind that Hammond offers a full range of modification services. Take a look at pages 18 and 19 for more information.				
Step 2 19" Mounting Rails		Standard Tapped 10-32 Rails (Pair)	☐ C4PR2473TZPL	☐ C4PR2477TZPL	n/a	
		Standard Square Hole Rails (Pair)	☐ C4PR2473SZPL	☐ C4PR2477SZPL	n/a	
		Extra Wide Tapped Rails (Pair)	n/a	n/a	☐ C4PR77TZPL	
		Extra Wide Square Hole Rails (Pair)	n/a	n/a	☐ C4PR77SZPL	
		All C4 Rails are Zinc Plated and include a 25 pack of 10-32 screws and cage nuts.				
Step 3 Side Panels		31.5" Solid Side Panels (Pair)	☐ C4SP7331SBK1	☐ C4SP7731SBK1	☐ C4SP7731SBK1	
		36" Solid Side Panels (Pair)	☐ C4SP7336SBK1	☐ C4SP7736SBK1	☐ C4SP7736SBK1	
		42" Solid Side Panels (Pair)	☐ C4SP7342SBK1	☐ C4SP7742SBK1	☐ C4SP7742SBK1	
		31.5" Vented Side Panels (Pair)	☐ C4SP7331VBK1	☐ C4SP7731VBK1	☐ C4SP7731VBK1	
		36" Vented Side Panels (Pair)	☐ C4SP7336VBK1	☐ C4SP7736VBK1	☐ C4SP7736VBK1	
		42" Vented Side Panels (Pair)	☐ C4SP7342VBK1	☐ C4SP7742VBK1	☐ C4SP7742VBK1	
Step 4 Doors		Solid Door	☐ C4DF2473SBK1	☐ C4DF2477SBK1	☐ C4DF3077SBK1	
		Tinted Acrylic Door	☐ C4DF2473PBK1	☐ C4DF2477PBK1	☐ C4DF3077PBK1	
		Perforated Door 51% F. A. R.	☐ C4DF2473VBK1	☐ C4DF2477VBK1	☐ C4DF3077VBK1	
		Perforated Split Doors 51% F. A. R. (Pair)	☐ C4BD2473VBK1	☐ C4BD2477VBK1	☐ C4BD3077VBK1	
Step 5 Top Panels		31.5" Solid Top Panel	☐ C2T1923SBK1	☐ C2T1923SBK1	☐ C2T2423SBK1	
		36" Solid Top Panel	☐ C2T1931SBK1	☐ C2T1931SBK1	☐ C2T2431SBK1	
		42" Solid Top Panel	☐ C2T1936SBK1	☐ C2T1936SBK1	☐ C2T2436SBK1	
		31.5" Vented Top Panel	☐ C2T1923VBK1	☐ C2T1923VBK1	☐ C2T2423VBK1	
		36" Vented Top Panel	☐ C2T1931VBK1	☐ C2T1931VBK1	☐ C2T2431VBK1	
		42" Vented Top Panel	☐ C2T1936VBK1	☐ C2T1936VBK1	☐ C2T2436VBK1	
		31.5" Fan Top Panel (4 or 6 holes)	☐ C2T1923FBK1	☐ C2T1923FBK1	☐ C2T2423FBK1	
		36" Fan Top Panel (4 or 6 holes)	☐ C2T1931FBK1	☐ C2T1931FBK1	☐ C2T2431FBK1	
		42" Fan Top Panel (4 or 6 holes)	☐ C2T1936FBK1	☐ C2T1936FBK1	☐ C2T2436FBK1	
		31.5" Fan Top Panel (4x 4.7" Fans)	☐ C2T1923F4BK1	☐ C2T1923F4BK1	☐ C2T2423F4BK1	
		36" Fan Top Panel (4x 4.7" Fans)	☐ C2T1931F4BK1	☐ C2T1931F4BK1	☐ C2T2431F4BK1	
		42" Fan Top Panel (4x 4.7" Fans)	☐ C2T1936F4BK1	☐ C2T1936F4BK1	☐ C2T2436F4BK1	
		31.5" Fan Top Panel (1x 10" Fan)	☐ C2T1923F10BK1	☐ C2T1923F10BK1	☐ C2T2423F10BK1	
36" Fan Top Panel (1x 10" Fan)	☐ C2T1931F10BK1	☐ C2T1931F10BK1	☐ C2T2431F10BK1			
42" Fan Top Panel (1x 10" Fan)	☐ C2T1936F10BK1	☐ C2T1936F10BK1	☐ C2T2436F10BK1			
Step 6 Bottom Panel		31.5" Solid Bottom Panel	☐ C4B2431SBK1	☐ C4B2431SBK1	☐ C4B3031SBK1	
		36" Solid Bottom Panel	☐ C4B2436SBK1	☐ C4B2436SBK1	☐ C4B3036SBK1	
		42" Solid Bottom Panel	☐ C4B2442SBK1	☐ C4B2442SBK1	☐ C4B3042SBK1	
Step 7 Vertical Manager		Vertical Open Tray (each)	☐ VCT73	☐ VCT77	☐ VCT77	
		Vertical Cable Manager w/Door (each)	☐ C4VCM73BK1	☐ C4VCM77BK1	☐ C4VCM77BK1	
		Looking for a fingered, fiber or other manager? Contact us to for more details.				
Step 8 Misc Hardware		Casters (Set of 4) 1000lb capacity	☐ 1425BH	☐ 1425BH	☐ 1425BH	
		Baying Kit	☐ CGH01	☐ CGH01	☐ CGH01	
		Grounding Kit	☐ GRDKIT04	☐ GRDKIT04	☐ GRDKIT04	
		10-32 Black Screws w/washers (25 pack)	☐ 1421ABK25	☐ 1421ABK25	☐ 1421ABK25	
		10-32 Cage Nuts (25 pack)	☐ 1421CNA25	☐ 1421CNA25	☐ 1421CNA25	
		Seismic Bolt-Down Kit	☐ C4K-Z4	☐ C4K-Z4	☐ C4K-Z4	
Step 9	ADD ACCESSORIES		ADD ACCESSORIES		ADD ACCESSORIES	
						
	SEE PAGE 18		SEE PAGES 18-19		SEE PAGES 20-21	

Rack Cabinet Solutions

CL Series - Co-Location Cabinet System




Shown
with optional
CLTROUGH


Hammond's Co-location Rack Cabinet features four (4) different bay configurations. Whether you are leasing the space or want to restrict access to sections of your cabinet, the Hammond CL Series is loaded with innovative features.

The CL features a fully-welded 14-gauge steel frame with 16-gauge doors and side panels. Recommended maximum weight load tested for 1,800 lb. Standard available configurations available in 36" and 42" depths.


CL Frame	Four (4) leveling feet are included with support for optional casters. Grounding studs provided on frame as well as side panels and doors. One single frame allows multiple bay configurations. 1-Bay = 44U, 2-Bay = 21U, 3-Bay = 14U, 4-Bay = 10U
Mounting Rails	Infinitely adjusting EIA-compliant square-hole or tapped 10-32 rail. Rails include unit markings to assist equipment installation.
Cable Entry & Management	Vertical Cable Managers can be installed either top or bottom. Designed to accommodate sliding rail mount kit on servers.
Thermal Performance	Perforated front and rear doors rated for 65% air flow. Doors lift off for easy equipment installation. Cabinet top includes brushed cable entry for cable managers, removable top panel and provisions for containment system and cable trough accessories.
Security	Doors include 4-pin combination lock with key override. Vented shelves include rear removable panels for vertical PDU installations. Optional Security upgrade kit ensures entire cabinet is tamper-proof and restricts bay users from feeding cables from one bay to another.
Finish	All CL cabinet components (and many accessories) are finished in textured black powder paint.



Doors open 180° and can be removed by swinging open and lifting off.



Easily remove cover panels to install a vertical PDU.



Vertical Cable Management can easily be moved to top or bottom.



One frame fits all bay configurations. Easily pass cables between cabinets.




Build your own assembly at: www.q-assembly.com

Your **QUICK & EASY** configuration tool is just a click away!



HAMMOND MODIFICATION SERVICES



Convert your CL cabinets into an air containment system. The product designers at Hammond Mfg can work with you to design the perfect cabinet solution.

If you require a cabinet with dimensions or colors different from what is shown, Please contact your local Hammond sales representative for more information on this service. Take a look at page 23 for more information.

CL Series - Co-Location Cabinet System

Use this chart to select your desired parts below. You may prefer to visit www.q-assembly.com and build your preferred solution online.			1 Bay (44U)	2 Bay (21U)	3 Bay (14U)	4 Bay (10U)
Step 1 Frame	Overall Dimensions 24" (W) x 83.4" (H)	36" deep	CLF244436BK	CLF244436BK	CLF244436BK	CLF244436BK
		42" deep	CLF244442BK	CLF244442BK	CLF244442BK	CLF244442BK
Step 2 Rails	19" Tapped 10-32 Rails (Pair)		CLTR44U	CLTR21U	CLTR14U	CLTR10U
	19" Square Hole Rails (Pair)		CLSR44U	CLSR21U	CLSR14U	CLSR10U
Step 3 Side Panels	Solid Side Panels (Each)	36" deep	CLSP4436BK (Compatible with all bay configurations)			
	Solid Side Panels (Each)	42" deep	CLSP4442BK (Compatible with all bay configurations)			
Step 4 Internal Kit	Each kit contains the doors, cable managers and bay shelves.	36" deep	CL1B36KIT	CL2B36KIT	CL3B36KIT	CL4B36KIT
		42" deep	CL1B42KIT	CL2B42KIT	CL3B42KIT	CL4B42KIT
Step 5 Top Panel	Solid Top Panel		C2T1923SBK1 (Compatible with all bay configurations)			
	Vented Top Panel		C2T1923VBK1 (Compatible with all bay configurations)			
Step 6 Bottom Panel	Solid Bottom Panel	36" deep	CLB2436 (Compatible with all bay configurations)			
	Solid Bottom Panel	42" deep	CLB2442 (Compatible with all bay configurations)			
Step 7	Baying Kit		GKIT (Compatible with all bay configurations)			
	Grounding Kit		GRDKIT04 (Compatible with all bay configurations)			
	Seismic Bolt-Down Kit		C4K-Z4 (Compatible with all bay configurations)			
	Security Upgrade Kit		CLSECUPG (Compatible with all bay configurations)			
	Cable Trough		CLTROUGH (Compatible with all bay configurations)			
	Right-hand door hinge kit.		CLRHNG (Compatible with all bay configurations)			
	PDU Toolless Mount Bracket		VCTPDU44U (Compatible with all bay configurations)			

RCI 3525 Electronic Locking Handle

The electronic locking rack handle provides the functionality of a manual latching system with the added benefit of electronic locking for access control and remote monitoring. It can be combined with any access control device for a basic self contained electronic access solution.

Features

- Remote lock and unlock control
- Single or multipoint locking
- Low power, gear motor driven mechanism
- Status LEDS on the front of the control unit
- Momentary or continuous lock actuation
- High Security DIN lock for mechanical key override
- Fits industry standard panel preparations
- Accommodates both left and right hand doors
- 78.7" (2000mm) Wire Harness and Hardware Kit included
- Product shipped with 3 keys (keyed alike)
- Compatible with Hammond C4 and CL Cabinet Series

Available from Hammond Mfg!



Digitus Biometrics db Biolock Electronic Locking Handle

When network security is a priority, have peace of mind that your data centre infrastructure is safely protected by a state-of-the-art biometric access control system.

Features

- Two configuration options:
 - A single fingerprint sensor can provide simultaneous access to front and rear door of the cabinet.
 - Separate fingerprint sensors on the front and rear cabinet doors, providing independent access to each door.
- Low power, gear motor driven mechanism
- Status LEDS on the front of the control unit
- Integrated electromechanical cabinet lock
- High Security DIN lock for mechanical key override
- Up to 8 external sensors to monitor cabinet doors, locks and panels
- RJ45 connector for networking
- Capacitive finger sensor for fake detection
- Compatible with Hammond C4 and CL Cabinet Series



Rack Accessories

2-Post Mounting Shelves:

Part No.	Description	Depth	Mount Depth	Rated
RASU190107UBK1	1U Cantilever Solid Shelf	7"	-	40 lb
RASU190115BK1	1U Cantilever Solid Shelf	15"	-	40 lb
RASUL190314BK1	2U Cantilever Solid Shelf	14.5"	-	65 lb
RASU190315BK1	2U Cantilever Solid Shelf	15"	-	100 lb
RASU190320BK1	2U Cantilever Solid Shelf	20"	-	100 lb
RASU190515BK1	3U Cantilever Solid Shelf	15"	-	200 lb
RASU190520BK1	3U Cantilever Solid Shelf	20"	-	200 lb
RASU190715BK1	4U Cantilever Solid Shelf	20"	-	200 lb
RASV190107UBK1	1U Cantilever Vented Shelf	7"	-	40 lb
RASV190115BK1	1U Cantilever Vented Shelf	15"	-	40 lb
RASV190120BK1	1U Cantilever Vented Shelf	20"	-	40 lb
RASVL190314BK1	2U Cantilever Vented Shelf	14.5"	-	65 lb
RASV190315BK1	2U Cantilever Vented Shelf	15"	-	100 lb
RASV190320BK1	2U Cantilever Vented Shelf	20"	-	100 lb
RASV190515BK1	3U Cantilever Vented Shelf	15"	-	200 lb
RASV190520BK1	3U Cantilever Vented Shelf	20"	-	200 lb
DNDMS19BK1	2U Centered Solid Shelf	19.5"	-	200 lb
DNDMS19GY2	2U Centered Solid Shelf (Grey)	19.5"	-	200 lb
DNDMV19BK1	2U Centered Vented Shelf	19.5"	-	200 lb
DNRMA1916BK1	3U Cantilever Solid Adjustable Shelf	16"	-	275 lb
DNRMA1920BK1	3U Cantilever Solid Adjustable Shelf	20"	-	275 lb
DNRMU19BK1	3U Dual-Channel Solid Shelf	19"	-	300 lb
DNRMU1924BK1	3U Dual-Channel Solid Shelf	24"	-	300 lb
DNRMV19BK1	3U Dual-Channel Vented Shelf	19"	-	300 lb
DNRMV1924BK1	3U Dual-Channel Vented Shelf	24"	-	300 lb
RKBM19BK1	3U Keyboard/ Monitor Shelf	15"	-	160 lb

4-Post Mounting Shelves & Drawers:

RSVS1918BK1	1U Sliding Vented Shelf	18"	20"	120 lb
RSVS1921BK1	1U Sliding Vented Shelf	21"	22"	120 lb
RSVS1926BK1	1U Sliding Vented Shelf	26"	28"	120 lb
RSVS1931BK1	1U Sliding Vented Shelf	31"	30"	120 lb
RSUS1918BK1	1U Sliding Solid Shelf	18"	20"	120 lb
RSUS1921BK1	1U Sliding Solid Shelf	21"	22"	120 lb
RSUS1926BK1	1U Sliding Solid Shelf	26"	28"	120 lb
RSUS1931BK1	1U Sliding Solid Shelf	31"	30"	120 lb
RSLIDEEX	Increases RSVS/ RSUS Mounting-Depth by 14"			
RMASU1925BK1	1U Adj. Depth Solid Shelf	25"	25" - 35"	75 lb
RMASUHD1925BK1	2U Adj. Depth Solid Shelf	25"	25" - 35"	200 lb
RMASU1930BK1	1U Adj. Depth Solid Shelf	30"	30" - 40"	75 lb
RMASUHD1936BK1	2U Adj. Depth Solid Shelf	36"	36" - 48"	200 lb
RMASV1925BK1	1U Adj. Depth Vented Shelf	25"	25" - 35"	75 lb
RMASVHD1925BK1	2U Adj. Depth Vented Shelf	25"	25" - 35"	200 lb
RMASV1930BK1	1U Adj. Depth Vented Shelf	30"	30" - 40"	75 lb
RMASVHD1936BK1	2U Adj. Depth Vented Shelf	36"	36" - 48"	200 lb
RDRW1900312BK1	2U Locking Drawer	12"	12"	120 lb
RDRW1900316BK1	2U Locking Drawer	16"	16"	120 lb
RDRW1900322BK1	2U Locking Drawer	22"	22"	120 lb
RDRW1900516BK1	3U Locking Drawer	16"	16"	120 lb
RDRW1900522BK1	3U Locking Drawer	22"	22"	120 lb
RDRW1900716BK1	4U Locking Drawer	16"	16"	120 lb
RAKS19BK1	4U Sliding Keyboard Shelf	15"	18"	120 lb
RSKS19005BK1	4U Swivel Keyboard Shelf	15"	34.8"	120 lb

Mounting Hardware

Part No.	Qty	Tap	Type
H1032BK25	25	10-32	Screws
H1032BK100	100	10-32	Screws
H1032BK500	500	10-32	Screws
1421ABK25	25	10-32	Screws
1421ABK100	100	10-32	Screws
1421ABK500	500	10-32	Screws
1421TS100	100	10-32	Thumb Screws
1421TS250	250	10-32	Thumb Screws
1421CNA25	25	10-32	Cage Nuts
1421CNA100	100	10-32	Cage Nuts
1421CNA250	250	10-32	Cage Nuts
1421N25	25	10-32	Clip Nuts
1421N100	100	10-32	Clip Nuts
1421N250	250	10-32	Clip Nuts
H1224S25	25	12-24	Screws
H1224S100	100	12-24	Screws
H1224S500	500	12-24	Screws
1421CNC25	25	12-24	Cage Nuts
1421CNC100	100	12-24	Cage Nuts

There are many other hardware options to choose from. Take a look at: www.hammondmgf.com/hardware.htm

Filler Panels

Install in unused rack space to improve both cooling efficiency and system esthetics.

Part No.	Description
PBPS19001BK2	1U Solid Steel Panel
PBPS19003BK2	2U Solid Steel Panel
PBPS19005BK2	3U Solid Steel Panel
PBPS19007BK2	4U Solid Steel Panel
PBPS19008BK2	5U Solid Steel Panel
PPFS19001BK2	1U Steel Perforated Panel
PPFS19003BK2	2U Steel Perforated Panel
PPFS19005BK2	3U Steel Perforated Panel
PPFS19007BK2	4U Steel Perforated Panel
PPFS19008BK2	5U Steel Perforated Panel
PBFS19001BK2	1U Formed Solid Steel Panel
PBFS19003BK2	2U Formed Solid Steel Panel
PBFS19005BK2	3U Formed Solid Steel Panel
PBFS19007BK2	4U Formed Solid Steel Panel
PBFS19008BK2	5U Formed Solid Steel Panel
PBPA19001BK2	1U Aluminum Steel Panel
PBPA19003BK2	2U Aluminum Steel Panel
PBPA19005BK2	3U Aluminum Steel Panel
PBPA19007BK2	4U Aluminum Steel Panel
PBPA19008BK2	5U Aluminum Steel Panel

Please note that we have panels ranging in rack unit size from 1U up-to 18U. Visit www.hammondmgf.com for more details.








Magnetic Panel Cover



Part No.	Description
MPC616	2-Pack of 6" x 16" 3mm Magnet Sheets

Please note this is a sample of our available shelves and drawers. For a full selection, visit www.hammondmgf.com.

Cable Management


Part No.	Description
 PCMD19001BK1	1U Hinged Horizontal Cable Manager (2.5" Overall Depth)
 PCMD19003BK1	2U Hinged Horizontal Cable Manager (2.5" Overall Depth)
 PCMD19005BK1	3U Hinged Horizontal Cable Manager (2.5" Overall Depth)
 PCMD19001BK1	1U Hinged Finger Panel (3" Depth)
 PCMD19003BK1	2U Hinged Finger Panel (3" Depth)
 PCMD19005BK1	3U Hinged Finger Panel (3" Depth)
 PCMB19001BK1	1U Steel Ring Panel
 PCMB19003BK1	2U Steel Ring Panel
 PCMB19001BK1	1U Steel Ring Panel - 23" Mounting
 PCMB19003BK1	2U Steel Ring Panel - 23" Mounting
 HCM190UBK1	0U 19" Lacing Bar w/Hook & Loop Strapping (48")
 HCM230UBK1	0U 23" Lacing Bar w/Hook & Loop Strapping (48")
 CMRBK1	1U Single Cable Ring - 1.25" Wide
 CMR3BK1	2U Single Cable Ring - 1.25" Wide
CMRC34BK1	1.5" x 3" x 4" Cable Ring Bracket
CMRC36BK1	1.5" x 3" x 6" Cable Ring Bracket
CMRC126BK1	1.5" x 12" x 6" Cable Ring Bracket
PCMT19003BK1	2U Rack Panel Mount Trough
CGUIDE	2U Hinged Cable Guide w/tie straps
CMSTRAP5	5 Hook and Loop Straps - Supports Max. 3.5" diameter bundles

Vertical Cable Managers

Hammond now offers a full range of vertical cable management solutions. Whether you require management for an open framed rack or server cabinet Hammond has the options you require.


Our Cable Management offering includes:

- Standard hinged door VCM
- Cable Tray with or without Toolless PDU mounting
- New fingered manager with optional cable spools and reversing door.



Rack Mount Monitor Bracket


- Heavy duty 12 gauge formed steel
- 3U for small screens 15" - 27"
- 10U for large screens 32" and up
- Includes monitor mounting screws
- Rack mounting hardware not included
- Black powder paint finish



Part No.	Description
RMMB193UBK3	3U - VESA MIS-D standard screen mount
RMMB1910UBK3	10U - VESA MIS-F standard screen mount

Rack Mount Fan Trays

- 1U 19" Rack Mount Fan Trays
- Ideal solution for hot spots
- Integral finger guards
- Circuit breaker protection
- Black powder paint finish



Part No.	Description	Max Mount Depth
FT300TA1BK	3-Fan, 300 CFM	Unlimited
FT600TA1BK	6-Fan, 600 CFM	19.2"
FT900TA1BK	9-Fan, 900 CFM	24.7"
FT300HA1BK	3-Fan, 300 CFM, ON/OFF Switch	Unlimited
FT600HA1BK	6-Fan, 600 CFM, ON/OFF Switch	19.2"
FT900HA1BK	9-Fan, 900 CFM, ON/OFF Switch	24.7"


Fan Components



Part No.	Description
DNMF100AC115	4.7" Fan - 105 CFM
DNFK1AC120	Single (1) Fan kit with grills and cord - 100 CFM
DNFK2AC120	Dual (2) Fan kit with grills and cord - 200 CFM
DNFG	Chrome Fan Guard with screws
DNFCD2P	Daisy Chain 2-Fan Cord - Lead Length 24"
DNFC48P	Single Fan Cord - Lead Length 48"

Fan Panel Assembly

- 3U 19" Rack Mount Fan Panel
- Target hot-spots
- 4.7" Fans with grill
- Includes 24" power cable
- Black powder coated



Part No.	Description
PPGPFA	Two (2) Fans - (Total 200 CFM, 60 dBA)
FP3F115	Three (3) Fans - (Total 300 CFM, 62 dBA)

Air Intake Blower

- 115Vac 50/60 Hz, UL recognized
- CSA certified, ball bearing type, cooled by incoming air
- Includes permanent filter



Part No.	Description
HB2160A	2U - Intake Blower (125 CFM) with 6ft cord
HB3250A	3U - Intake Blower (200 CFM) with 6ft cord
HB4500A	4U - Intake Blower (465 CFM) with 6ft cord

Detachable Ground Cable

- 12.5" long - 10 Gauge Copper Wire.
- Terminated with crimped on terminals.
- Terminal hole is 0.256" diameter.
- Includes mounting hardware for both 1/4" and 10-32
- Includes stick-on grounding symbols (two for each jumper)



Part No.	Description
GRDKIT04	Ground Cable with Quick Disconnect

Rack Unit Label



Part No.	Description
RULBK	Universal Rack Unit Label - up to 49U

Horizontal Outlet Strips

All Outlet Strips on this page include a 125 VAC circuit breaker, use 1U (1.75") panel space, and are finished in black.

All Outlet Strips on this page include a 125 VAC circuit breaker, use 1U (1.75") panel space, and are finished in black.

Part No.	# of Outlets		Power Indication		Cord Length	Plug Type	Amp Rating	Surge	Finish
	Front	Rear	Switch	Pilot Light Only					
15A Outlet Strip with FRONT Mounted Receptacles									
1582H6A1BK	6	-	Illuminated	-	6ft	5-15P	15A	-	Black
1582H6B1BK	6	-	Illuminated	-	15ft	5-15P	15A	-	Black
1582H8A1BK	8	-	Illuminated	-	6ft	5-15P	15A	-	Black
1582H8B1BK	8	-	Illuminated	-	15ft	5-15P	15A	-	Black
1582T6A1BK	6	-	-	Yes	6ft	5-15P	15A	-	Black
1582T6B1BK	6	-	-	Yes	15ft	5-15P	15A	-	Black
1582T8A1BK	8	-	-	Yes	6ft	5-15P	15A	-	Black
1582T8B1BK	8	-	-	Yes	15ft	5-15P	15A	-	Black

15A Outlet Strip with REAR Mounted Receptacles

1583H6A1BK	-	6	Illuminated	-	6ft	5-15P	15A	-	Black
1583H6B1BK	-	6	Illuminated	-	15ft	5-15P	15A	-	Black
1583H8A1BK	-	8	Illuminated	-	6ft	5-15P	15A	-	Black
1583H8B1BK	-	8	Illuminated	-	15ft	5-15P	15A	-	Black
1583T6B1BK	-	6	-	Yes	15ft	5-15P	15A	-	Black
1583T8A1BK	-	8	-	Yes	6ft	5-15P	15A	-	Black
1583T8B1BK	-	8	-	Yes	15ft	5-15P	15A	-	Black
1583H6A1SBK	-	6	Illuminated	-	6ft	5-15P	15A	Yes	Black
1583H6B1SBK	-	6	Illuminated	-	15ft	5-15P	15A	Yes	Black

15A Outlet Strip with FRONT AND REAR Mounted Receptacles

1583H6A1BKX	2	4	Illuminated	-	6ft	5-15P	15A	-	Black
1583H6B1BKX	2	4	Illuminated	-	15ft	5-15P	15A	-	Black
1583T6A1BKX	2	4	-	Yes	6ft	5-15P	15A	-	Black
1583H12A1BKX	6	6	Illuminated	-	6ft	5-15P	15A	-	Black
1583H12B1BKX	6	6	Illuminated	-	15ft	5-15P	15A	-	Black
1583T12A1BKX	6	6	-	Yes	6ft	5-15P	15A	-	Black

15A Outlet Strip with 90 Degree Offset Receptacles

1582H6A1BKRA	6	-	Illuminated	-	6ft	5-15P	15A	-	Black
1582H6B1BKRA	6	-	Illuminated	-	15ft	5-15P	15A	-	Black
1582T6A1BKRA	6	-	-	Yes	6ft	5-15P	15A	-	Black
1582T6B1BKRA	6	-	-	Yes	15ft	5-15P	15A	-	Black
1583T12A1SBKRAX	6	6	-	Yes	6ft	5-15P	15A	Yes	Black
1583H6A1BKRA	-	6	Illuminated	-	6ft	5-15P	15A	-	Black
1583H6B1BKRA	-	6	Illuminated	-	15ft	5-15P	15A	-	Black
1583T6A1BKRA	-	6	-	Yes	6ft	5-15P	15A	-	Black
1583T6B1BKRA	-	6	-	Yes	15ft	5-15P	15A	-	Black

20A Outlet Strips with FRONT OR REAR-Mounted Receptacles

1589H6D1BKRF	6	-	No Light	-	15ft	L5-20P	20A	-	Black
1589H6F1BKRF	6	-	No Light	-	6ft	5-20P	20A	-	Black
1589H6G1BKRF	6	-	No Light	-	15ft	5-20P	20A	-	Black
1589H8G1BKRF	8	-	No Light	-	15ft	5-20P	20A	-	Black
1589T6D1BKRF	6	-	-	Yes	15ft	L5-20P	20A	-	Black
1589T6G1BKRF	6	-	-	Yes	15ft	5-20P	20A	-	Black
1589T8F1BKRF	8	-	-	Yes	6ft	5-20P	20A	-	Black
1589H6D1BKRR	-	6	No Light	-	15ft	L5-20P	20A	-	Black
1589H6F1BKRR	-	6	No Light	-	6ft	5-20P	20A	-	Black
1589H6G1BKRR	-	6	No Light	-	15ft	5-20P	20A	-	Black
1589H8G1BKRR	-	8	No Light	-	15ft	5-20P	20A	-	Black
1589T6D1BKRR	-	6	-	Yes	15ft	L5-20P	20A	-	Black
1589T6F1BKRR	-	6	-	Yes	6ft	5-20P	20A	-	Black
1589T6G1BKRR	-	6	-	Yes	15ft	5-20P	20A	-	Black

15 & 20A Outlet Strip with built-in Ammeter

1582H6A1BKAM	6	-	Illuminated	-	6ft	5-15P	15A	-	Black
1583H6A1BKAM	-	6	Illuminated	-	6ft	5-15P	15A	-	Black
1583T6A1BKAM	-	6	-	Yes	6ft	5-15P	15A	-	Black
1583T6B1BKAM	-	6	-	Yes	15ft	5-15P	15A	-	Black
1589H6F1BKRRAM	-	6	No Light	-	6ft	5-20P	20A	-	Black
1589T6C1BKRRAM	-	6	-	Yes	6ft	L5-20P	20A	-	Black
1589T6F1BKRRAM	-	6	-	Yes	6ft	5-20P	20A	-	Black

With over 500 skus of Outlet Strips, we could not possibly add them all into this product guide.

For additional sizes and options, please visit www.hammondmfg.com

Plug Types



"Straight Blade"
NEMA 5-15P



"Locking Plug"
NEMA L5-15P



"Straight Blade"
NEMA 5-20P



"Locking Plug"
NEMA L5-20P

Vertical & Industrial Outlet Strips



Includes hardware required to mount to a cabinet, unistruts or open frame racks.

Additional kits can be purchased by ordering Part No. **1585CLIP**

When mounting to HWM series use Part No. **HWMPCLIP**
See page 8 for details.

Part No.	Part No.	# of	Overall	Cord	Surge	Plug	Amp	Finish
Pilot Light	On/Off Switch	Outlets	Length	Length	Protection	Type	Rating	
15A Vertical Outlet Strips								
15851T6A1	15851H6A1	6	18"	6ft	No	5-15P	15A	Silver
15851T6B1	15851H6B1	6	18"	15ft	No	5-15P	15A	Silver
15852T8A1	15852H8A1	8	24"	6ft	No	5-15P	15A	Silver
15852T8B1	15852H8B1	8	24"	15ft	No	5-15P	15A	Silver
15853T6A1	15853H6A1	6	36"	6ft	No	5-15P	15A	Silver
1585T8A1	1585H8A1	8	48"	6ft	No	5-15P	15A	Silver
1585T10A1	1585H10A1	10	48"	6ft	No	5-15P	15A	Silver
1585T10B1	1585H10B1	10	48"	15ft	No	5-15P	15A	Silver
1585T10B1S	1585H10B1S	10	48"	15ft	Yes*	5-15P	15A	Silver
1586T10A1	1586H10A1	10	60"	6ft	No	5-15P	15A	Silver
1586T10B1	1586H10B1	10	60"	15ft	No	5-15P	15A	Silver
1586T12A1	1586H12A1	12	60"	6ft	No	5-15P	15A	Silver
1587T10A1	1587H10A1	10	70"	6ft	No	5-15P	15A	Silver
1587T12A1	1587H12A1	12	70"	6ft	No	5-15P	15A	Silver
1587T12C1	1587H12C1	12	70"	6ft	No	L5-15P	15A	Silver
1587T12D1	1587H12D1	12	70"	15ft	No	L5-15P	15A	Silver
1588T12A1	1588H12A1	12	77"	6ft	No	5-15P	15A	Silver
1588T12A1BK	1588H12A1BK	12	77"	6ft	No	5-15P	15A	Black
1588T12B1BK	1588H12B1BK	12	77"	15ft	No	5-15P	15A	Black

20A Vertical Outlet Strips								
1589T48D1	1589H48D1	8	48"	15ft	No	L5-20P	20A	Silver
1589T48F1	1589H48F1	8	48"	6ft	No	5-20P	20A	Silver
1589T48G1	1589H48G1	8	48"	15ft	No	5-20P	20A	Silver
1589T48D116	1589H48D116	16	48"	15ft	No	L5-20P	20A	Silver
1589T48F116	1589H48F116	16	48"	6ft	No	5-20P	20A	Silver
1589T48G116	1589H48G116	16	48"	15ft	No	5-20P	20A	Silver
1589T60C1	1589H60C1	10	60"	6ft	No	L5-20P	20A	Silver
1589T60D1	1589H60D1	10	60"	15ft	No	L5-20P	20A	Silver
1589T60F1	1589H60F1	10	60"	6ft	No	5-20P	20A	Silver
1589T60G1	1589H60G1	10	60"	15ft	No	5-20P	20A	Silver
1589T70C1	1589H70C1	10	70"	6ft	No	L5-20P	20A	Silver
1589T70D1	1589H70D1	10	70"	15ft	No	L5-20P	20A	Silver
1589T70F1	1589H70F1	10	70"	6ft	No	5-20P	20A	Silver
1589T70G1	1589H70G1	10	70"	15ft	No	5-20P	20A	Silver
1589T70D124	1589H70D124	24	70"	15ft	No	L5-20P	20A	Silver
1589T70F124	1589H70F124	24	70"	6ft	No	5-20P	20A	Silver
1589T70G124	1589H70G124	24	70"	15ft	No	5-20P	20A	Silver
1589T77C1	1589H77C1	12	77"	6ft	No	L5-20P	20A	Silver
1589T77D1	1589H77D1	12	77"	15ft	No	L5-20P	20A	Silver
1589T77F1	1589H77F1	12	77"	6ft	No	5-20P	20A	Silver
1589T77G1	1589H77G1	12	77"	15ft	No	5-20P	20A	Silver

Are you looking for an IP Managed or enhanced PDU? Our alliance with power distribution industry leaders gives you access to the products you need, mounted within the Hammond Cabinet your trust.

When we do not have an outlet strip that meets your needs, we can help find you a one that will.

Please contact your Hammond Mfg representative call 1-866-535-DATA (3282) for more information.



Server Technology
Solutions for the Data Center Equipment Cabinet

GEIST

15A Industrial & Commercial Grade Outlet Strip



Part No.	# of Outlets	Power Indication Lighted On/Off Switch	Pilot Light Only	Surge Protection	Cord Length	Plug Type	Amp Rating	Finish
1584H6A1	6	Yes	-	No	6ft	5-15P	15A	Black
1584H6A1S	6	Yes	-	Yes	6ft	5-15P	15A	Black
1584H6B1	6	Yes	-	No	15ft	5-15P	15A	Black
1584H6B1S	6	Yes	-	Yes	15ft	5-15P	15A	Black
1584H8A1	8	Yes	-	No	6ft	5-15P	15A	Black
1584H8B1	8	Yes	-	No	15ft	5-15P	15A	Black
1584T6A1	6	-	Yes	No	6ft	5-15P	15A	Black
1584T6A1S	6	-	Yes	Yes	6ft	5-15P	15A	Black
1584T6B1	6	-	Yes	No	15ft	5-15P	15A	Black
1584T8A1	8	-	Yes	No	6ft	5-15P	15A	Black
1584T8B1	8	-	Yes	No	15ft	5-15P	15A	Black

Hammond Modification Services



HAMMOND MODIFICATION SERVICES

When standard product just won't do!

Whether you require a unique paint color, an additional cutout or product assembly, Hammond Modification Services has you covered. As an ISO 9001:2008 certified company, Hammond offers services that complement our existing high quality product lines. Hammond offers three unique services to take our products to the next level.

These services include:

1. Product Modifications
2. Assembly & Configuration
3. Drop-Shipment.



Paints:

- Standard Colors
- RAL Colours
- Custom Colours




Holes & Cutouts:

- Knockouts
- Punches
- Precision Laser Cutting




Mounting:

- Tapped Holes
- Mounting Studs
- Ground & Bonding Studs
- PEM Studs & Nuts



Construction Changes:

- Changes to Height, Width, Depth



Accessories:

- Windows
- Shelves
- Climate Control
- Outlet Strips


Assembly & Configuration Services

When a standard product simply will not meet your requirements, Hammond offers a full range of Modification options that include: paint color, holes and cutouts, mounting, changes to height/width/depth, as well as accessories options. Often when our customers order a product, they bundle it with accessories. If you want to skip the hassle of installing the accessories yourself, we can do it for you. If you do not have the space or facilities to assemble a large volume of products, Hammond Assembly Services can save you hours of time spent installing accessories. Hammond Assembly Services will reduce the waste in packaging and ensure your product is delivered, ready for use.



Q-Assembly is a quoting tool that enables you to configure your Hammond product with your choice of components and accessories.

Submit your Q-Assembly and our sales team will provide a quotation to the Hammond distribution partner of your choice.



Start building your assembly at:
www.q-assembly.com

Drop-Shipment Services


Whether you want to reduce handling fees or your facilities cannot accommodate inventory, our Drop-Shipment Services can add value to your business. We can deliver your Hammond orders directly to your customer across North America and within your marketing territory. Ask about our Drop-Shipment Services when placing your order.

Note: Special freight requirements may need to be arranged prior to shipment. Contact us for additional details.

Hammond Modification Portfolio

3U RCHS with Modified Panels

Desktop cabinets work well for IT and Test/Measurement applications. Below is a modified RCHS that was designed smaller as a mobile cart for heavy specialized equipment. The mounted panels were modified to align with accessories installed on-site.



CL Series Sliding Doors For Air Containment

The Hammond CL has options for 1-Bay up to 4-Bay making it a versatile cabinet when it relates to heat containment. In this example, we built a sliding door for the end of a containment aisle.



Extra Wide Swing Out Cabinet

Wall mount cabinets are a convenient way to mount both IT and security equipment within the same cabinet. Below is a modified HWM cabinet that was designed to be extra-wide with vertical cable managers and cable rings.



Adjustable Depth Side Panels

The depth of a four (4) post rack can be adjusted as the equipment mounted within them changes. Below is a set of adjustable-depth 24U side panels that improve esthetics and security of the installation.



4-Bay Cabinet with Red Doors


Colors help a cabinet stand out in a computer room and enhance cabinet features. Below is a modified CL cabinet that includes a high-gloss red powder coat with a black frame. Using a color on your cabinet can also support a companies branding strategy.



30in Wide Cabinet with Chimney

Data center cooling is a growing concern among IT Managers. Our modified C4 Cabinet with passive chimney (below) provides heat containment for high kW equipment.

With the cabinet frame painted white, the computer room is visibly brighter.



Do you need help sourcing the best product for your project?
Contact us today toll-free with your product and technical inquiries.

For inquiries in Canada please call:

877-535-DATA (3282)

For inquiries within Québec please call:

866-574-9005

For inquiries within United States please call:

716-630-7030

Canada

Hammond Manufacturing Company Limited
394 Edinburgh Rd, North, Guelph, Ontario, Canada N1H 1E5
Tel: (519) 822-2960 Fax: (519) 822-0715 dcisales@hammfg.com

Les Fabrications Hammond (Québec) Inc.
4240, Seré, St. Laurent, Québec, Canada H4T 1A6
Tel: (514) 343-9010 Fax: (514) 343-9941 quebec@hammondmfg.com

USA

Hammond Manufacturing Company Inc.
475 Cayuga Rd. #100, Cheektowaga, NY 14225-1309 USA
Tel: (716) 630-7030 Fax: (716) 630-7042 us-info@hammondmfg.com

Europe

Hammond Electronics Limited
1 Onslow Close, Kingsland Business Park, Basingstoke
Hampshire, United Kingdom RG24 8QL
Tel: 01256 812812 Fax: 01256 332249 uk-info@hammondmfg.com

Australia

Hammond Electronics Pty Ltd
ABN 13 099 121 981
11 - 13 Port Rd., Queenstown SA 5014
Tel: +61-8-8240-2244 Fax: +61-8-8240-2255 oz-info@hammondmfg.com

Learn more at:
www.hammondmfg.com



facebook.com/hammondmfg



youtube.com/hammondmfg



twitter.com/hammondmfg



**HAMMOND
MANUFACTURING®**



Canadian Security Association
L'Association canadienne de la sécurité

Distributed by: