

MICRO SWITCH

FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED MFG CODE 81928

SWITCH—BASIC

CATALOG LISTING

BE-2RV24-A2

BE-2RV24-A2

M

DRAWING
NUMBER

26

ISSUE

8

REPLACES

PR-3691

RELEASE NO

CHECK

REVISIONS

A C032973

O B W

5 DEC 73

B C036627

C J H

8 APR 76

C CO

58782

WJM

24 JAN 86

D CO-

73287-J

J A L

22 NOV 93

E CO-

77588

MAM

29 MAR 94

CHECK

12 NOV 73

12 NOV 73

LSD

73


NOV 73

NOV 73

NOV 73

NOV 73

NOV 73



NOTE -



- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 2 1/2 OZ MAX

RELEASE FORCE ----- 1/2 OZ MIN

PRETRAVEL ----- .625 MAX

DIFFERENTIAL TRAVEL ----- .109 MAX

OVERTRAVEL ----- .078 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

25-A-125, 250, 480 VAC 1 HP-125 VAC,
2 HP-250 OR 480 VAC, PILOT DUTY
750 VA-480 VAC, MAX, 60/75°C (Cu)



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE

ONE PLACE () ± .030

TWO PLACE () ± .015

THREE PLACE () ± .005

ANGLES ±

WEIGHT

FO-52848

DRAWN

NOV 73

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BE-2RV24-A2](#)